



4		3		2		1		
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.								
LOC EY		DIST 25		REVISIONS				
P		LTR		DESCRIPTION		DATE	DWN	APVD
		M		REV PER ECR 07-027142		13NOV07	JR	TM
AMP WIRE RANGE 16-14 AWG STRANDED				 Listed 16-14 AWG STRANDED				
 COPPER SPLICE HEAT SHRINKABLE TUBING				1 TUBING MATERIAL; CROSS-LINKED POLYMER WITH MELT LINER; COLOR, BLUE; BLACK INK LEGEND 1/16 MIN; HEIGHT; ONE FULL APPEARANCE MIN. 2 TEMP RATING -65°F TO 257°F { -55°C TO 125°C } 3 SHIPPING WEIGHT .004 LBS EACH 4 VOLTAGE RATING: 600 V MAX (1000 V MAX FIXTURES & SIGNS)  MATERIAL & FINISH ; BODY - COPPER, TIN PLATED SLEEVE - NYLON				
1000		5.21 [.205]		2.16 [.085]		603503-3		
50/BOX		5.21 [.205]		2.16 [.085]		603503-2		
PACKAGE TYPE		EXPANDED I.D. MIN		RECOVERED I.D. MAX		PART NO.		
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN JR RUTH 24JUN04		Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK T MICHIELUTTI 24JUN04		NAME		
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13 [.005] 4 PLC ± - ANGLES ± -		APVD T MICHIELUTTI 24JUN04		PRE-INSULATED SEALED SPLICE WIRE SIZE: 16-14 AWG		
MATERIAL - 		FINISH - 		PRODUCT SPEC -		SIZE A3		
CUSTOMER DRAWING				APPLICATION SPEC -		CAGE CODE 00779		
				WEIGHT -		DRAWING NO C-603503		
				RESTRICTED TO -		SCALE 1:1		
				SHEET 1		OF 1		
				REV M				

AMP 1470-19 REV 31MAR2000