


FLEXO NR

- Excellent Noise Suppression
- Abrasion Resistant
- Extremely Lightweight
- Attractive Appearance
- Does Not Trap Heat Or Moisture

Nominal Size	Part #	Expansion Range		Bulk Spool	Shop Spool	Available Colors	Lbs/100'
		Min	Max				
1/8"	NRN0.13BK	1/8"	3/16"	500'	100'	Black	0.3
1/4"	NRN0.25BK	1/4"	3/8"	500'	100'	Black	0.5
3/8"	NRN0.38BK	3/8"	1/2"	250'	100'	Black	0.9
1/2"	NRN0.50BK	1/2"	3/4"	250'	100'	Black	1.1
5/8"	NRN0.63BK	5/8"	1"	250'	100'	Black	1.5
3/4"	NRN0.75BK	3/4"	1 1/4"	250'	75'	Black	2.0
1"	NRN1.00BK	1"	1 5/8"	250'	50'	Black	2.4



Cut Cleanly
Hot Knife

Material

Polyethylene Terephthalate

Grade

NRN

Wall Thickness

.025"

Self-Fitting Protective Oversleeve


Flexo Noise Reduction (NR) is a biaxially braided sleeving combining monofilament and multifilament PET yarns to create a full coverage expandable sleeve that substantially reduces noise on wires, tubes and hoses. The lightweight, rugged construction also provides protection from abrasion and vibration that is far superior to foam harness sleeves. NR expands for easy installation over splices and connectors and is flexible enough for tight radius applications.

NR is used in body wiring harnesses, instrument panel and lighting wiring, cable and hose assemblies, and other limited access applications where noise reduction is desirable.

The braided construction will not hold moisture and drains quickly when immersed.

Colors Available:

Black (BK)



FLEXO NR



Abrasion Resistance
Medium

Abrasion Test Machine
Taber 5150

Abrasion Test Wheel
Calibrase H-18

Abrasion Test Load
500g



Rating _____ ***UL94**
**UL 94 V-O Raw Material*



Chemical Resistance

1=No Effect 4=More Affected
2=Little Effect 5=Severely Affected
3=Affected

Aromatic Solvents	_____	2
Aliphatic Solvents	_____	1
Chlorinated Solvents	_____	3
Weak Bases	_____	1
Salts	_____	1
Strong Bases	_____	2
Salt Water 0-S-1926	_____	1
Hydraulic Fluid MIL-H-5606	_____	1
Lube Oil MIL-L-7808	_____	1
De-Icing Fluid MIL-A-8243	_____	1
Strong Acids	_____	3
Strong Oxidants	_____	2
Esters/Keytones	_____	1
UV Light	_____	1
Petroleum	_____	1
Fungus ASTM G-21	_____	1
Halogen Free	_____	Yes
RoHS	_____	Yes
SVHC	_____	None

Melt Point


ASTM D-2117
446°F (230°C)

Maximum Continuous

MIL-I-23053
257°F (125°C)

Minimum Continuous

-94°F (-70°C)



PHYSICAL PROPERTIES

Monofilament Diameter _____ **.010**
ASTM D-204

Flammability Rating _____ ***UL94**
**UL 94 V-O Raw Material*

Recommended Cutting _____ **Scissor/HK**

Colors _____ **1**

Wall Thickness _____ **.025**

Tensile Strength (Yarn) _____ **7.5**
ASTM D-2256 Lbs

Specific Gravity ASTM D-792 _____ **1.38**

Moisture Absorption _____ **.1-.2**
% ASTM D-570

Hard Vacuum Data ASTM E-595 at 10-5 torr

TML _____ **.19**

CVCM _____ **.00**

WVR _____ **.16**

Outgassing _____ **Med**

Oxygen Index _____ **21**
ASTM D-2863