


PANDUIT PART NO.	MAX BUNDLE DIAMETER	PACKAGE QTY	LENGTH L = ±.3 [7]
MLT1S-CP316	1" [25]	100	5.0" [127]
MLT2S-CP316	2" [51]	100	7.9" [201]
MLT2.7S-CP316	2.7" [69]	100	10.2" [259]
MLT4S-CP316	4" [102]	100	14.3" [362]
MLT6S-CP316	6" [152]	100	20.5" [521]
MLT8S-CP316	8" [203]	100	26.8" [679]
MLT10S-CP316	10" [254]	100	33.0" [838]



NOTES:

1. APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, ST3MT, HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 200 LBS. (889 NEWTONS) WHEN TESTED ON A 1.5" MANDREL.
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
 - .XXX = $\pm .010$ [.25]
 - .XX = $\pm .02$ [.5]
 - .X = $\pm .03$ [.8]
 - ANGLES = $\pm 2^\circ$
5. MATERIAL: 316 STAINLESS STEEL

FULLY ROUNDED
EDGES ALONG
STRAP BODY

SECTION A - A

SCALE 8:1

					PANDUIT CORP. TINLEY PARK, ILLINOIS			
					METAL LOCKING TIE STANDARD SERIES-316 STAINLESS STEEL -CUSTOMER DRAWING-			
08A	2/12	MIM	RGRO	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY				
REV	DATE	BY	CHK	DESCRIPTION	DRAWN BY JAMB	CHK'D DPN	SCALE 2x	DRAWING NO. N41120BS_DC