


Detailed Specifications & Technical Data

BELDEN
SENDING ALL THE RIGHT SIGNALS

METRIC MEASUREMENT VERSION

I601855 Fiber - TrayOptic®



For more Information
please call

1-800-Belden1



General Description:

FiberExpress Tray Optic Cable, 18-Fiber, OM1 OFNR, Loose Tube, Indoor & Outdoor Rated with UV Resistant Orange PVC Jacket, Industrial Grade, Water-blocked with Gigabit Ethernet Grade fiber.

Physical Characteristics (Overall)

Fiber Type:	62.5/125/250 Micron
Number of Fibers:	18
Core Diameter:	62.5 +/- 2.5
Core Non-Circularity:	5%; Maximum
Clad Diameter:	125 +/- 2
Clad Non-Circularity:	1%; Maximum
Primary Coating Material:	Acrylate
Primary Coating Diameter:	245 +/- 10

Fiber Color Code Chart:

Color
Blue
Orange
Green
Brown
Gray
White

Buffer Tube Diameter:	1.9
Buffer Tube Material:	Flame Retardant Thermoplastic
Buffer Tube Filling Material:	Synthetic Thixotropic Gel

Buffer Tube Color Code Chart:

Number	Color
1	Blue
2	Orange
3	Green

Core-clad Offset:	1.5 microns Maximum
-------------------	---------------------

Inner Jacket

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Color:	Orange
---------------------	--------

Overall Cable

Overall Cabling Fillers:	PVC
Overall Nominal Diameter:	11.176 mm

Mechanical Characteristics (Overall)

Storage Temperature Range:	-40°C To +80°C
Operating Temperature Range:	-40°C To +70°C
Bulk Cable Weight:	130.962 Kg/Km
Min. Bend Radius/Minor Axis:	223.520 mm
Min. Bend Radius for Long Term Application:	167.640 mm
Crush Resistance:	Passes TIA/EIA 455-41; 2000 N/cm

Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

I601855 Fiber - TrayOptic®

Impact Resistance:	Passes TIA/EIA 455-25; 2000 Impacts @ 1.6 N-m
Solar Radiation Resistance:	High
Water Penetration:	Passes TIA/EIA 455-82
Compound Flow:	Passes TIA/EIA 455-81
Max. Load for Installation:	2668.920 N
Max. Load for Long Term Application:	800.676 N
Proof Test:	100 kpsi

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	OFNR
CEC/C(UL) Specification:	OFNR
EU Directive 2011/65/EU (RoHS II):	Yes
IEEE Specification:	802.3Z
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2006
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	Suitable for installation in trays per NFPA 70.

Flame Test

C(UL) Flame Test:	FT4
IEEE Flame Test:	1202, IEEE 383 Vertical Tray Flame Test (70,000 BTU)

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Optical Characteristics (Overall)

Maximum Attenuation @ 850nm:	3.5 dB/km
Maximum Attenuation @ 1300nm:	1.2 dB/km
Point Loss @ 850nm & 1300nm:	0.2
Minimum Bandwidth @ 850nm:	200 MHz*km
Minimum Bandwidth @ 1300nm:	500 MHz*km
Refractive Index @ 850nm:	1.496
Refractive Index @ 1300nm:	1.491
Numerical Aperture:	.275
Maximum Gigabit Ethernet Length @ 850nm:	300 meters
Maximum Gigabit Ethernet Length @ 1300nm:	550 meters

Related Documents:

[Loose Tube Trayoptic Cable.pdf](#) - Loose Tube Trayoptic Cable

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
I601855	1 FT	0.000	ORANGE		REPLACED BY FD1T018RF

Revision Number: 2 Revision Date: 04-15-2015

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities

Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION



I601855 Fiber - TrayOptic®

and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.