





Belegungsplan
Loading-Plan



- Übertragungseigenschaften nach ISO/IEC 11801:2002: Class D.
- Schutzart: IP20
- Temperaturbereich: -40°C ...+70°C
- Transmission properties in accordance with ISO/IEC 11801:2002: Class D.
- Protection level: IP20
- Temperature range: -40°C ...+70°C

AWG 22/7 schleppfähig/trailing	09 45 751 1183	100 m
AWG 22/7 schleppfähig/trailing	09 45 751 1178	50 m
AWG 22/7 schleppfähig/trailing	09 45 751 1175	20 m
AWG 22/7 schleppfähig/trailing	09 45 751 1173	10 m
AWG 22/7 schleppfähig/trailing	09 45 751 1168	5 m
AWG 22/7 schleppfähig/trailing	09 45 751 1166	3 m
AWG 22/7 schleppfähig/trailing	09 45 751 1164	1,5 m
AWG 22/7 schleppfähig/trailing	09 45 751 1163	1 m
AWG 22/1 massiv/solid	09 45 751 1161	100 m
AWG 22/1 massiv/solid	09 45 751 1156	50 m
AWG 22/1 massiv/solid	09 45 751 1153	20 m
AWG 22/1 massiv/solid	09 45 751 1151	10 m
AWG 22/1 massiv/solid	09 45 751 1127	5 m
AWG 22/1 massiv/solid	09 45 751 1125	3 m
AWG 22/1 massiv/solid	09 45 751 1123	1,5 m
AWG 22/7 flexibel/stranded	09 45 751 0061	100 m
AWG 22/7 flexibel/stranded	09 45 751 0056	50 m
AWG 22/7 flexibel/stranded	09 45 751 0053	20 m
AWG 22/7 flexibel/stranded	09 45 751 0051	10 m
AWG 22/7 flexibel/stranded	09 45 751 0027	5 m
AWG 22/7 flexibel/stranded	09 45 751 0025	3 m
AWG 22/7 flexibel/stranded	09 45 751 0023	1,5 m
massiv / flexibel solid / stranded	Bestell-Nr. Part-No.	Maß a Dim. a



All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances	
	Dat.	Name		Dat.	Name		
32220	22.10.04	Wie	Detail.	11.06.03	Wae	RJ45 Kabel 4xAWG 22 IP20 RJ45 Cable 4xAWG 22 IP20 2x RJ45 Plastic	
32089	21.06.04	Wie	Insp.	11.06.03	VSo		
31017	02.12.03	Wae	Stand.				
31014	23.09.03	Wae					
31013							
Mod.	Dat.	Name	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP			TB 09 45 751 1123	
						Sub.	Blatt/ page