



STL34NF06

N-CHANNEL 60V - 0.024Ω - 34A PowerFLAT™ LOW GATE CHARGE STripFET™II MOSFET

PRELIMINARY DATA

TYPE	V _{DSS}	R _{DS(on)}	I _D
STL34NF06	60 V	< 0.028Ω	34 A



- TYPICAL R_{DS(on)} = 0.024Ω
- IMPROVED DIE-TO-FOOTPRINT RATIO
- VERY LOW PROFILE PACKAGE

DESCRIPTION

This Power MOSFET is the second generation of STMicroelectronics unique "STripFET™" technology. The resulting transistor shows extremely low on-resistance and minimal gate charge. The new PowerFLAT™ package allow a significant reduction in board space without compromising performance.

APPLICATIONS

- DC-DC CONVERTERS
- BATTERY MANAGEMENT IN NOMADIC EQUIPMENT



ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	Value	Unit
V _{DS}	Drain-source Voltage (V _{GS} = 0)	60	V
V _{DGR}	Drain-gate Voltage (R _{GS} = 20 kΩ)	60	V
V _{GS}	Gate- source Voltage	± 20	V
I _D	Drain Current (continuous) at T _C = 25°C (*) Drain Current (continuous) at T _C = 100°C	34 20	A A
I _{DM} (•)	Drain Current (pulsed)	136	A
P _{TOT}	Total Dissipation at T _C = 25°C	70	W
	Derating Factor	0.56	W/°C
E _{AS} (1)	Single Pulse Avalanche Energy	250	mJ
T _{stg}	Storage Temperature	-55 to 150	°C
T _j	Max. Operating Junction Temperature		

(•) Pulse width limited by safe operating area

(1) Starting T_j = 25°C, I_D = 17A, V_{DD} = 42V

(*) Current Limited by Wire Bonding is 20A

November 2002

1/6

STL34NF06

THERMAL DATA

Rthj-case	Thermal Resistance Junction-case Max	1.8	°C/W
Rthj-pcb (#)	Thermal Resistance Junction-ambient Max	31.2	°C/W

(*) When mounted on 1inch² FR4 Board, 2oz of Cu, t ≤ 10 sec.

ELECTRICAL CHARACTERISTICS (T_{CASE} = 25 °C UNLESS OTHERWISE SPECIFIED) OFF

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
V _{(BR)DSS}	Drain-source Breakdown Voltage	I _D = 250 μA, V _{GS} = 0	60			V
I _{DSS}	Zero Gate Voltage Drain Current (V _{GS} = 0)	V _{DS} = Max Rating V _{DS} = Max Rating, T _C = 125 °C			1 10	μA μA
I _{GSS}	Gate-body Leakage Current (V _{DS} = 0)	V _{GS} = ± 20V			±100	nA

ON (1)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
V _{GS(th)}	Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = 250μA	2			V
R _{DS(on)}	Static Drain-source On Resistance	V _{GS} = 10V, I _D = 17A		0.024	0.028	Ω

DYNAMIC

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
g _{fs} (1)	Forward Transconductance	V _{DS} = 30 V, I _D = 17 A		TBD		S
C _{iss}	Input Capacitance	V _{DS} = 25V, f = 1 MHz, V _{GS} = 0		920		pF
C _{oss}	Output Capacitance			225		pF
C _{rss}	Reverse Transfer Capacitance			80		pF

1. Pulsed: Pulse duration = 300 μs, duty cycle 1.5 %.

ELECTRICAL CHARACTERISTICS (CONTINUED)**SWITCHING ON**

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-on Delay Time	$V_{DD} = 30V$, $I_D = 17 A$ $R_G = 4.7\Omega$ $V_{GS} = 10V$ (see test circuit, Figure 3)		11		ns
t_r	Rise Time			50		ns
Q_g	Total Gate Charge	$V_{DD} = 48V$, $I_D = 34 A$, $V_{GS} = 10V$		32	43	nC
Q_{gs}	Gate-Source Charge			6.5		nC
Q_{gd}	Gate-Drain Charge			14.4		nC

SWITCHING OFF

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
$t_{d(off)}$	Turn-Off-Delay Time	$V_{DD} = 30V$, $I_D = 17A$, $R_G = 4.7\Omega$, $V_{GS} = 10V$ (see test circuit, Figure 3)		27		ns
t_f	Fall Time			11		ns

SOURCE DRAIN DIODE

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
$I_{SD} (3)$	Source-drain Current				34	A
$I_{SDM} (2)$	Source-drain Current (pulsed)				136	A
$V_{SD} (1)$	Forward On Voltage	$I_{SD} = 34 A$, $V_{GS} = 0$			1.2	V
t_{rr}	Reverse Recovery Time	$I_{SD} = 34 A$, $di/dt = 100A/\mu s$, $V_{DD} = 10V$, $T_j = 150^\circ C$ (see test circuit, Figure 5)		63		ns
Q_{rr}	Reverse Recovery Charge			151		nC
I_{RRM}	Reverse Recovery Current			4.8		A

Note: 1. Pulsed: Pulse duration = 300 μs , duty cycle 1.5 %.
2. Pulse width limited by safe operating area.
3. Current Limited by Wire Bonding is 20A

Fig. 1: Unclamped Inductive Load Test Circuit




Fig. 2: Unclamped Inductive Waveform




Fig. 3: Switching Times Test Circuit For Resistive Load




Fig. 4: Gate Charge test Circuit






Fig. 5: Test Circuit For Inductive Load Switching And Diode Recovery Times



PowerFLAT™(5x5) MECHANICAL DATA

DIM.	mm.			inch		
	MIN.	TYP	MAX.	MIN.	TYP.	MAX.
A		0.90	1.00		0.035	0.039
A1		0.02	0.05		0.001	0.002
b	0.43	0.51	0.58	0.017	0.020	0.023
c	0.33	0.41	0.48	0.013	0.016	0.019
D		5.00			0.197	
E		5.00			0.197	
E2	3.10	3.18	3.25	0.122	0.125	0.128
e		1.27			0.050	



Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

© The ST logo is a registered trademark of STMicroelectronics

© 2002 STMicroelectronics - Printed in Italy - All Rights Reserved
STMicroelectronics GROUP OF COMPANIES

Australia - Brazil - Canada - China - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco
Singapore - Spain - Sweden - Switzerland - United Kingdom - United States.

© <http://www.st.com>