


Silicon NPN Transistor



Features:

- Low current (maximum 100 mA)
- Low voltage (maximum 45 V)
- NPN transistor in a TO-18 metal package

Applications:

A F silicon epitaxial planar transistor

Absolute Maximum Ratings ($T_a = 25^\circ\text{C}$)

Symbol	Parameter	Value	Unit
V_{CBO}	Collector - base voltage	50	V
V_{CEO}	Collector - emitter voltage	45	V
V_{CES}	Collector - emitter voltage	50	V
V_{EBO}	Emitter - base voltage	6	V
I_C	Collector current - continuous	100	mA
P_C	Collector power dissipation at $T_A = 25^\circ\text{C}$	300	mW
T_J	Junction temperature	175	$^\circ\text{C}$
T_{stg}	Storage temperature range	-55 to 175	$^\circ\text{C}$

Thermal Characteristics

Symbol	Parameter	Maximum	Unit
$R_{th\ j-c}$	Thermal resistance from junction to case	0.2	$^\circ\text{C/W}$

Electrical Characteristics ($T_C = 25^\circ\text{C}$ Unless Otherwise Specified)

Symbol	Parameter	Conditions	Minimum	Typical	Maximum	Unit
$V_{(BR)\ CBO}$	Collector - base breakdown voltage	$I_C = 10\ \mu\text{A}; I_E = 0$	50	-	-	V
$V_{(BR)\ CEO}$	Collector - emitter breakdown voltage	$I_C = 2\ \text{mA}; I_B = 0$	45	-	-	V
$V_{(BR)\ EBO}$	Emitter - base breakdown voltage	$I_E = 10\ \mu\text{A}; I_C = 0$	5	-	-	V
$V_{CE\ (sat)-1}$	Collector - emitter saturation voltage	$I_C = 10\ \text{mA}; I_B = 0.5\ \text{mA}$	-	-	0.25	V
$V_{CE\ (sat)-2}$	Collector - emitter saturation voltage	$I_C = 100\ \text{mA}; I_B = 5\ \text{mA}$	-	-	0.6	V
$V_{BE\ (on)\ 1}$	Base - emitter on voltage	$I_C = 2\ \text{mA}; V_{CE} = 5\ \text{V}$	0.55	-	0.7	V

Silicon NPN Transistor



Electrical Characteristics ($T_C = 25^\circ\text{C}$ Unless Otherwise Specified)

Symbol	Parameter	Conditions	Minimum	Typical	Maximum	Unit
$V_{BE(ON)2}$	Base - emitter on voltage	$I_C = 10\text{ mA}; V_{CE} = 5\text{ V}$	-	-	0.77	V
I_{EBO}	Emitter cut-off current	$I_E = 0; V_{CB} = 20\text{ V}$	-	-	50	nA
I_{CBO}	Collector cut-off current	$V_{CB} = 30\text{ V dc}, I_E = 0$ $V_{CB} = 30\text{ V dc}, I_E = 0, T_J = 150^\circ\text{C}$	-	-	15 15	nA μA
h_{FE1}	DC current gain	$I_C = 10\text{ }\mu\text{A}; V_{CE} = 5\text{ V}$	40	-	150	-
h_{FE2}	DC current gain	$I_C = 2\text{ mA}; V_{CE} = 5\text{ V}$	200	-	450	-
Cobo	Output capacitance	$V_{CB} = 10\text{ V}, I_E = 0, f = 1\text{ MHz}$	-	-	6	pF
NF	Noise figure	$V_{CE} = 5\text{ V}, I_C = 0.2\text{ mA}, R_g = 2\text{ K ohm}$ $F = 1\text{ K Hz B} = 200\text{ HZ}$	-	-	10	dB

Part Number Table

Description	Part Number
Silicon NPN Transistor	BC107

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.