


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1864		Released	JN	03/27/08	JN	03/27/08	JN	03/27/08



RoHS
Compliant



SPC Type No.	Screw Type	Thread	Length (Inches)	Head	
				Dia.	Height
SPC13370	Round Head	2-56	1/4		
SPC13418			1/2	.146	.051
SPC13388			3/4	.162	.061
SPC13389			1		
SPC13390	Flat Head	4-40	1/4		
SPC13391			1/2	.195	.067*
SPC13392			3/4	.225	
SPC13394			1		
SPC13396		6-32	1/4		
SPC13397			1/2	.244	.083*
SPC13399			3/4	.279	
SPC13401			1		
SPC13403		8-32	1/4		
SPC13405			1/2	.292	.100*
SPC13407			3/4	.332	
SPC13409			1		
SPC13381	Binder Head	10-32	1/4	.340	.116*
SPC13387			3/4	.385	
SPC13377			1		
SPC13371		2-56	1/2	.171	.043
SPC13384			3/4	.181	.050
SPC13372			1/4		
SPC13373		4-40	1/2	.223	.061
SPC13374			3/4	.235	.068
SPC13393			1		
SPC13395		6-32	1/4		
SPC13375			1/2	.275	.078
SPC13398			3/4	.290	.087
SPC13400			1		
SPC13402		8-32	1/4		
SPC13404			1/2	.326	.095
SPC13406			3/4	.344	.105
SPC13408			1		
SPC13382		10-32	1/4		
SPC13386			1/2	.379	.112
SPC13383			3/4	.399	.123
SPC13376			1		

SPC-F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:			
	Jason Nash	03/27/08	Round Head, Flat Head and Binder Head Screws			
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
	Jason Nash	03/27/08	A	TA-854	TA-854.dwg	A
	APPROVED BY:	DATE:	SCALE: NTS		U.O.M.: INCHES [mm]	SHEET: 1 OF 1
	Jason Nash	03/27/08				

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.