




Features:

- Low profile package.
- Built-in strain relief.
- Glass passivated junction.
- Low inductance.
- Typical I_R less than 5.0 μ A above 11V.
- High temperature soldering guaranteed: 260°C/10 seconds at terminals
- Plastic package has underwriters laboratory flammability classification 94V-0

DO-41



Mechanical Data

Case	: Moulded plastic DO-41.
Lead	: Pure tin plated lead free, solderable per MIL-STD-202, Method 2025.
Polarity	: Color band denotes cathode end.
Mounting position	: Any.
Weight	: 0.012 ounces, 0.3 gram.

1N47- Series



Maximum Ratings and Electrical Characteristics

Rating at 25°C Ambient Temperature Unless Otherwise Specified.

Type Number	Symbol	Value	Units
Peak Power Dissipation at $T_A = 50^\circ\text{C}$, Derate above 50°C (Note 1)	P_D	1.0 6.67	Watts mW/°C
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method) (Note 2)	I_{FSM}	10.0	Amps
Operating and Storage Temperature Range	T_J, T_{STG}	-55 to +150	°C

- Notes : 1. Mounted on 5.0mm² (0.013mm thick) land areas.
 2. Measured on 8.3ms single half sine-wave or equivalent square wave,
 duty cycle = 4 pulses per minute maximum.

Electrical Characteristics ($T_A = 25^\circ\text{C}$ Unless Otherwise Noted)

$V_F = 1.2\text{V}$ maximum, $I_F = 200\text{mA}$ for all types.


Power (Watt)	Zener Voltage V _Z at I _{ZT} Voltage			Test Current I _{ZT} mA	Maximum Zener Impedance (Note 4)		Leakage Current		Surge Current at T _A = 25°C I _r = mA (Note 5)	Part Number	
	Nom.				Z _{ZT} at I _{ZT} Ohms	Z _{ZK} at I _{ZK}	I _R @ V _R				
	(Notes 2 & 3)	Minimum	Maximum			Ohms	mA	uA Maximum	Volts		
1	12	11.40	12.60	21	9	700	0.25	5.0	9.1	380	1N4742A
	13	12.35	13.65	19	10				9.9	344	1N4743A
	15	14.25	15.75	17	14				11.4	3.4	1N4744A
	16	15.20	16.80	15.5	16				12.2	285	1N4745A
	18	17.10	18.90	14.0	20	750			13.7	250	1N4746A
	20	19.00	21.00	12.5	22				15.2	225	1N4747A
	22	20.90	23.10	11.5	23				16.7	205	1N4748A
	24	22.80	25.20	10.5	25				18.2	190	1N4749A
	27	25.65	28.35	9.5	35	1000			20.6	170	1N4750A
	30	28.50	31.50	8.5	40				22.8	150	1N4751A
	33	31.35	34.65	7.5	45				25.1	135	1N4752A
	36	34.20	37.80	7.0	50				27.4	125	1N4753A
	47	44.65	49.35	5.5	80	1500			35.8	95	1N4756A
	51	48.45	53.55	5.0	95				38.8	90	1N4757A
	56	53.20	58.80	4.5	110	2000			42.6	80	1N4758A
	68	64.60	71.40	3.7	150				51.7	65	1N4760A
	75	71.25	78.75	3.3	175				56.0	60	1N4761A
	100	95.00	105.0	2.5	350				3000	76.0	45




- Notes
- 1: Tolerance and Type Number Designation. The type numbers listed have a standard tolerance on the nominal zener voltage of $\pm 5\%$.
 - 2: Specials Available Include:
 - A. Nominal zener voltages between the voltages shown and tighter voltage tolerances.
 - B. Matched sets.
 - 3: Zener Voltage (VZ) Measurement. Guarantees the zener voltage when measured at 90 seconds while maintaining the lead temperature (TL) at $30\text{C} \pm 1\text{C}$, from the diode body.
 - 4: Zener Impedance (ZZ) Derivation. The zener impedance is derived from the 60 cycle ac voltage, which results when an ac current having an rms value equal to 10% of the dc zener current (IZT or IZK) is superimposed on IZT or IZK.
 - 5: Surge Current (Ir) Non-Repetitive. The rating listed in the electrical characteristics table is maximum peak, non-repetitive, reverse surge current of 1/2 square wave or equivalent sine wave pulse of 1/120 second duration superimposed on the test current, IZT, per JEDEC registration; however, actual device capability is as described.

Ratings and Characteristics Curves (1N4742A thru 1N4753A, 1N4756A thru 1N4758A, 1N4760A, 1N4761A and 1N4764A


Power Temperature Derating Curve




Typical Forward Characteristics




Effect of Zener Current on Zener Impedance




Effect of Zener Voltage on Zener Impedance



Typical Leakage Current




Typical Capacitance verses V_Z




Temperature Coefficients

a - Range for Units to 12 Volts




Temperature Coefficients


b - Range for Units to 12 to 100 Volts




Effect of Zener Current



Typical Thermal Resistance versus Lead Length



Maximum Surge Power



1N47- Series



Notes:

International Sales Offices:



AUSTRALIA - Farnell

Tel No: ++61 1300 361 005
Fax No: ++61 1300 361 225



FINLAND - Farnell

Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



ITALY - Farnell

Tel No: ++ 39 02 93 995 200
Fax No: ++ 39 02 93 995 300



SPAIN - Farnell

Tel No: 901 20 20 80
Fax No: 901 20 20 90



AUSTRIA - Farnell

Tel No: ++ 43 662 2180 680
Fax No: ++ 43 662 2180 670



FRANCE - Farnell

Tel No: ++ 33 474 68 99 99
Fax No: ++ 33 474 68 99 90



MALAYSIA - Farnell-Newark

Tel No: ++ 60 3 7873 8000
Fax No: ++ 60 3 7873 7000



SWEDEN - Farnell

Tel No: ++ 46 8 730 50 00
Fax No: ++ 46 8 83 52 62



BELGIUM - Farnell

Tel No: ++ 32 3 475 2810
Fax No: ++ 32 3 227 3648



GERMANY - Farnell

Tel No: ++ 49 89 61 39 39 39
Fax No: ++ 49 89 613 59 01



NETHERLANDS - Farnell

Tel No: ++ 31 30 241 7373
Fax No: ++ 31 30 241 7333



SWITZERLAND - Farnell

Tel No: ++ 44 204 64 64
Fax No: ++ 44 204 64 54



BRAZIL - Farnell-Newark

Tel No: ++ 55 11 4066 9400
Fax No: ++ 55 11 4066 9410



HONG KONG - Farnell-Newark

Tel No: ++ 852 2268 9888
Fax No: ++ 852 2268 9899



NEW ZEALAND - Farnell

Tel No: 0800 90 80 80
Fax No: 0800 90 80 81



UK - Farnell

Tel No: ++ 44 8701 200 200
Fax No: ++ 44 8701 200 201



CHINA - Farnell-Newark

Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



HUNGARY - Farnell

Tel No: ++ 44 870 1200 208
Fax No: ++ 44 870 1200 209



NORWAY - Farnell

Tel No: 800 146 70
Fax No: 800 146 76



UK - CPC

++ 44 8701 202 530
++ 44 8701 202 531



CZECH REPUBLIC - Farnell

Tel No: ++ 44 870 1200 208
Fax No: ++ 44 870 1200 209



INDIA - Farnell

Tel No: ++ 44 870 1200 208
Fax No: ++ 44 870 1200 209



PORTUGAL - Farnell

Tel No: ++ 34 93 475 8804
Fax No: ++ 34 93 474 5288



USA - Newark

Tel No: 800 463 9275



DENMARK - Farnell

Tel No: ++ 45 44 53 66 44
Fax No: ++ 45 44 53 66 06



IRELAND - Farnell

Tel No: ++ 353 1 830 9277
Fax No: ++ 353 1 830 9016



RUSSIA - Farnell

Tel No: ++ 44 870 1200 208
Fax No: ++ 44 870 1200 209



EXPORT - Farnell

Tel No: ++ 44 8701 200 208
Fax No: ++ 44 8701 200 209

For enquiries from all other markets



ESTONIA - Farnell

Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



ISRAEL - Farnell

Tel No: ++ 180 937 0015
Fax No: ++ 180 937 0014



SINGAPORE - Farnell-Newark

Tel No: ++ 65 6788 0200
Fax No: ++ 65 6788 0300

<http://www.farnell.com>
<http://www.newark.com>
<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2008.

