

FEATURES

- High speed
- Low capacitance
- Blue enhanced
- Low dark current

DESCRIPTION

The **PDB-C115** is a silicon, PIN planar diffused, blue enhanced photodiode. Ideal for high speed photoconductive applications. Packaged in a hermetic TO-5 metal can with a flat window.

APPLICATIONS


- Instrumentation
- Oximeters
- Laser sensor
- Medical sensor

ABSOLUTE MAXIMUM RATING (TA=25°C unless otherwise noted)

SYMBOL	PARAMETER	MIN	MAX	UNITS
V_{BR}	Reverse Voltage		100	V
T_{STG}	Storage Temperature	-55	+150	°C
T_O	Operating Temperature Range	-40	+125	°C
T_S	Soldering Temperature*		+240	°C
I_L	Light Current		1.0	mA

*1/16 inch from case for 3 secs max

SPECTRAL RESPONSE



ELECTRO-OPTICAL CHARACTERISTICS (TA=25°C unless otherwise noted)

SYMBOL	CHARACTERISTIC	TEST CONDITIONS	MIN	TYP	MAX	UNITS
I_{SC}	Short Circuit Current	$H = 100 \text{ fc}$, 2850 K	45	65		μA
I_D	Dark Current	$H = 0$, $V_R = 10 \text{ V}$		1.0	5.0	nA
R_{SH}	Shunt Resistance	$H = 0$, $V_R = 10 \text{ mV}$.5	2		$\text{G}\Omega$
TCR_{SH}	RSH Temp. Coefficient	$H = 0$, $V_R = 10 \text{ mV}$		-8		% / °C
C_J	Junction Capacitance	$H = 0$, $V_R = 10 \text{ V}^{**}$		15		pF
λ_{range}	Spectral Application Range	Spot Scan	350		1100	nm
λ_p	Spectral Response - Peak	Spot Scan		950		nm
V_{BR}	Breakdown Voltage	$I = 10 \mu\text{A}$	100	125		V
NEP	Noise Equivalent Power	$V_R = 10 \text{ V @ Peak}$		2.5×10^{-14}		$\text{W} / \sqrt{\text{Hz}}$
tr	Response Time	$RL = 1 \text{ K}\Omega$, $V_R = 50 \text{ V}$		15		nS

Information in this technical data sheet is believed to be correct and reliable. However, no responsibility is assumed for possible inaccuracies or omission. Specifications are subject to change without notice. **f = 1 MHz