

## *TABLE of CONTENTS*

### **ISOLATION TRANSFORMERS**

#### **10BASE-T**

|                                                                 |   |
|-----------------------------------------------------------------|---|
| Electrical Specifications: Surface Mount and Through Hole ..... | 2 |
|-----------------------------------------------------------------|---|

#### **ETHERNET**

|                                                                 |   |
|-----------------------------------------------------------------|---|
| Electrical Specifications: Surface Mount and Through Hole ..... | 3 |
|-----------------------------------------------------------------|---|

#### **APPLICATION CIRCUITS**

|                |   |
|----------------|---|
| 10Base-T ..... | 4 |
| Ethernet ..... | 5 |


|                         |   |
|-------------------------|---|
| <b>SCHEMATICS</b> ..... | 6 |
|-------------------------|---|

#### **MECHANICALS**

|                     |    |
|---------------------|----|
| Surface Mount ..... | 8  |
| Through Hole .....  | 10 |

# ISOLATION TRANSFORMERS FOR 10BASE-T

For Adapter Cards, MAUs, Hubs,  
and Motherboard Applications



- Designed to meet or exceed IEEE 802.3, 10Base-T specifications
- Available with common mode chokes for EMI suppression
- Surface mount, IC grade, transfer-molded package withstands 235°C peak temperature profile
- Through hole, auto-insertable, 16-pin DIP package

## Electrical Specifications @ 25°C — Operating Temperature 0°C to 70°C


| Part Number                | Turns Ratio (±5%) |          | Primary Pins       | Common Mode Choke | Sine Wave Inductance OCL <sup>1</sup> (μH MIN) | Interwinding Capacitance C <sub>ww</sub> <sup>1</sup> (pF MAX) | Leakage Inductance L <sub>L</sub> <sup>1</sup> (μH MAX) | DCR (Ω MAX) | Hi-Pot (Vrms) | Schem.    | Mech.     |
|----------------------------|-------------------|----------|--------------------|-------------------|------------------------------------------------|----------------------------------------------------------------|---------------------------------------------------------|-------------|---------------|-----------|-----------|
|                            | Transmit          | Receive  |                    |                   |                                                |                                                                |                                                         |             |               |           |           |
| SURFACE MOUNT <sup>2</sup> |                   |          |                    |                   |                                                |                                                                |                                                         |             |               | pages 6-7 | pages 8-9 |
| PE-65454                   | 1:1.414           | 1:1      | 3-4/1-2            |                   | 140                                            | 12                                                             | 0.2                                                     | 0.4         | 2000          | T1        | SMT2      |
| E5017                      | 1CT:1CT           | 1CT:1CT  | 1-3/6-8            | X                 | 200                                            | 10                                                             | 0.25                                                    | 1.0         | 1500          | T6        | SMT4      |
| PE-65726                   | 1CT:1CT           | 1CT:1CT  | 1-3/6-8            |                   | 200                                            | 10                                                             | 0.2                                                     | 0.3         | 2000          | T4        | SMT4      |
| 23Z114SM                   | 1CT:1CT           | 1CT:1CT  | 1-3/6-8            |                   | 200                                            | 12                                                             | 0.3                                                     | 0.3         | 2000          | T4        | SMT5      |
| PE-68048                   | 1CT: 1.414CT      | 1CT:1CT  | 6-8/1-3            | X                 | 110                                            | 15                                                             | 0.4                                                     | 1.0         | 1500          | T5        | SMT4      |
| PE-65745                   | 1CT: 1.414CT      | 1CT:1CT  | 6-8/1-3            |                   | 140                                            | 12                                                             | 0.2                                                     | 0.3         | 2000          | T4        | SMT4      |
| 23Z128SM                   | 1CT:1.414CT       | 1CT:1CT  | 6-8/1-3            |                   | 200                                            | 15                                                             | 0.5                                                     | 0.4         | 2000          | T4        | SMT5      |
| E2023                      | 1CT: 2.5CT        | 1CT: 1CT | 6-8/1-3            | X                 | 200                                            | 15                                                             | 0.5                                                     | 0.4         | 2000          | T10       | SMT4      |
| E4005                      | 1CT: 2.5CT        | 1CT: 1CT | 6-8/1-3            | X                 | 200                                            | 10                                                             | 0.4                                                     | 0.5         | 1500          | T10       | SMT4      |
| EX2024 <sup>3</sup>        | 1CT: 2.5CT        | 1CT:1CT  | 6-8/1-3            | X                 | 350                                            | 30                                                             | 0.8                                                     | 0.6         | 2000          | T10       | SMT4      |
| 23Z356SM                   | 1CT:1.414CT       | 1CT:1CT  | 6-8/1-3            | X                 | 200                                            | 12                                                             | 0.5                                                     | 0.6         | 2000          | T7        | SMT5      |
| 23Z435SM                   | 2CT:1CT           | 1CT:1CT  | 1-3/6-8            |                   | 100                                            | 10                                                             | 0.4                                                     | 0.5         | 2000          | T4        | SMT5      |
| PE-68052                   | 2CT:1CT           | 1CT:1CT  | 1-3/6-8            | X                 | 140                                            | 12                                                             | 0.3                                                     | 1.0         | 1500          | T6        | SMT4      |
| E4001                      | 1CT:2CT           | 1CT:1CT  | 6-8/1-3            | X                 | 112                                            | 8                                                              | 0.3                                                     | 0.8         | 3000          | T5        | SMT4      |
| PE-68041                   | 1CT:2CT           | 1CT:1CT  | 6-8/1-3            |                   | 112                                            | 8                                                              | 0.3                                                     | 0.5         | 1500          | T4        | SMT4      |
| 23Z467SM                   | 1CT:2CT           | 1CT:1CT  | 6-8/1-3            | X                 | 140                                            | 12                                                             | 0.2                                                     | 0.6         | 2000          | T7        | SMT5      |
| PE-68023                   | 1CT:2CT           | 1CT:1CT  | 1-3/6-8            | X                 | 200                                            | 12                                                             | 0.3                                                     | 1.0         | 1500          | T6        | SMT4      |
| PE-68042                   | 2.828CT:1         | 1:1      | 2-4/7-9            |                   | 200                                            | 14                                                             | 1                                                       | 0.5         | 1500          | T9        | SMT1      |
| PE-68810                   | —                 | 1:1 (4X) | 1-2/3-4            |                   | 140                                            | 12                                                             | 0.2                                                     | 0.4         | 2000          | T3        | SMT4      |
| PE-68820                   | 1:1.414 (4X)      | —        | 1-2/3-4<br>5-6/7-8 |                   | 140                                            | 12                                                             | 0.2                                                     | 0.4         | 2000          | T3        | SMT4      |
| THROUGH HOLE               |                   |          |                    |                   |                                                |                                                                |                                                         |             |               | pages 6-7 | page 10   |
| 23Z435                     | 2CT:1CT           | 1CT:1CT  | 1-3/6-8            |                   | 80                                             | 10                                                             | 0.4                                                     | 0.5         | 2000          | T4        | TH3       |
| 23Z128                     | 1CT: 2CT          | 1CT:1CT  | 6-8/1-3            |                   | 140                                            | 15                                                             | 0.5                                                     | 0.4         | 2000          | T4        | TH3       |
| PE-65263                   | 1CT:1CT           | 1CT:1CT  | 1-3/6-8            |                   | 200                                            | 15                                                             | 0.25                                                    | 0.3         | 2000          | T4        | TH4       |

### NOTES:

- OCL, C<sub>ww</sub> and L<sub>L</sub> are measured at 20 mVrms, 100 kHz.
- To order Tape & Reel packaging for surface mount parts, add the suffix "T" to the part number. Example: PE-65454T. The "T" will appear on all paper work, but will not be marked on parts.
- Part numbers denoted "EX" are extended temperature parts -40°C to 85°C, electrical specifications @ 25°C.

# ISOLATION TRANSFORMERS FOR ETHERNET

## AUI Transformers



- Low leakage inductance and coupling capacitance for faster rise times
- Small form factor, 50 mil lead spacing
- Through hole, auto-insertable, 16-pin DIP package


### Electrical Specifications @ 25°C — Operating Temperature 0°C to 70°C

| Part Number                | Turns Ratio (±5%) | Primary Pins | Primary Sine Wave OCL <sup>1</sup> (μH ±20%) | Primary ET-Constant (V-μs MIN) | Rise Time <sup>2</sup> (ns MAX) | Interwinding Capacitance C <sub>ww</sub> <sup>1</sup> (pF MAX) | Leakage Inductance L <sub>L</sub> <sup>1</sup> (μH MAX) | DCR (Ω MAX) | Schem.    | Mech.     | Hipot (Vrms) |
|----------------------------|-------------------|--------------|----------------------------------------------|--------------------------------|---------------------------------|----------------------------------------------------------------|---------------------------------------------------------|-------------|-----------|-----------|--------------|
| SURFACE MOUNT <sup>3</sup> |                   |              |                                              |                                |                                 |                                                                |                                                         |             | pages 6-7 | pages 8-9 |              |
| E6002                      | 1:1               | 1-2/4-5/7-8  | 40 (MIN)                                     | 2.1                            | 3.0                             | 8                                                              | 0.20                                                    | 0.25        | T2        | SMT4      | 2000         |
| PE-65723                   | 1:1               | 1-2/4-5/7-8  | 75                                           | 1.8                            | 3.0                             | 8                                                              | 0.20                                                    | 0.30        | T2        | SMT4      | 2000         |
| PE-68801                   | 1:1               | 1-2/3-4/5-6  | 75                                           | 1.8                            | 3.0                             | 12                                                             | 0.20                                                    | 0.30        | T8        | SMT3      | 2000         |
| 23Z90SM                    | 1:1               | 1-2/4-5/7-8  | 75                                           | 2.4                            | 3.0                             | 10                                                             | 0.20                                                    | 0.20        | T2        | SMT5      | 2000         |
| PE-65728                   | 1:1               | 1-2/4-5/7-8  | 100                                          | 1.8                            | 3.0                             | 9                                                              | 0.20                                                    | 0.30        | T2        | SMT4      | 2000         |
| 23Z91SM                    | 1:1               | 1-2/4-5/7-8  | 100                                          | 2.4                            | 3.0                             | 10                                                             | 0.20                                                    | 0.30        | T2        | SMT5      | 2000         |
| PE-65727                   | 1:1               | 1-2/4-5/7-8  | 150                                          | 1.2                            | 3.0                             | 12                                                             | 0.20                                                    | 0.30        | T2        | SMT4      | 2000         |
| PE-65733                   | 1:1               | 1-2/4-5/7-8  | 350                                          | 2.6                            | 3.5                             | 16                                                             | 0.30                                                    | 0.35        | T2        | SMT4      | 2000         |
| 23Z108SM                   | 1:1               | 1-2/4-5/7-8  | 350                                          | 2.5                            | 3.5                             | 16                                                             | 0.30                                                    | 0.35        | T2        | SMT5      | 2000         |
| THROUGH HOLE               |                   |              |                                              |                                |                                 |                                                                |                                                         |             | pages 6-7 | page 10   |              |
| PE-64102                   | 1:1               | 1-2/4-5/7-8  | 75                                           | 2.1                            | 3.0                             | 10                                                             | 0.20                                                    | 0.20        | T2        | TH4       | 500          |
| PE-64107                   | 1:1               | 1-2/4-5/7-8  | 75                                           | 2.4                            | 3.5                             | 10                                                             | 0.25                                                    | 0.30        | T2        | TH2       | 2000         |
| PE-64502                   | 1:1               | 1-2/4-5/7-8  | 75                                           | 2.1                            | 3.0                             | 10                                                             | 0.20                                                    | 0.20        | T2        | TH4       | 2000         |
| PE-64103                   | 1:1               | 1-2/4-5/7-8  | 100                                          | 2.1                            | 3.0                             | 10                                                             | 0.20                                                    | 0.30        | T2        | TH4       | 500          |
| PE-64108                   | 1:1               | 1-2/4-5/7-8  | 100                                          | 2.1                            | 3.5                             | 10                                                             | 0.25                                                    | 0.40        | T2        | TH2       | 2000         |
| PE-64503                   | 1:1               | 1-2/4-5/7-8  | 100                                          | 2.1                            | 3.0                             | 10                                                             | 0.20                                                    | 0.30        | T2        | TH4       | 2000         |
| PE-64104                   | 1:1               | 1-2/4-5/7-8  | 150                                          | 2.1                            | 3.5                             | 12                                                             | 0.20                                                    | 0.30        | T2        | TH4       | 500          |
| PE-64109                   | 1:1               | 1-2/4-5/7-8  | 150                                          | 3.0                            | 3.0                             | 15                                                             | 0.20                                                    | 0.45        | T2        | TH2       | 2000         |

#### NOTES:

- OCL, C<sub>ww</sub> and L<sub>L</sub> are measured at 20 mVrms, 100 kHz.
- Rise time is measured in 75 Ω systems.
- To order Tape & Reel packaging for surface mount parts, add the suffix "T" to the part number.  
Example: PE-65723T. The "T" will appear on all paper work, but will not be marked on parts.


## Typical Application Circuit




### NOTES:

1. Connections at pins 12 and 13 apply to PE-68023 only. These are test points. **Do not ground.**
2. For specific information, see pages 2 and 3 in this catalog.
3. For specific connection, refer to National's Application Notes.

## Typical 10Base-T Application Circuit




## Schematics




Schematics (continued)


T7




T8



T9




T10





## Surface Mount Mechanicals


### SMT1




**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$   
 Unless otherwise specified,  
 all tolerances are  $\pm .010$   
 0,25

**Weight** ..... 1.15 grams  
**Tube** ..... .25/tube  
**Tape & Reel** ..... .350/reel

### SMT2



### SMT3



**Weight** ..... 0.22 grams  
**Tube** ..... .60/tube  
**Tape & Reel** ..... .1500/reel

**Dimensions:**  $\frac{\text{Inches}}{\text{mm}}$  Unless otherwise specified, all tolerances are  $\pm .010$   
 0,25

**Weight** ..... 0.28 grams  
**Tube** ..... .35/tube  
**Tape & Reel** ..... .1500/reel




## SMT4

[illegible]

Unless otherwise specified, all tolerances are  $\pm \frac{.010}{0.25}$

**Tape & Reel . . . . .900/reel**

## SMT5



Unless otherwise specified, all tolerances are  $\pm \frac{.005}{0.13}$


**Tape & Reel . . . . .750/reel**

# ISOLATION TRANSFORMERS



## Through Hole Mechanicals

### TH1




Dimensions:  $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified, all tolerances are  $\pm \frac{.010}{0,25}$

Weight ..... 2.17 grams

Tube ..... .20/tube

### TH2




Dimensions:  $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified, all tolerances are  $\pm \frac{.010}{0,25}$


Weight ..... 2.18 grams

Tube ..... .20/tube

### TH3



### TH4



Dimensions:  $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified, all tolerances are  $\pm \frac{.005}{0,13}$

Weight ..... 1.7 grams

Tube ..... .28/tube

Dimensions:  $\frac{\text{Inches}}{\text{mm}}$  Unless otherwise specified, all tolerances are  $\pm \frac{.010}{0,25}$

## For More Information :

### UNITED STATES (Worldwide)

12220 World Trade Drive  
San Diego, CA 92128  
U.S.A.  
<http://www.pulseeng.com>  
TEL: 858 674 8100  
FAX: 858 674 8262

### UNITED KINGDOM (Northern Europe)

1 & 2 Huxley Road  
The Surrey Research Park  
Guildford, Surrey GU2 5RE  
United Kingdom  
TEL: 44 1483 401700  
FAX: 44 1483 401701

### FRANCE (Southern Europe)

Zone Industrielle  
F-39270  
Orgelet  
France  
TEL: 33 3 84 35 04 04  
FAX: 33 3 84 25 46 41

### SINGAPORE (Southern Asia)

150 Kampong Ampat  
#07-01/02  
KA Centre  
Singapore 368324  
TEL: 65 287 8998  
FAX: 65 280 0080

### TAIWAN, R.O.C. (Northern Asia)

3F-4, No. 81, Sec. 1  
HsinTai Wu Road  
Hsi-Chih, Taipei Hsien  
Taiwan, R.O.C.  
Tel: 886 2 2698 0228  
FAX: 886 2 2698 0948

### HONG KONG (Great China)

19/F, China United Plaza  
1008 Tai Nan West Street  
Cheung Sha Wan, Kowloon  
Hong Kong, China  
Tel: 852 2788 6588  
FAX: 852 2776 1055

### DISTRIBUTOR

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.

Printed on recycled paper. ©2002, Pulse Engineering, Inc.