




MDT2012-CLH



Recommended patterns
推荐焊盘尺寸



FEATURES 特点

- Miniature size: 2012 footprint (2.0mm × 1.2mm) and an extremely low profile (0.55mm Max. Height)
- Magnetically shielded
- Ideal for a variety of DC-DC converter Inductor application (DVC, DSC, Cellular phone, PDA)
- Operating temperature: -40 ~ +85°C
- RoHS compliant
- 小型薄型 (2.0mm × 1.2mm、高度0.55mm max)
- 磁性屏蔽结构
- 是适用于 (DVC、DSC、Cellular phone、PDA) 各种设备的DC-DC转换器电感器的理想选择
- 工作温度范围: -40 ~ +85°C
- 符合RoHS指令

STANDARD PART NUMBERS 标准零件号

TYPE MDT2012-CLH, (Quantity/reel; 5,000 PCS)

零件号码	电感值 ⁽¹⁾	公差	直流电阻 ⁽²⁾	温度上升电流 ⁽³⁾
Part Number	Inductance ⁽¹⁾ (μH) at 1MHz	Tolerance (%)	DC Resistance ⁽²⁾ (mΩ) ±30%	Temperature Rise Current ⁽³⁾ ΔT=40°C (A) Max.
MDT2012-CLHR47M	0.47	±20	130	1.70
MDT2012-CLH1R0M	1.0	±20	190	1.45

- (1) Inductance is measured with a |Z| Analyzer 4291A/ B (Agilent Technologies) or equivalent. Test frequency at 1MHz, 0.5V
 (2) DC Resistance is measured with a milliohm meter 4338B (Agilent Technologies) or equivalent.
 (3) Maximum allowable DC current is that causes coil temperature to rise by 40°C. (The ambient reference temperature: 20°C)

- (1) 电感值由阻抗分析器4291A/ B(Agilent技术)或等效物测试。测试频率为1MHz, 0.5V。
 (2) 直流电阻由毫欧计4338B(Agilent技术)或等效物测试。
 (3) 最大容许电流是通电情况下线圈温度上升达到40°C时的电流值。(环境温度: 20°C)

EXAMPLES OF CHARACTERISTICS 特性范例

