


## Features

- AVR® - High-performance and Low-power RISC Architecture
  - 118 Powerful Instructions - Most Single Clock Cycle Execution
  - 32 x 8 General Purpose Working Registers
  - Up to 8 MIPS Throughput at 8 MHz
- Data and Nonvolatile Program Memories
  - 4K/8K Bytes of In-System Programmable Flash
    - SPI Serial Interface for In-System Programming
    - Endurance: 1,000 Write/Erase Cycles
  - 256/512 Bytes EEPROM
    - Endurance: 100,000 Write/Erase Cycles
  - 256/512 Bytes Internal SRAM
  - Programming Lock for Software Security
- Peripheral Features
  - 8-channel, 10-bit ADC
  - Programmable UART
  - Two 8-bit Timer/Counters with Separate Prescaler and Compare Mode
  - One 16-bit Timer/Counter with Separate Prescaler, Compare and Capture Modes, and dual 8-, 9-, or 10-bit PWM
  - Programmable Watchdog Timer with On-chip Oscillator
  - On-chip Analog Comparator
- Special Microcontroller Features
  - Power-on Reset Circuit
  - Real Time Clock (RTC) with Separate Oscillator and Counter Mode
  - External and Internal Interrupt Sources
  - Three Sleep Modes: Idle, Power Save, and Power Down
- Power Consumption at 4 MHz, 3V, 20°C
  - Active: 6.4 mA
  - Idle Mode: 1.9 mA
  - Power Down Mode: <1  $\mu$ A
- I/O and Packages
  - 32 Programmable I/O Lines
  - 40-pin PDIP, 44-pin PLCC and 44-pin TQFP
- Operating Voltages
  - $V_{CC}$ : 4.0 - 6.0V AT90S4434/AT90S8535
  - $V_{CC}$ : 2.7 - 6.0V AT90LS4434/AT90LS8535
- Speed Grades:
  - 0 - 8 MHz AT90S4434/AT90S8535
  - 0 - 4 MHz AT90LS4434/AT90LS8535

## Pin Configurations



# 8-bit AVR® Microcontroller with 4K/8K Bytes In-System Programmable Flash

**AT90S4434**  
**AT90LS4434**  
**AT90S8535**  
**AT90LS8535**

## Preliminary




## Description

The AT90S4434/8535 is a low-power CMOS 8-bit microcontroller based on the AVR RISC architecture. By executing powerful instructions in a single clock cycle, the AT90S4434/8535 achieves throughputs approaching 1 MIPS per MHz allowing the system designer to optimize power consumption versus processing speed.

## Block Diagram

Figure 1. The AT90S4434/8535 Block Diagram



The AVR core combines a rich instruction set with 32 general purpose working registers. All the 32 registers are directly connected to the Arithmetic Logic Unit (ALU), allowing two independent registers to be accessed in one single instruction executed in one clock cycle. The resulting architecture is more code efficient while achieving throughputs up to ten times faster than conventional CISC microcontrollers.

The AT90S4434/8535 provides the following features: 4K/8K bytes of In-System Programmable Flash, 256/512 bytes EEPROM, 256/512 bytes SRAM, 32 general purpose I/O lines, 32 general purpose working registers, Real Time Clock (RTC), three flexible timer/counters with compare modes, internal and external interrupts, a programmable serial UART, 8-channel, 10-bit ADC, programmable Watchdog Timer with internal oscillator, an SPI serial port, and three software selectable power saving modes. The Idle mode stops the CPU while allowing the SRAM, timer/counters, SPI port, and interrupt system to continue functioning. The Power Down mode saves the register contents but freezes the oscillator, disabling all other chip functions until the next interrupt or hardware reset. In Power Save mode, the timer oscillator continues to run, allowing the user to maintain a timer base while the rest of the device is sleeping.

The device is manufactured using Atmel's high density nonvolatile memory technology. The on-chip ISP Flash allows the program memory to be reprogrammed in-system through an SPI serial interface or by a conventional nonvolatile memory programmer. By combining an 8-bit RISC CPU with In-System Programmable Flash on a monolithic chip, the Atmel AT90S4434/8535 is a powerful microcontroller that provides a highly flexible and cost effective solution to many embedded control applications.

The AT90S4434/8535 AVR is supported with a full suite of program and system development tools including: C compilers, macro assemblers, program debugger/simulators, in-circuit emulators, and evaluation kits.

## Comparison between AT90S4434 and AT90S8535

The AT90S4434 has 4K bytes of In-System Programmable Flash, 256 bytes of EEPROM, and 256 bytes of internal SRAM. The AT90S8535 has 8K bytes of In-System Programmable Flash, 512 bytes of EEPROM, and 512 bytes of internal SRAM. Table 1 summarizes the different memory sizes for the two devices.

**Table 1.** Memory Size Summary

| Part      | Flash    | EEPROM    | SRAM      |
|-----------|----------|-----------|-----------|
| AT90S4434 | 4K bytes | 256 bytes | 256 bytes |
| AT90S8535 | 8K bytes | 512 bytes | 512 bytes |

## Pin Descriptions

### VCC

Digital supply voltage

### GND

Digital ground

### Port A (PA7..PA0)

Port A is an 8-bit bi-directional I/O port. Port pins can provide internal pull-up resistors (selected for each bit). The Port A output buffers can sink 20mA and can drive LED displays directly. When pins PA0 to PA7 are used as inputs and are externally pulled low, they will source current if the internal pull-up resistors are activated.

Port A also serves as the analog inputs to the A/D Converter.

The Port A pins are tristated when a reset condition becomes active, even if the clock is not running.

### Port B (PB7..PB0)

Port B is an 8-bit bi-directional I/O port with internal pull-up resistors. The Port B output buffers can sink 20 mA. As inputs, Port B pins that are externally pulled low will source current if the pull-up resistors are activated. Port B also serves the functions of various special features of the AT90S4434/8535 as listed on page 68.

The Port B pins are tristated when a reset condition becomes active, even if the clock is not running.

#### **Port C (PC7..PC0)**

Port C is an 8-bit bi-directional I/O port with internal pullup resistors. The Port C output buffers can sink 20 mA. As inputs, Port C pins that are externally pulled low will source current if the pull-up resistors are activated. Two Port C pins can alternatively be used as oscillator for Timer/Counter2.

The port C pins are tristated when a reset condition becomes active, even if the clock is not running.

#### **Port D (PD7..PD0)**

Port D is an 8-bit bidirectional I/O port with internal pull-up resistors. The Port D output buffers can sink 20 mA. As inputs, Port D pins that are externally pulled low will source current if the pull-up resistors are activated.

Port D also serves the functions of various special features of the AT90S4434/8535 as listed on page 76.

The port D pins are tristated when a reset condition becomes active, even if the clock is not running.

#### **RESET**

Reset input. An external reset is generated by a low level on the RESET pin. Reset pulses longer than 50 ns will generate a reset, even if the clock is not running. Shorter pulses are not guaranteed to generate a reset.

#### **XTAL1**

Input to the inverting oscillator amplifier and input to the internal clock operating circuit.

#### **XTAL2**

Output from the inverting oscillator amplifier

#### **AVCC**

This is the supply voltage pin for the A/D Converter. It should be externally connected to  $V_{CC}$  via a low-pass filter. See page 59 for details on operation of the ADC.

#### **AREF**

This is the analog reference input for the A/D Converter. For ADC operations, a voltage in the range AGND to  $AV_{CC}$  must be applied to this pin.

#### **AGND**


Analog ground. If the board has a separate analog ground plane, this pin should be connected to this ground plane. Otherwise, connect to GND.

## Architectural Overview

The fast-access register file concept contains 32 x 8-bit general purpose working registers with a single clock cycle access time. This means that during one single clock cycle, one Arithmetic Logic Unit (ALU) operation is executed. Two operands are output from the register file, the operation is executed, and the result is stored back in the register file - in one clock cycle.

Six of the 32 registers can be used as three 16-bits indirect address register pointers for Data Space addressing - enabling efficient address calculations. One of the three address pointers is also used as the address pointer for the constant table look up function. These added function registers are the 16-bits X-register, Y-register and Z-register.

**Figure 2.** The AT90S4434/8535 AVR RISC Architecture



The ALU supports arithmetic and logic functions between registers or between a constant and a register. Single register operations are also executed in the ALU. Figure 2 shows the AT90S4434/8535 AVR RISC microcontroller architecture.

In addition to the register operation, the conventional memory addressing modes can be used on the register file as well. This is enabled by the fact that the register file is assigned the 32 lowermost Data Space addresses (\$00 - \$1F), allowing them to be accessed as though they were ordinary memory locations.

The I/O memory space contains 64 addresses for CPU peripheral functions as Control Registers, Timer/Counters, A/D-converters, and other I/O functions. The I/O Memory can be accessed directly, or as the Data Space locations following those of the register file, \$20 - \$5F.

The AVR uses a Harvard architecture concept - with separate memories and buses for program and data. The program memory is executed with a two stage pipeline. While one instruction is being executed, the next instruction is pre-fetched from the program memory. This concept enables instructions to be executed in every clock cycle. The program memory is in-system downloadable Flash memory.


With the relative jump and call instructions, the whole 2K/4K address space is directly accessed. Most AVR instructions have a single 16-bit word format. Every program memory address contains a 16- or 32-bit instruction.

During interrupts and subroutine calls, the return address program counter (PC) is stored on the stack. The stack is effectively allocated in the general data SRAM, and consequently the stack size is only limited by the total SRAM size and the usage of the SRAM. All user programs must initialize the SP in the reset routine (before subroutines or interrupts are executed). The 9/10-bit stack pointer SP is read/write accessible in the I/O space.

The 256/512 bytes data SRAM can be easily accessed through the five different addressing modes supported in the AVR architecture.

The memory spaces in the AVR architecture are all linear and regular memory maps.

**Figure 3.** Memory Maps



A flexible interrupt module has its control registers in the I/O space with an additional global interrupt enable bit in the status register. All the different interrupts have a separate interrupt vector in the interrupt vector table at the beginning of the program memory. The different interrupts have priority in accordance with their interrupt vector position. The lower the interrupt vector address, the higher the priority.

## Register Summary

| Address     | Name     | Bit 7  | Bit 6  | Bit 5  | Bit 4  | Bit 3  | Bit 2  | Bit 1  | Bit 0  | Page    |
|-------------|----------|--|--------|--------|--------|--------|--------|--------|--------|---------|
| \$3F (\$5F) | SREG     | I  | T      | H      | S      | V      | N      | Z      | C      | page 17 |
| \$3E (\$5E) | SPH      | -  | -      | -      | -      | -      | -      | SP9    | SP8    | page 18 |
| \$3D (\$5D) | SPL      | SP7  | SP6    | SP5    | SP4    | SP3    | SP2    | SP1    | SP0    | page 18 |
| \$3C (\$5C) | Reserved |  |        |        |        |        |        |        |        |         |
| \$3B (\$5B) | GIMSK    | INT1   | INT0   | -      | -      | -      | -      | -      | -      | page 23 |
| \$3A (\$5A) | GIFR     | INTF1  | INTF0  |        |        |        |        |        |        | page 24 |
| \$39 (\$59) | TIMSK    | OCIE2  | TOIE2  | TICIE1 | OCIE1A | OCIE1B | TOIE1  | -      | TOIE0  | page 24 |
| \$38 (\$58) | TIFR     | OCF2   | TOV2   | ICF1   | OCF1A  | OCF1B  | TOV1   | -      | TOV0   | page 25 |
| \$37 (\$57) | Reserved |  |        |        |        |        |        |        |        |         |
| \$36 (\$56) | Reserved |  |        |        |        |        |        |        |        |         |
| \$35 (\$55) | MCUCR    | -  | SE     | SM1    | SM0    | ISC11  | ISC10  | ISC01  | ISC00  | page 26 |
| \$34 (\$54) | MCUSR    | -  | -      | -      | -      | -      | -      | EXTRF  | PORF   | page 22 |
| \$33 (\$53) | TCCR0    | -  | -      | -      | -      | -      | CS02   | CS01   | CS00   | page 30 |
| \$32 (\$52) | TCNT0    | Timer/Counter0 (8 Bits)                              |        |        |        |        |        |        |        | page 31 |
| \$31 (\$51) | Reserved |  |        |        |        |        |        |        |        |         |
| \$30 (\$50) | Reserved |  |        |        |        |        |        |        |        |         |
| \$2F (\$4F) | TCCR1A   | COM1A1   | COM1A0 | COM1B1 | COM1B0 | -      | -      | PWM11  | PWM10  | page 33 |
| \$2E (\$4E) | TCCR1B   | ICNC1  | ICES1  | -      | -      | CTC1   | CS12   | CS11   | CS10   | page 34 |
| \$2D (\$4D) | TCNT1H   | Timer/Counter1 - Counter Register High Byte          |        |        |        |        |        |        |        | page 35 |
| \$2C (\$4C) | TCNT1L   | Timer/Counter1 - Counter Register Low Byte           |        |        |        |        |        |        |        | page 35 |
| \$2B (\$4B) | OCR1AH   | Timer/Counter1 - Output Compare Register A High Byte |        |        |        |        |        |        |        | page 36 |
| \$2A (\$4A) | OCR1AL   | Timer/Counter1 - Output Compare Register A Low Byte  |        |        |        |        |        |        |        | page 36 |
| \$29 (\$49) | OCR1BH   | Timer/Counter1 - Output Compare Register B High Byte |        |        |        |        |        |        |        | page 36 |
| \$28 (\$48) | OCR1BL   | Timer/Counter1 - Output Compare Register B Low Byte  |        |        |        |        |        |        |        | page 36 |
| \$27 (\$47) | ICR1H    | Timer/Counter1 - Input Capture Register High Byte    |        |        |        |        |        |        |        | page 36 |
| \$26 (\$46) | ICR1L    | Timer/Counter1 - Input Capture Register Low Byte     |        |        |        |        |        |        |        | page 36 |
| \$25 (\$45) | TCCR2    | -  | PWM2   | COM21  | COM20  | CTC2   | CS22   | CS21   | CS20   | page 40 |
| \$24 (\$44) | TCNT2    | Timer/Counter2 (8 Bits)                              |        |        |        |        |        |        |        | page 41 |
| \$23 (\$43) | OCR2     | Timer/Counter2 Output Compare Register               |        |        |        |        |        |        |        | page 41 |
| \$22 (\$42) | ASSR     | -  | -      | -      | -      | AS2    | TCN2UB | OCR2UB | TCR2UB | page 42 |
| \$21 (\$41) | WDTCR    | -  | -      | -      | WDTOE  | WDE    | WDP2   | WDP1   | WDP0   | page 44 |
| \$20 (\$40) | Reserved |  |        |        |        |        |        |        |        |         |
| \$1F (\$3F) | EEARH    |  |        |        |        |        |        |        | EEAR9  | page 46 |
| \$1E (\$3E) | EEARL    | EEAR7  | EEAR6  | EEAR5  | EEAR4  | EEAR3  | EEAR2  | EEAR1  | EEAR0  | page 46 |
| \$1D (\$3D) | EEDR     | EEPROM Data Register                                 |        |        |        |        |        |        |        | page 46 |
| \$1C (\$3C) | EECR     | -  | -      | -      | -      | EERIE  | EEMWE  | EEWE   | EERE   | page 46 |
| \$1B (\$3B) | PORTA    | PORTA7   | PORTA6 | PORTA5 | PORTA4 | PORTA3 | PORTA2 | PORTA1 | PORTA0 | page 67 |
| \$1A (\$3A) | DDRA     | DDA7   | DDA6   | DDA5   | DDA4   | DDA3   | DDA2   | DDA1   | DDA0   | page 67 |
| \$19 (\$39) | PINA     | PINA7  | PINA6  | PINA5  | PINA4  | PINA3  | PINA2  | PINA1  | PINA0  | page 67 |
| \$18 (\$38) | PORTB    | PORTB7   | PORTB6 | PORTB5 | PORTB4 | PORTB3 | PORTB2 | PORTB1 | PORTB0 | page 69 |
| \$17 (\$37) | DDRB     | DBB7   | DBB6   | DBB5   | DBB4   | DBB3   | DBB2   | DBB1   | DBB0   | page 69 |
| \$16 (\$36) | PINB     | PINB7  | PINB6  | PINB5  | PINB4  | PINB3  | PINB2  | PINB1  | PINB0  | page 69 |
| \$15 (\$35) | PORTC    | PORTC7   | PORTC6 | PORTC5 | PORTC4 | PORTC3 | PORTC2 | PORTC1 | PORTC0 | page 74 |
| \$14 (\$34) | DDRC     | DDC7   | DDC6   | DDC5   | DDC4   | DDC3   | DDC2   | DDC1   | DDC0   | page 74 |
| \$13 (\$33) | PINC     | PINC7  | PINC6  | PINC5  | PINC4  | PINC3  | PINC2  | PINC1  | PINC0  | page 74 |
| \$12 (\$32) | PORTD    | PORTD7   | PORTD6 | PORTD5 | PORTD4 | PORTD3 | PORTD2 | PORTD1 | PORTD0 | page 77 |
| \$11 (\$31) | DDRD     | DDD7   | DDD6   | DDD5   | DDD4   | DDD3   | DDD2   | DDD1   | DDD0   | page 77 |
| \$10 (\$30) | PIND     | PIND7  | PIND6  | PIND5  | PIND4  | PIND3  | PIND2  | PIND1  | PIND0  | page 77 |
| \$0F (\$2F) | SPDR     | SPI Data Register                                    |        |        |        |        |        |        |        | page 51 |
| \$0E (\$2E) | SPSR     | SPIF   | WCOL   | -      | -      | -      | -      | -      | -      | page 51 |
| \$0D (\$2D) | SPCR     | SPIE   | SPE    | DORD   | MSTR   | CPOL   | CPHA   | SPR1   | SPR0   | page 50 |
| \$0C (\$2C) | UDR      | UART I/O Data Register                               |        |        |        |        |        |        |        | page 55 |
| \$0B (\$2B) | USR      | RXC  | TXC    | UDRE   | FE     | OR     | -      | -      | -      | page 55 |
| \$0A (\$2A) | UCR      | RXCIE  | TXCIE  | UDRIE  | RXEN   | TXEN   | CHR9   | RXB8   | TXB8   | page 56 |
| \$09 (\$29) | UBRR     | UART Baud Rate Register                              |        |        |        |        |        |        |        | page 57 |
| \$08 (\$28) | ACSR     | ACD  | -      | ACO    | ACI    | ACIE   | ACIC   | ACIS1  | ACIS0  | page 58 |
| \$07 (\$27) | ADMUX    | -  | -      | -      | -      | -      | MUX2   | MUX1   | MUX0   | page 63 |
| \$06 (\$26) | ADCSR    | ADEN   | ADSC   | ADFR   | ADIF   | ADIE   | ADPS2  | ADPS1  | ADPS0  | page 63 |
| \$05 (\$25) | ADCH     | -  | -      | -      | -      | -      | -      | ADC9   | ADC8   | page 64 |
| \$04 (\$24) | ADCL     | ADC7   | ADC6   | ADC5   | ADC4   | ADC3   | ADC2   | ADC1   | ADC0   | page 64 |

## Register Summary (Continued)

| Address     | Name     | Bit 7 | Bit 6 | Bit 5 | Bit 4 | Bit 3 | Bit 2 | Bit 1 | Bit 0 | Page |
|-------------|----------|-------|-------|-------|-------|-------|-------|-------|-------|------|
| \$03 (\$20) | Reserved |       |       |       |       |       |       |       |       |      |
| \$02 (\$22) | Reserved |       |       |       |       |       |       |       |       |      |
| \$01 (\$21) | Reserved |       |       |       |       |       |       |       |       |      |
| \$00 (\$20) | Reserved |       |       |       |       |       |       |       |       |      |

Notes:

1. For compatibility with future devices, reserved bits should be written to zero if accessed. Reserved I/O memory addresses should never be written.
2. Some of the status flags are cleared by writing a logical one to them. Note that the CBI and SBI instructions will operate on all bits in the I/O register, writing a one back into any flag read as set, thus clearing the flag. The CBI and SBI instructions work with registers \$00 to \$1F only.

## Instruction Set Summary

| Mnemonics                                | Operands | Description                            | Operation   | Flags         | #Clocks |
|--|----------|--|---|---------------|---------|
| <b>ARITHMETIC AND LOGIC INSTRUCTIONS</b> |          |  |   |               |         |
| ADD                                      | Rd, Rr   | Add two Registers                      | $Rd \leftarrow Rd + Rr$                               | Z,C,N,V,H     | 1       |
| ADC                                      | Rd, Rr   | Add with Carry two Registers           | $Rd \leftarrow Rd + Rr + C$                           | Z,C,N,V,H     | 1       |
| ADIW                                     | RdL,K    | Add Immediate to Word                  | $RdL:RdH \leftarrow RdL:RdH + K$                      | Z,C,N,V,S     | 2       |
| SUB                                      | Rd, Rr   | Subtract two Registers                 | $Rd \leftarrow Rd - Rr$                               | Z,C,N,V,H     | 1       |
| SUBI                                     | Rd, K    | Subtract Constant from Register        | $Rd \leftarrow Rd - K$                                | Z,C,N,V,H     | 1       |
| SBC                                      | Rd, Rr   | Subtract with Carry two Registers      | $Rd \leftarrow Rd - Rr - C$                           | Z,C,N,V,H     | 1       |
| SBCI                                     | Rd, K    | Subtract with Carry Constant from Reg. | $Rd \leftarrow Rd - K - C$                            | Z,C,N,V,H     | 1       |
| SBIW                                     | RdL,K    | Subtract Immediate from Word           | $RdL:RdH \leftarrow RdL:RdH - K$                      | Z,C,N,V,S     | 2       |
| AND                                      | Rd, Rr   | Logical AND Registers                  | $Rd \leftarrow Rd \bullet Rr$                         | Z,N,V         | 1       |
| ANDI                                     | Rd, K    | Logical AND Register and Constant      | $Rd \leftarrow Rd \bullet K$                          | Z,N,V         | 1       |
| OR                                       | Rd, Rr   | Logical OR Registers                   | $Rd \leftarrow Rd \vee Rr$                            | Z,N,V         | 1       |
| ORI                                      | Rd, K    | Logical OR Register and Constant       | $Rd \leftarrow Rd \vee K$                             | Z,N,V         | 1       |
| EOR                                      | Rd, Rr   | Exclusive OR Registers                 | $Rd \leftarrow Rd \oplus Rr$                          | Z,N,V         | 1       |
| COM                                      | Rd       | One's Complement                       | $Rd \leftarrow \$FF - Rd$                             | Z,C,N,V       | 1       |
| NEG                                      | Rd       | Two's Complement                       | $Rd \leftarrow \$00 - Rd$                             | Z,C,N,V,H     | 1       |
| SBR                                      | Rd,K     | Set Bit(s) in Register                 | $Rd \leftarrow Rd \vee K$                             | Z,N,V         | 1       |
| CBR                                      | Rd,K     | Clear Bit(s) in Register               | $Rd \leftarrow Rd \bullet (\$FF - K)$                 | Z,N,V         | 1       |
| INC                                      | Rd       | Increment                              | $Rd \leftarrow Rd + 1$                                | Z,N,V         | 1       |
| DEC                                      | Rd       | Decrement                              | $Rd \leftarrow Rd - 1$                                | Z,N,V         | 1       |
| TST                                      | Rd       | Test for Zero or Minus                 | $Rd \leftarrow Rd \bullet Rd$                         | Z,N,V         | 1       |
| CLR                                      | Rd       | Clear Register                         | $Rd \leftarrow Rd \oplus Rd$                          | Z,N,V         | 1       |
| SER                                      | Rd       | Set Register                           | $Rd \leftarrow \$FF$                                  | None          | 1       |
| <b>BRANCH INSTRUCTIONS</b>               |          |  |   |               |         |
| RJMP                                     | k        | Relative Jump                          | $PC \leftarrow PC + k + 1$                            | None          | 2       |
| IJMP                                     |          | Indirect Jump to (Z)                   | $PC \leftarrow Z$                                     | None          | 2       |
| RCALL                                    | k        | Relative Subroutine Call               | $PC \leftarrow PC + k + 1$                            | None          | 3       |
| ICALL                                    |          | Indirect Call to (Z)                   | $PC \leftarrow Z$                                     | None          | 3       |
| RET                                      |          | Subroutine Return                      | $PC \leftarrow STACK$                                 | None          | 4       |
| RETI                                     |          | Interrupt Return                       | $PC \leftarrow STACK$                                 | I             | 4       |
| CPSE                                     | Rd,Rr    | Compare, Skip if Equal                 | if (Rd = Rr) $PC \leftarrow PC + 2$ or 3              | None          | 1/2/3   |
| CP                                       | Rd,Rr    | Compare                                | $Rd - Rr$   | Z, N, V, C, H | 1       |
| CPC                                      | Rd,Rr    | Compare with Carry                     | $Rd - Rr - C$   | Z, N, V, C, H | 1       |
| CPI                                      | Rd,K     | Compare Register with Immediate        | $Rd - K$  | Z, N, V, C, H | 1       |
| SBRC                                     | Rr, b    | Skip if Bit in Register Cleared        | if (Rr(b)=0) $PC \leftarrow PC + 2$ or 3              | None          | 1/2/3   |
| SBRS                                     | Rr, b    | Skip if Bit in Register is Set         | if (Rr(b)=1) $PC \leftarrow PC + 2$ or 3              | None          | 1/2/3   |
| SBIC                                     | P, b     | Skip if Bit in I/O Register Cleared    | if (P(b)=0) $PC \leftarrow PC + 2$ or 3               | None          | 1/2/3   |
| SBIS                                     | P, b     | Skip if Bit in I/O Register is Set     | if (P(b)=1) $PC \leftarrow PC + 2$ or 3               | None          | 1/2/3   |
| BRBS                                     | s, k     | Branch if Status Flag Set              | if (SREG(s) = 1) then $PC \leftarrow PC + k + 1$      | None          | 1/2     |
| BRBC                                     | s, k     | Branch if Status Flag Cleared          | if (SREG(s) = 0) then $PC \leftarrow PC + k + 1$      | None          | 1/2     |
| BREQ                                     | k        | Branch if Equal                        | if (Z = 1) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRNE                                     | k        | Branch if Not Equal                    | if (Z = 0) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRCS                                     | k        | Branch if Carry Set                    | if (C = 1) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRCC                                     | k        | Branch if Carry Cleared                | if (C = 0) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRSH                                     | k        | Branch if Same or Higher               | if (C = 0) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRLO                                     | k        | Branch if Lower                        | if (C = 1) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRMI                                     | k        | Branch if Minus                        | if (N = 1) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRPL                                     | k        | Branch if Plus                         | if (N = 0) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRGE                                     | k        | Branch if Greater or Equal, Signed     | if (N $\oplus$ V = 0) then $PC \leftarrow PC + k + 1$ | None          | 1/2     |
| BRLT                                     | k        | Branch if Less Than Zero, Signed       | if (N $\oplus$ V = 1) then $PC \leftarrow PC + k + 1$ | None          | 1/2     |
| BRHS                                     | k        | Branch if Half Carry Flag Set          | if (H = 1) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRHC                                     | k        | Branch if Half Carry Flag Cleared      | if (H = 0) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRTS                                     | k        | Branch if T Flag Set                   | if (T = 1) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRTC                                     | k        | Branch if T Flag Cleared               | if (T = 0) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRVS                                     | k        | Branch if Overflow Flag is Set         | if (V = 1) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRVC                                     | k        | Branch if Overflow Flag is Cleared     | if (V = 0) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRIE                                     | k        | Branch if Interrupt Enabled            | if (I = 1) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |
| BRID                                     | k        | Branch if Interrupt Disabled           | if (I = 0) then $PC \leftarrow PC + k + 1$            | None          | 1/2     |

## Instruction Set Summary (Continued)

| Mnemonics                            | Operands | Description                      | Operation  | Flags   | #Clocks |
|--------------------------------------|----------|----------------------------------|--|---------|---------|
| <b>DATA TRANSFER INSTRUCTIONS</b>    |          |                                  |  |         |         |
| MOV                                  | Rd, Rr   | Move Between Registers           | $Rd \leftarrow Rr$   | None    | 1       |
| LDI                                  | Rd, K    | Load Immediate                   | $Rd \leftarrow K$  | None    | 1       |
| LD                                   | Rd, X    | Load Indirect                    | $Rd \leftarrow (X)$  | None    | 2       |
| LD                                   | Rd, X+   | Load Indirect and Post-Inc.      | $Rd \leftarrow (X), X \leftarrow X + 1$                            | None    | 2       |
| LD                                   | Rd, -X   | Load Indirect and Pre-Dec.       | $X \leftarrow X - 1, Rd \leftarrow (X)$                            | None    | 2       |
| LD                                   | Rd, Y    | Load Indirect                    | $Rd \leftarrow (Y)$  | None    | 2       |
| LD                                   | Rd, Y+   | Load Indirect and Post-Inc.      | $Rd \leftarrow (Y), Y \leftarrow Y + 1$                            | None    | 2       |
| LD                                   | Rd, -Y   | Load Indirect and Pre-Dec.       | $Y \leftarrow Y - 1, Rd \leftarrow (Y)$                            | None    | 2       |
| LDD                                  | Rd, Y+q  | Load Indirect with Displacement  | $Rd \leftarrow (Y + q)$  | None    | 2       |
| LD                                   | Rd, Z    | Load Indirect                    | $Rd \leftarrow (Z)$  | None    | 2       |
| LD                                   | Rd, Z+   | Load Indirect and Post-Inc.      | $Rd \leftarrow (Z), Z \leftarrow Z + 1$                            | None    | 2       |
| LD                                   | Rd, -Z   | Load Indirect and Pre-Dec.       | $Z \leftarrow Z - 1, Rd \leftarrow (Z)$                            | None    | 2       |
| LDD                                  | Rd, Z+q  | Load Indirect with Displacement  | $Rd \leftarrow (Z + q)$  | None    | 2       |
| LDS                                  | Rd, k    | Load Direct from SRAM            | $Rd \leftarrow (k)$  | None    | 2       |
| ST                                   | X, Rr    | Store Indirect                   | $(X) \leftarrow Rr$  | None    | 2       |
| ST                                   | X+, Rr   | Store Indirect and Post-Inc.     | $(X) \leftarrow Rr, X \leftarrow X + 1$                            | None    | 2       |
| ST                                   | -X, Rr   | Store Indirect and Pre-Dec.      | $X \leftarrow X - 1, (X) \leftarrow Rr$                            | None    | 2       |
| ST                                   | Y, Rr    | Store Indirect                   | $(Y) \leftarrow Rr$  | None    | 2       |
| ST                                   | Y+, Rr   | Store Indirect and Post-Inc.     | $(Y) \leftarrow Rr, Y \leftarrow Y + 1$                            | None    | 2       |
| ST                                   | -Y, Rr   | Store Indirect and Pre-Dec.      | $Y \leftarrow Y - 1, (Y) \leftarrow Rr$                            | None    | 2       |
| STD                                  | Y+q, Rr  | Store Indirect with Displacement | $(Y + q) \leftarrow Rr$  | None    | 2       |
| ST                                   | Z, Rr    | Store Indirect                   | $(Z) \leftarrow Rr$  | None    | 2       |
| ST                                   | Z+, Rr   | Store Indirect and Post-Inc.     | $(Z) \leftarrow Rr, Z \leftarrow Z + 1$                            | None    | 2       |
| ST                                   | -Z, Rr   | Store Indirect and Pre-Dec.      | $Z \leftarrow Z - 1, (Z) \leftarrow Rr$                            | None    | 2       |
| STD                                  | Z+q, Rr  | Store Indirect with Displacement | $(Z + q) \leftarrow Rr$  | None    | 2       |
| STS                                  | k, Rr    | Store Direct to SRAM             | $(k) \leftarrow Rr$  | None    | 2       |
| LPM                                  |          | Load Program Memory              | $R0 \leftarrow (Z)$  | None    | 3       |
| IN                                   | Rd, P    | In Port                          | $Rd \leftarrow P$  | None    | 1       |
| OUT                                  | P, Rr    | Out Port                         | $P \leftarrow Rr$  | None    | 1       |
| PUSH                                 | Rr       | Push Register on Stack           | STACK $\leftarrow Rr$  | None    | 2       |
| POP                                  | Rd       | Pop Register from Stack          | $Rd \leftarrow \text{STACK}$                                       | None    | 2       |
| <b>BIT AND BIT-TEST INSTRUCTIONS</b> |          |                                  |  |         |         |
| SBI                                  | P,b      | Set Bit in I/O Register          | $I/O(P,b) \leftarrow 1$  | None    | 2       |
| CBI                                  | P,b      | Clear Bit in I/O Register        | $I/O(P,b) \leftarrow 0$  | None    | 2       |
| LSL                                  | Rd       | Logical Shift Left               | $Rd(n+1) \leftarrow Rd(n), Rd(0) \leftarrow 0$                     | Z,C,N,V | 1       |
| LSR                                  | Rd       | Logical Shift Right              | $Rd(n) \leftarrow Rd(n+1), Rd(7) \leftarrow 0$                     | Z,C,N,V | 1       |
| ROL                                  | Rd       | Rotate Left Through Carry        | $Rd(0) \leftarrow C, Rd(n+1) \leftarrow Rd(n), C \leftarrow Rd(7)$ | Z,C,N,V | 1       |
| ROR                                  | Rd       | Rotate Right Through Carry       | $Rd(7) \leftarrow C, Rd(n) \leftarrow Rd(n+1), C \leftarrow Rd(0)$ | Z,C,N,V | 1       |
| ASR                                  | Rd       | Arithmetic Shift Right           | $Rd(n) \leftarrow Rd(n+1), n=0..6$                                 | Z,C,N,V | 1       |
| SWAP                                 | Rd       | Swap Nibbles                     | $Rd(3..0) \leftarrow Rd(7..4), Rd(7..4) \leftarrow Rd(3..0)$       | None    | 1       |
| BSET                                 | s        | Flag Set                         | $SREG(s) \leftarrow 1$   | SREG(s) | 1       |
| BCLR                                 | s        | Flag Clear                       | $SREG(s) \leftarrow 0$   | SREG(s) | 1       |
| BST                                  | Rr, b    | Bit Store from Register to T     | $T \leftarrow Rr(b)$   | T       | 1       |
| BLD                                  | Rd, b    | Bit load from T to Register      | $Rd(b) \leftarrow T$   | None    | 1       |
| SEC                                  |          | Set Carry                        | $C \leftarrow 1$   | C       | 1       |
| CLC                                  |          | Clear Carry                      | $C \leftarrow 0$   | C       | 1       |
| SEN                                  |          | Set Negative Flag                | $N \leftarrow 1$   | N       | 1       |
| CLN                                  |          | Clear Negative Flag              | $N \leftarrow 0$   | N       | 1       |
| SEZ                                  |          | Set Zero Flag                    | $Z \leftarrow 1$   | Z       | 1       |
| CLZ                                  |          | Clear Zero Flag                  | $Z \leftarrow 0$   | Z       | 1       |
| SEI                                  |          | Global Interrupt Enable          | $I \leftarrow 1$   | I       | 1       |
| CLI                                  |          | Global Interrupt Disable         | $I \leftarrow 0$   | I       | 1       |
| SES                                  |          | Set Signed Test Flag             | $S \leftarrow 1$   | S       | 1       |
| CLS                                  |          | Clear Signed Test Flag           | $S \leftarrow 0$   | S       | 1       |
| SEV                                  |          | Set Twos Complement Overflow.    | $V \leftarrow 1$   | V       | 1       |
| CLV                                  |          | Clear Twos Complement Overflow   | $V \leftarrow 0$   | V       | 1       |
| SET                                  |          | Set T in SREG                    | $T \leftarrow 1$   | T       | 1       |
| CLT                                  |          | Clear T in SREG                  | $T \leftarrow 0$   | T       | 1       |
| SEH                                  |          | Set Half Carry Flag in SREG      | $H \leftarrow 1$   | H       | 1       |
| CLH                                  |          | Clear Half Carry Flag in SREG    | $H \leftarrow 0$   | H       | 1       |
| NOP                                  |          | No Operation                     |  | None    | 1       |
| SLEEP                                |          | Sleep                            | (see specific descr. for Sleep function)                           | None    | 3       |
| WDR                                  |          | Watchdog Reset                   | (see specific descr. for WDR/timer)                                | None    | 1       |

## Ordering Information


| Power Supply | Speed (MHz) | Ordering Code  | Package | Operation Range               |
|--------------|-------------|----------------|---------|-------------------------------|
| 2.7 - 6.0V   | 4           | AT90LS4434-4AC | 44A     | Commercial<br>(0°C to 70°C)   |
|              |             | AT90LS4434-4JC | 44J     |                               |
|              |             | AT90LS4434-4PC | 40P6    |                               |
|              | 8           | AT90LS4434-4AI | 44A     | Industrial<br>(-40°C to 85°C) |
|              |             | AT90LS4434-4JI | 44J     |                               |
|              |             | AT90LS4434-4PI | 40P6    |                               |
| 4.0 - 6.0V   | 8           | AT90S4434-8AC  | 44A     | Commercial<br>(0°C to 70°C)   |
|              |             | AT90S4434-8JC  | 44J     |                               |
|              |             | AT90S4434-8PC  | 40P6    |                               |
|              | 4           | AT90S4434-8AI  | 44A     | Industrial<br>(-40°C to 85°C) |
|              |             | AT90S4434-8JI  | 44J     |                               |
|              |             | AT90S4434-8PI  | 40P6    |                               |
| 2.7 - 6.0V   | 4           | AT90LS8535-4AC | 44A     | Commercial<br>(0°C to 70°C)   |
|              |             | AT90LS8535-4JC | 44J     |                               |
|              |             | AT90LS8535-4PC | 40P6    |                               |
|              | 8           | AT90LS8535-4AI | 44A     | Industrial<br>(-40°C to 85°C) |
|              |             | AT90LS8535-4JI | 44J     |                               |
|              |             | AT90LS8535-4PI | 40P6    |                               |
| 4.0 - 6.0V   | 8           | AT90S8535-8AC  | 44A     | Commercial<br>(0°C to 70°C)   |
|              |             | AT90S8535-8JC  | 44J     |                               |
|              |             | AT90S8535-8PC  | 40P6    |                               |
|              | 4           | AT90S8535-8AI  | 44A     | Industrial<br>(-40°C to 85°C) |
|              |             | AT90S8535-8JI  | 44J     |                               |
|              |             | AT90S8535-8PI  | 40P6    |                               |

### Package Type

|             |  |
|-------------|--|
| <b>44A</b>  | 44-lead, Thin (1.0mm) Plastic Gull Wing Quad Flat Package (TQFP) |
| <b>40P6</b> | 40-lead, 0.600" Wide, Plastic Dual in Line Package (PDIP)        |
| <b>44J</b>  | 44-lead, Plastic J-Ledged Chip Carrier (PLCC)                    |


## Packaging Information

**44A, 44-lead, Thin (1.0 mm) Plastic Gull Wing Quad Flat Package (TQFP)**  
Dimensions in Millimeters and (Inches)




\*Controlling dimension: millimeters

**40P6**, 40-lead, 0.600" Wide,  
Plastic Dual Inline Package (PDIP)  
Dimensions in Inches and (Millimeters)  
JEDEC STANDARD MS-011 AC



## 44J, 44-lead, Plastic J-Leaded Chip Carrier (PLCC) Dimensions in Inches and (Millimeters)





## Atmel Headquarters

### Corporate Headquarters

2325 Orchard Parkway  
San Jose, CA 95131  
TEL (408) 441-0311  
FAX (408) 487-2600

### Europe

Atmel U.K., Ltd.  
Coliseum Business Centre  
Riverside Way  
Camberley, Surrey GU15 3YL  
England  
TEL (44) 1276-686-677  
FAX (44) 1276-686-697

### Asia

Atmel Asia, Ltd.  
Room 1219  
Chinachem Golden Plaza  
77 Mody Road Tsimhatsui  
East Kowloon  
Hong Kong  
TEL (852) 2721-9778  
FAX (852) 2722-1369

### Japan

Atmel Japan K.K.  
9F, Tonetsu Shinkawa Bldg.  
1-24-8 Shinkawa  
Chuo-ku, Tokyo 104-0033  
Japan  
TEL (81) 3-3523-3551  
FAX (81) 3-3523-7581

## Atmel Operations

### Atmel Colorado Springs

1150 E. Cheyenne Mtn. Blvd.  
Colorado Springs, CO 80906  
TEL (719) 576-3300  
FAX (719) 540-1759

### Atmel Rousset

Zone Industrielle  
13106 Rousset Cedex  
France  
TEL (33) 4-4253-6000  
FAX (33) 4-4253-6001

### Fax-on-Demand

North America:  
1-(800) 292-8635  
International:  
1-(408) 441-0732

*e-mail*  
literature@atmel.com

*Web Site*  
<http://www.atmel.com>

*BBS*  
1-(408) 436-4309

### © Atmel Corporation 1999.

Atmel Corporation makes no warranty for the use of its products, other than those expressly contained in the Company's standard warranty which is detailed in Atmel's Terms and Conditions located on the Company's web site. The Company assumes no responsibility for any errors which may appear in this document, reserves the right to change devices or specifications detailed herein at any time without notice, and does not make any commitment to update the information contained herein. No licenses to patents or other intellectual property of Atmel are granted by the Company in connection with the sale of Atmel products, expressly or by implication. Atmel's products are not authorized for use as critical components in life support devices or systems.

Marks bearing ® and/or ™ are registered trademarks and trademarks of Atmel Corporation.

Terms and product names in this document may be trademarks of others.



Printed on recycled paper.

1041ES-04/99/xM