

LAN Testing and Multimeter



2 in 1



Features:

- Measures dc / ac Voltage, dc / ac current, resistance, continuity, diode and LAN tester
- 3-1/2 digit (2,000 count) LCD display for multi-meter functions
- LED Displays the actual pin configuration of 10BASE-T and 10BASE-2 thin Ethernet, FJ45 258 A, tia-568a / 568b and token ring cables
- Double moulded housing
- CATIII 6,00 V, CATII 1,000 V
- Provides easy to read continuity and fault status display
- Checks for continuity, open wire, ground wire, shorted pair and crossed pair faults
- Allows for remote testing of installed cables from wall jack or patch panel
- Auto or manual scanning for LAN tester
- Auto-ranging with auto power off for multi-meter functions

Specifications:

Maximum input voltage	: 6,00 V ac / dc
Diode test	: Maximum test current 1 mA, open circuit voltage of 1.5 V typical
Continuity check	: Audible signal if the resistance is <150
Display	: 2,000 count 3-1/2 digit LCD
Over range indication	: LCD displays "OL"
Polarity	: Minus (-) sign for negative polarity
Low battery indication	: "BAT" symbol indicates low battery condition
Input Impedance	: >7.5 M (V dc and V ac)
AC response	: Average responding
ACV bandwidth	: 50 Hz to 60 Hz
Auto power off	: 15 minutes (approximately)
Fuse	: mA, μ A ranges; 0.2 A / 250 V fast acting fuse
Batteries	: 9 V battery and two "AA" batteries
Operating temperature	: 32°F to 104°F (0°C to 40°C)
Storage temperature	: 14°F to 122°F (-10°C to 50°C)
Weight	: 308 g
Size	: 162 × 74.5 × 44 mm
Standard	: IEC61010-1 CAT III-600 V pollution degree II, CE approved

LAN Testing and Multimeter

2 in 1



Specification Table

Function	Range	Accuracy
DC Voltage	200 mV	$\pm(0.5\% \text{ rdg} + 3\text{d})$
	2 V, 20 V	$\pm(1\% \text{ rdg} + 3\text{d})$
	200 V, 600 V	
AC Voltage 50 to 60 Hz	2 V, 20 V	$\pm(1\% \text{ rdg} + 5\text{d})$
	200 V, 600 V	$\pm(1.5\% \text{ rdg} + 10\text{d})$
DC Current	200 μA , 2,000 μA	$\pm(1.5\% \text{ rdg} + 3\text{d})$
	20 mA, 200 mA	$\pm(2\% \text{ rdg} + 3\text{d})$
AC Current	200 μA , 2,000 μA	$\pm(1.8\% \text{ rdg} + 8\text{d})$
	20 mA, 200 mA	$\pm(2.5\% \text{ rdg} + 8\text{d})$
Resistance	200	$\pm(0.8\% \text{ rdg} + 5\text{d})$
	2 k Ω , 20 k Ω , 200 k Ω	$\pm(1.2\% \text{ rdg} + 3\text{d})$
	2 M Ω	$\pm(2\% \text{ rdg} + 5\text{d})$
	20 M Ω	$\pm(5\% \text{ rdg} + 8\text{d})$

Part Number Table

Description	Part Number
LAN Tester and DMM	72-8495

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

