


HONEYWELL PART NUMBER
341SM169-H252
PRODUCT CODE TZA2939

REV	DOCUMENT	CHANGED BY	CHECK
3	0041782	PK 21JUL08	ASD



CORROSION RESISTANT
STEEL ACTUATOR



POINT "A"

.080 MAX
PRETRAVEL

.340 ± .040
OPERATING
POSITION



NOTES

- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F
- CHARACTERISTICS TAKEN AT POINT "A"

RELEASE NO.	PR - 19095
REPLACES	X93276 - SM

CHARACTERISTICS
OPERATING FORCE - - 45 GRAMS MAX
RELEASE FORCE - - - 7 GRAMS MIN
DIFFERENTIAL TRAVEL - - - .018 MAX
OVERTRAVEL - - - - - .017 MIN

ELECTRICAL DATA			
CONTACT ARRANGEMENT SPDT			
APPROVALS	KEMA, CE	11A 250V ~ T85 1E4 5A 30 Vdc T85 1E4	
	UL, CSA	11A 1/4 HP 125 250 VAC 5A 30 VDC	BRAND L190

DESIGN UNITS: INCH		
TOLERANCES UNLESS NOTED:		
NO PLACE	X	±
ONE PLACE	.X	±
TWO PLACE	.XX	±
THREE PLACE	.XXX	±
FOUR PLACE	.XXXX	±
ANGLES		±
THIRD ANGLE PROJECTION		

DRAWN	VK	03 DEC 07
CHECK	RJ	03 DEC 07
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
B	I	341SM169-H252	3
SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1