

[Wire & Cable > Hook Up Wire > Hookup Wire: Nickel Coated Copper Wire, 0-16 AWG](#)Cable Type: **Spec 55PC**Operating Voltage: **600 V**Wire & Cable Insulation Material: **Radiation-Crosslinked, Modified ETFE**Conductor Material: **Nickel-Coated Copper**Wire Size: **4 AWG**[All Hookup Wire: Nickel Coated Copper Wire, 0-16 AWG \(11\)](#)

Features

Electrical Characteristics

Operating Voltage	600 V
-------------------	-------

Body Features

Wire & Cable Insulation Material	Radiation-Crosslinked, Modified ETFE
Conductor Material	Nickel-Coated Copper
Wire Color (Base)	White

Dimensions

Wire Size	4 AWG
-----------	-------

Usage Conditions

Cable Type	Spec 55PC
Operating Temperature Range	-65 – 200 °C [-85 – 392 °F]

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2025

(250)

Candidate List Declared Against: JUNE 2025 (250)

Does not contain REACH SVHC

Halogen Content

Out of Scope - excluded from Halogen requirements

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 0662-207-0482
CONT SOC ASSY

Customers Also Bought



TE Part #601036-000
D-602-45



TE Part #C01287-000
55PC1221-24-9/96-9




TE Part #222650-000
55A0114-26-5L0



TE Part #766653-000
55PC1221-22-9/96-9



TE Part #NB13052001
RNF-100-1-BK-STK



TE Part #829100-000
562A032-25-0



TE Part #878516-000
222K174-25-0



TE Part #927772-1
JPT REC 2.8 Contact SWS Sn



TE Part #AAC7538-00
DSV25-R-BT-07-1-C-SB-H



TE Part #ZPF000000000114657
732-8064-01 A1064

Documents

Product Drawings

55PC0213-4-9

English

Datasheets & Catalog Pages

[Raychem Wire and Cable Quick Reference Guide](#)

English

Product Specifications

[Product Specification](#)

English