



www.ameripack.com

Heavy-duty Shipping Cases



Ameripack's Heavy-duty Shipping containers are designed and constructed to offer the ultimate in security and protection for your valuable products.


DESIGN: Our Shipping Cases are formed by our **special ATA tooling** which creates molded-in **corner bumpers** and **stacking lugs**. The protruding bumpers offer additional protection, especially at every containers' weakest point - the corner. These bumpers absorb the impacts so your products don't. The molded-in lugs ensure stability when stacking cases.

HARDWARE: Our Shipping Cases utilize our standard **Heavy-duty hardware**

- 2" Aluminum valance extrusion (with silicone sealant and moisture gasket)
- Steel hinges, steel twist-draw latches, steel spring-loaded handles, and 9" lid stays

STANDARD HARDWARE

Shell: High-density Polyethylene



2" Aluminum Valance w/ Channel



Steel Spring-loaded Handle



Steel Twist Draw Latch




4"x 1 7/8" Steel Hinge

Neoprene O-Ring Valance Gasket

9" Heavy-duty Lid Stay

OPTIONAL HARDWARE



2" Aluminum Valance w/ 1/2" Flange

- Stainless Steel Padlock Hasp
- Stainless Steel Latch Protector
- Built-in Key Lock
- Pressure Relief Valve
- Humidity Indicator
- Label and Card Holders
- Telescoping Handle
- Removeable Casters
- Built-in Edge Wheels

USE: Heavy Duty Shipping Cases are best for products which may be shipped frequently as freight or luggage, or for items which may be heavy (over 40 pounds), delicate, and/or valuable. Items such as computers, commercial tooling, video equipment, and motorcycle engines.

WHY Ameripack?: Our vacuum-formed Shipping Cases offer industry leading value. Compared to other styles of shipping case, our durable and lightweight cases offer longer case life with lower shipping costs and lower cost of ownership.

FEATURES:

- High-density polyethylene plastic for strength and impact resistance
- Molded-in bumpers for unsurpassed product protection
- Molded-in ribs and channels for stacking stability
- 2 1/8" valance and heavy-duty hardware for high quality security
- Able to meet stringent ATA 300 - Cat. 1 and MIL specifications
- Withstand temperatures from -80 degrees F to +180 degrees
- Solvent, moisture, and water-resistant
- Hundreds of standard sizes available
- Almost limitless custom options

BENEFITS:

- Designed and constructed for long term durability and reuse
- Damage and corrosion resistance plus lightweight means reduced shipping costs
- Bel-Air craftsmanship ensures that the case takes the beating, not your delicate equipment

APPLICATIONS:

- Broadcast and video equipment
- Industrial and commercial tools
- Computers and electronics
- Surveying and seismographic devices
- Industrial and commercial lighting
- Diagnostic and testing equipment
- Rare and valuable collectables

Call 800-456-7963 now for instant case recommendations, design and pricing!


Heavy Duty Thermoform Shipping Cases From:



Standard Hardware

Shell: High Density Polyethylene
Stock Color = Silver

Valance: 2" Aluminum Valance



Lid Stay: 9" Heavy Duty Lid Stay

Hinge: 4" X 1.88" Steel hinge



Latch: Steel Twist Draw Latch




Handle: Steel Spring-Loaded Handle



O-Ring: Neoprene Gasket

Optional Hardware

Stainless Steel Padlock Hasp
Stainless Steel Latch Protector
Built-In Key Lock
Pressure Relief Valve
Telescoping Handle / Casters
Humidity Indicator
Label and Card Holders



Optional
Valance w/
Panel Flange
Shown at
Left

Part #	Length	Width	Heights Variable in 0.25" Increments			Weight	Standard #		
			Total Height	Lid Height	Base Height		Handles	Latches	Hinges/Stays
AP1212S	12	12	9 to 14	4.5 to 7	4.5 to 7	9	1	2	2/1
AP1212M	12	12	12.5 to 18	4.5 to 7	8 to 11	10	2	2	2/1
AP1212D	12	12	16 to 22	8 to 11	8 to 11	11	2	2	2/1
AP1512S	15	12	10 to 16	5 to 8	5 to 8	11	1	2	2/1
AP1616S	16	16	8 to 15	4 to 7.5	4 to 7.5	12	1	2	2/1
AP1616M	16	16	13.5 to 20	4 to 7.5	9.5 to 12.5	13	2	2	2/1
AP1616D	16	16	19 to 25	9.5 to 12.5	9.5 to 12.5	14	2	2	2/1
AP1814S*	18	14.5	8 to 14	4 to 7	4 to 7	12	1	2	2/1
AP1814M*	18	14.5	12 to 18	4 to 7	8 to 11	13	2	2	2/1
AP1814D*	18	14.5	16 to 28	8 to 14	8 to 14	16	2	2	2/1
AP1910S	19	10	10 to 11	5 to 5.5	5 to 5.5	11	1	2	2/1
AP1910M	19	10	15.5 to 16	5 to 5.5	11 to 11.5	12	2	2	2/1
AP1910D	19	10	22 to 23	11 to 11.5	11 to 11.5	13	2	2	2/1
AP2112S	21	12	9 to 12	4.5 to 6	4.5 to 6	13	1	2	2/2
AP2112M	21	12	14.5 to 17.5	4.5 to 6	10 to 11.5	14	2	2	2/2
AP2112D	21	12	20 to 23	10 to 11.5	10 to 11.5	15	2	2	2/2
AP2218S*	22	18	6 to 13	3 to 6.5	3 to 6.5	15	1	2	2/2
AP2218M*	22	18	13.5 to 16.5	5 to 6.5	8.5 to 10	17	2	2	2/2
AP2218D*	22	18	17 to 20	8.5 to 10	8.5 to 10	19	2	2	2/2
AP2424S*	24	24	11 to 14	5.7 to 7	5.5 to 7	20	1	4	2/2
AP2424M*	24	24	16 to 19.5	5.5 to 7	10.5 to 12.5	22	4	4	2/2
AP2424D*	24	24	21 to 25	10.5 to 12.5	10.5 to 12.5	24	4	4	2/2

* Indicates Stock Shell

107 N Gold Dr · Robbinsville, NJ 08691 · Phone: (609)259-7004 · Fax: (609)259-8975 · e-mail: sales@ameripack.com

Sheet 1 of 2

Heavy Duty Thermoform Shipping Cases From:



Part #	Length	Width	Heights Variable in 0.25" Increments			Weight	Standard #		
			Total Height	Lid Height	Base Height		Handles	Latches	Hinges/Stays
AP2521S	25.5	21	12 to 15	6 to 7.5	6 to 7.5	18	1	2	2/2
AP2521M	25.5	21	16 to 19.5	6 to 7.5	10 to 12	20	2	2	2/2
AP2521D	25.5	21	20 to 24	10 to 12	10 to 12	22	2	2	2/2
AP2712S	27	12.5	7 to 8.5	3.5 to 4.5	3.5 to 4.5	14	1	2	2/2
AP2712M	27	12.5	10.5 to 12	3.5 to 4.5	7 to 7.5	17	2	2	2/2
AP2712D	27	12.5	14 to 15	7 to 7.5	7 to 7.5	20	2	2	2/2
AP2727D	27	27	14 to 21	7 to 10.5	7 to 10.5	28	4	4	2/2
AP2818S*	28	18	11 to 15	5.5 to 7.5	5.5 to 7.5	20	1	2	2/2
AP2818M*	28	18	14 to 17.5	5.5 to 7.5	8.5 to 10	22	2	2	2/2
AP2818D*	28	18	17 to 20	8.5 to 10	8.5 to 10	24	2	2	2/2
AP2825S	27.5	25	13 to 15	6.5 to 7.5	6.5 to 7.5	26	4	4	2/2
AP2825M	27.5	25	17 to 23	6.5 to 7.5	10.5 to 15.5	29	4	4	2/2
AP2825D	27.5	25	21 to 31	10.5 to 15.5	10.5 to 15.5	32	4	4	2/2
AP3012S	30	12	9 to 12	4.5 to 6	4.5 to 6	16	1	2	2/2
AP3012M	30	12	14.5 to 18	4.5 to 6	10 to 12	18	2	2	2/2
AP3012D	30	12	20 to 24	10 to 12	10 to 12	20	2	2	2/2
AP3018D	30	18	17 to 22	8.5 to 11	8.5 to 11	24	2	2	2/2
AP3120S	31	20	9 to 16	4.5 to 8	4.5 to 8	26	2	2	2/2
AP3122S*	31	22	10 to 14	5 to 7	5 to 7	27	2	2	2/2
AP3122M*	31	22	15 to 19	5 to 7	10 to 12	29	2	2	2/2
AP3122D*	31	22	20 to 24	10 to 12	10 to 12	32	2	2	2/2
AP3214S	32	14	12 to 16	6 to 8	6 to 8	24	2	2	2/2
AP3214M	32	14	14 to 18	6 to 8	8 to 10	26	2	3	3/2
AP3214D	32	14	16 to 20	8 to 10	8 to 10	28	2	3	3/2
AP3418S	34	17	14 to 17	7 to 8.5	7 to 8.5	30	2	3	3/2
AP3424S*	34	24	15 to 21	7.5 to 10.5	7.5 to 10.5	35	4	4	3/2
AP3424M*	34	24	19 to 24.5	7.5 to 10.5	11.5 to 14	38	4	4	3/2
AP3424D*	34	24	23 to 28	11.5 to 14	11.5 to 14	41	4	4	3/2
AP3620D	36	20	20 to 24	10 to 12	10 to 12	36	4	3	3/2
AP4325S*	43	25	8 to 9	4 to 4.5	4 to 4.5	42	4	4	4/2
AP4325M*	43	25	16.5 to 22.5	4 to 4.5/7 to 8.5	12.5 to 13.5	45	4	4	4/2
AP4325D*	43	25	25 to 27	12.5 to 13.5	12.5 to 13.5	48	4	4	4/2

* Indicates Stock Shell

107 N Gold Dr · Robbinsville, NJ 08691 · Phone: (609)259-7004 · Fax: (609)259-8975 · e-mail: sales@ameripack.com

Sheet 2 of 2