



REV	DOCUMENT	CHANGED BY	CHECK
4	0041144	SS 26JUN08	BLR



RELEASE NO. PR-17367	CATALOG LISTING CW-B5541
REPLACES	

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:			DRAWN	JAS	12JUN89	Honeywell				
OPERATING FORCE-----150 GRAMS MAX		CONTACT ARRANGEMENT S P N O					CHECK	JAP	14JUN89					
RELEASE FORCE-----25 GRAMS MIN		L215 15.1A 1/2HP 125, <u>250</u> OR 277 VAC 1/2A 125 VDC 1/4A 250 VDC; 5A 125 VAC "L" 		NO PLACES X ± -			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH, BASIC				
DIFFERENTIAL TRAVEL-----.002-.010				ONE PLACE .X ± 0.030										
OVERTRAVEL-----0.030 MIN				TWO PLACE .XX ± 0.015			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY							
FREE POSITION-----0.675 MAX				THREE PLACE .XXX ± 0.005										
RELEASE TRAVEL-----0.010 MIN				ANGLES X ± -			RASTER			SIZE	TYPE	CAGE CODE	DRAWING NAME	REV
				THIRD ANGLE PROJECTION 						B	I	-	V7-1C27D8-000-1	4
										SCALE		-	SHEET	1 OF 1