



Note: Due to space restrictions, parts are stamped with wattage ratings reduced to the nearest whole number. The actual wattage ratings are as published in this catalog.

Resistance Value
 1R0 = 1.0Ω
 10R = 10.0Ω
 250 = 250Ω
 1K0 = 1,000Ω
 4K5 = 4,500Ω
 51K = 51,000Ω

24 **Ohmite Mfg. Co.** 1600 Golf Rd., Rolling Meadows, IL 60008 • 1-866-9-OHMITE • Int'l 1-847-258-0300 • Fax 1-847-574-7522 • www.ohmite.com • info@ohmite.com

FEATURES

- Prevents severe vibration or mechanical shock to resistor
- Increases resistor wattage up to 100% when mounted on metal surface (1.5 sq. in. by 0.040 in. thick min. per watt dissipated)
- Holes in clip base permit fastening to chassis surface with machine screws, eyelets or rivets
- Sold in bags of ten (10)



Mounting Clip For 90 Series

STANDARD PART NUMBERS FOR 90 SERIES MOUNTING CLIP

Part No.	Resistor rating (watts)	Clip length (in./mm)	Clip width (in./mm)	Clip height (in./mm)	No. of holes	Hole centers (in./mm)	Hole diameter (in./mm)	
✓ 5900	1.5	0.40 / 10.319	0.150 / 3.810	0.250 / 6.350	1		0.71 / 1.803	✚ = Most popular standard values
✓ 5902	2.25	0.35 / 8.890	0.217 / 5.500	0.275 / 6.980	2	0.156 / 3.969	0.71 / 1.803	✓ = Standard values
✚ 5904	3.25	0.50 / 12.700	0.257 / 6.500	0.319 / 8.103	2	0.250 / 6.350	0.093 / 2.362	✚ = Non-standard values subject to minimum handling charge per item
✚ 5906	5.0	0.90 / 22.860	0.237 / 6.019	0.284 / 7.214	2	0.400 / 10.160	0.103 / 2.616	
✚ 5908	11.0	1.75 / 44.450	0.333 / 8.458	0.377 / 9.576	2	0.800 / 20.320	0.103 / 2.616	