



Coil Data at 20 °C	Conditions	Min	Typ	Max	Unit
Coil resistance		180	200	220	Ohm
Coil voltage			5		VDC
Rated power			125		mW
Coil current			25		mA
Thermal resistance	max. Relay temperature = operating temperature + self heating		85		K/W
Inductance			18		mH
Pull-In voltage				3,5	VDC
Drop-Out voltage		0,75			VDC

Contact Data 94	Conditions	Min	Typ	Max	Unit
Contact-material			Rhodium		
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			10	W
Switching voltage	DC or Peak AC			100	V
Switching current	DC or Peak AC			0,2	A
Carry current	DC or Peak AC			0,5	A
Contact resistance static	Measured with 40% overdrive Start Value			150	mOhm
Contact resistance dynamic	Maximum value 1,5 ms after excitation Start Value			200	mOhm
Insulation resistance	RH <45 %, 100 V test voltage	1			GOhm
Breakdown voltage (<21 AT)	according to EN 60255-5	150			VDC
Operate time incl. bounce	measured with 40% overdrive			2	ms
Release time	measured with no coil excitation			2	ms
Capacity	@ 10 kHz across open switch			1,5	pF

Special Product Data	Conditions	Min	Typ	Max	Unit
Dielectric Strength Coil/Contact	according to EN 60255-5	1,5			kV DC
Insulation resistance Coil/Contact	RH <45%, 200 VDC measuring voltage	5			TOhm
Capacity Coil/Contact	@ 10 kHz		0,8		pF
Housing material				epoxy resin	
Connection pins				CuFe2P, tin plated	
Approval				UL File No. NRNT2.E156887, NRNT8.E156887	
Reach / RoHS conformity				yes	



Products for
tomorrow...

Europe: +49 / 7731 8399 0 | Email: info@meder.com
USA: +1 / 508 295 0771 | Email: salesusa@meder.com
Asia: +852 / 2955 1682 | Email: salesasia@meder.com

Item No.:
3205190351
Item:
DIP05-1C90-51Q

Environmental data	Conditions	Min	Typ	Max	Unit
Operating temperature		-20		70	°C
Storage temperature		-35		95	°C
Soldering temperature	wave soldering max. 5 sec.			260	°C
Washability				fully sealed	

General data	Conditions	Min	Typ	Max	Unit
Packaging				tube per 25 pcs.	

Modifications in the sense of technical progress are reserved

Designed at: 09.10.07 Designed by: THAUKE
Last Change at: 20.08.12 Last Change by: THAUKE

Approval at: 10.10.07 Approval by: JHEYDER
Approval at: 23.08.12 Approval by: JHEYDER

Version: 5