

A

B

C

D


A

B

C



D

view shown without plastic pin and grounding



Detail of grounding strip

PC card drilling dimensions(after plating)
(thickness 1.60 ±0.20)



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.21	10.96	D09S81C4GX00	D09S81C6GX00
15	39.14	33.32	26.32	24.54	19.18	D15S81C4GX00	D15S81C6GX00
25	53.03	47.04	40.04	38.25	33.12	D25S81C4GX00	D25S81C6GX00
37	69.32	63.50	56.50	54.71	49.68	D37S81C4GX00	D37S81C6GX00
						Gold flash	0,76 µ gold

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.21	10.96	D09S81C4GX00LF	D09S81C6GX00LF
15	39.14	33.32	26.32	24.54	19.18	D15S81C4GX00LF	D15S81C6GX00LF
25	53.03	47.04	40.04	38.25	33.12	D25S81C4GX00LF	D25S81C6GX00LF
37	69.32	63.50	56.50	54.71	49.68	D37S81C4GX00LF	D37S81C6GX00LF
						Gold flash	0,76 µ gold

rev	ecn no	dr	date
F	-	JOU	2000/09/07
G	LS05-004	MPE	2005/02/14
H	LS06-0097	LGO	2006/07/28
J	LS06-0140	LGO	2006/09/22
-	-	-	-
-	-	-	-
-	-	-	-

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection A3	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED		size	Scale
Dr	PESSON	1996/11/06	ANGULAR LINEAR	0.X	±0.1	ECN LS06-0140
Eng	PESSON	1996/11/06		0.XX	±0.1	
Chr	LEGARE	1996/11/06		0.XXX	±0.1	
Appr	LEGARE	1996/11/06	Product family		D-SUB	Spec ref -
FCI			FEMALE CONNECTOR DELTA D EUROPE			Rev.
			right angled press fit			J
catalog no			C01-8646-0514			sheet 1 of 1