



PART NO.	ENG. NO.	
02-06-1101	1561-(P901)	
02-06-1103	1561-(P901)L	
02-06-5101	1561-(P561)	
02-06-5102	1561-(P561)L	
02-06-5108	1561-(P228)	
02-06-5109	1561-(P228)L	
02-06-5100	1561-(P550)	
02-06-5103	1561-(P550)L	
02-06-5105	1561-(P591)	
02-06-5104	1561-(P591)L	
02-06-1118	1561-1(P901)	
NOT TOOLED	1561-1(P901)L	



SECT. "B-B"
SCALE:10X



SECT. "C-C"
SCALE:10X

LEGEND

1561-*(****)*

BLANK=WITH LOCKING TABS
1=WITHOUT LOCKING TABS

P=PREPLATE
BLANK=POSTPLATE

FORM
BLANK=CHAIN
L=LOOSE

FINISH CODE

NOTES:

1. MATERIAL: BRASS

2. FINISH:

901 HOT TIN DIP (.00051)/.000020 MIN.

228 SELECT GOLD PLATE (.00075)/.000030 MIN. IN CONTACT AREA, SELECT TIN.
(.00250)/.000100 MIN. IN CRIMP AREA OVER (.00125)/.000050 MIN. NICKEL OVERALL.

561 SELECT GOLD PLATE (.00076)/.000030 MIN. IN CONTACT AREA, OVER
(.00127)/.000050 MIN. NICKEL OVERALL.

591 SELECT GOLD PLATE (.00175)/.000050 MIN. IN CONTACT AREA, OVER (.00127)/.000050
MIN. NICKEL OVERALL WITH (.000025)/.000010 MAX. GOLD FLASH OVERALL.


550 SELECT GOLD PLATE (.00038)/.000015 MIN. IN CONTACT AREA, OVER (.00076)/.000030
MIN. NICKEL OVERALL WITH (.000025)/.000010 MAX. GOLD FLASH OVERALL.

* THE PRIMARY SHIPPING CARTON WILL BE LABELED, "COMPLIANT TO
ROHS DIRECTIVE 2004/95/EC AND ANNEX II OF DIRECTIVE 2000/53/EC",
AND CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH
TIN-LEAD."


3. PRODUCT SPECIFICATION: PS-02-06.

4. PACKAGING INFORMATION: NOT AVAILABLE


5. TERMINAL FOR USE WITH (.157)/.062 DIA. SERIES HOUSINGS AND
WILL ACCEPT 18 THRU 24 AWG WIRE WITH (.152/3.05)/.060/.120
INSULATION DIA.





(.25)
MAX.
.010
CARRIER CUTOFF



(.25)
MAX.
.010
CARRIER CUTOFF



(.150/.142)
.059/.056
DIA.



AP	REVISED/REDRAWN UCP2004-2257 RHOLTS 05/14/04
A0	REINSTATE 02065105 UCP2003-1827 ELHAG 03/02/24
AN	OBSOLETE P/N UCR2002-0270 COMERCI 01/9/25
AM1	ADDED ISO VIEW UCR1998-0248 WANG 98-05-21
AM	REV. AND REDRAWN PER ECR 10372 GEP 8-20-87 RW

SEE REVISION BLOCK EC NO: UCP2004-2257 DRW:RHOLTS 2005/03/30 CHKD:FSMITH 2005/03/30 APPR:FSMITH 2005/04/11 AP	DESCRIPTION	QUALITY SYMBOLS ▽ = 0 ◻ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .005 2 PLACES ± 0.13 ± .010 1 PLACE ± 0.25 ± --- ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SCALE 6:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			REVISE ON CAD ONLY	
				DIMENSION STYLE IN/MM		TITLE CRIMP TERMINAL, FEMALE .062 DIA. FOR 18-24 AWG WIRE				
				DRAWN BY DATE GEW 1991/02/19		MOLEX MOLEX INCORPORATED				
				CHECKED BY DATE RW 1991/02/19						
				APPROVED BY DATE GWF 1991/02/19		MATERIAL NO. SEE CHART	DOCUMENT NO. SD-1561-*	SHEET NO. 1 OF 1		
				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						C