


UNLESS OTHERWISE NOTED	
DIMENSIONS ARE IN INCHES	TOLERANCES ARE:
ONE PLACE DECIMALS $\pm .1[2.5]$	THREE PLACE DECIMALS $\pm .005[.127]$
TWO PLACE DECIMALS $\pm .01[.25]$	FOUR PLACE DECIMALS $\pm .0020[.051]$
ANGLES $\pm 2^\circ$	

TITLE: 2MM SOCKET STRIP ASSEMBLY

DWG NO: SQW-1XX-XX-XXX-X-XXX
SHEET 1 OF 1



SECT. "A-A"

FIG. 1






FIG. 2

POLARIZATION OPTION LOCATION
INSERT PK-07-N INTO SPECIFIED
POSITION AND BREAK OFF TAB



NOTES:

- CONTACT PUSHOUT FORCE: .5 LB MIN.
- MAX ALLOWABLE CUT FLASH: .015 [.38] MAX.
- Δ REPRESENTS A CRITICAL DIMENSION.
- MATTE TIN PLATING DOES NOT ENABLE LEAD FREE SURFACE MOUNT PROCESSING

TABLE 2			
ROW SPEC.	NO. OF POS.	PKG TUBE	TUBE PLUG
-D	05-50	PT-1-24-01-22	TP-03
-T	05-50	PT-1-24-06-15	TP-03
-Q	05-50	PT-1-24-15-29	TP-07
-D, -T & -Q	02-04	LAYER PACKAGING	

EXISPROD\ASSEMBLY\2MM
SQW-ASM

santec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: BURREN 8-19-96

SQW-1XX-XX-XXX-X-XXX
SHEET 1 OF 1

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SANTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SANTEC INC.