






MATERIAL NO.	ENGINEERING NO.	LENGTH
1300140037	2R7004A20A120	12' +.75-0 [305mm +19.0-0]
1300140042	2R7004A20F060	6'0" +2.19-0 [1.8M +55.6-0]



1	WHITE/BLACK
2	BLACK
3	WHITE
4	RED
5	ORANGE
6	BLUE
7	GREEN/YELLOW-GND

- NOTES:
- 1. MATERIAL: SEE TABLE
 - 2. FINISHES: SEE TABLE
 - 3. MATES WITH: 7/C MINI-CHANGE CORD ASSY.
 - 4. ELECTRICAL SPECIFICATIONS:
 - VOLTAGE RATING: 600V AC/DC
 - CURRENT RATING: 8 AMPS
 - 5. RoHS COMPLIANT

7	1	LABEL	PLASTIC FILM	BLACK/YELLOW
6	1	POTTING	EPOXY	
5	7	WIRE, 16 AWG (UL 1015)	PVC INSULATED	SEE WIRE DIAGRAM
4	7	SOCKET SLEEVE	ST. STEEL	
3	7	CONTACT SOCKET	BRASS	GOLD PLATED
2	1	INSERT	PVC	YELLOW
1	1	RECEPTACLE SHELL	ZINC ALLOY	E-COAT, BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

RELEASED
EC NO: WNA2009-0813
DRWN: BRUPERT
CHKD: BRUPERT
APPR: J. MURPHY

2009/06/09
2009/06/10

QUALITY SYMBOLS
=0
=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .005	± .0005
2 PLACES	± .005	± .0005
1 PLACE	± .005	± .0005

ANGULAR ± 1/2°

DRAFT WHERE APPLICABLE
MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY
BRUPERT

CHECKED BY
B. WOODMAN

APPROVED BY
J. MURPHY

MATERIAL NO.
SEE CHART

DATE
06/05/2009

DATE
06/05/2009

DATE
06/05/2009

SCALE
1:1

DESIGN UNITS
INCH

THIRD ANGLE PROJECTION

TITLE
MINI-CHANGE RECEPTACLE
FEMALE, 7 POLE
1/2 IN NPT

MOLEX INCORPORATED

DOCUMENT NO.
SD-130014-006

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION