

Tri-State Enable/Disable 5.0V Oscillator



Model: F5C-2ELF

RoHS Compliant / Pb Free

Rev. 10/24/2011

http://www.foxonline.com/need_a_sample.htm

Need a
Sample®

FEATURES

- 5.0V Operationg
- HCMOS/TTL Output
- Tri-State Enable/Disable
- 14-Pin DIP

OPTIONS

- 8-Pin DIP Available (H5C-2ELF)

• PART NUMBER SELECTION [Learn More](#) - Internet Required

Part Number	Model Number	Frequency Stability ¹	Operating Temperature (°C)	Frequency Range (MHz)
147LF-Freq-xxxxx	F5C-2ELF	±100PPM	0 ~ +70	1.500 ~ 59.000
326LF-Freq-xxxxx	F5C-2ERLF	±100PPM	-40 ~ +85	1.500 ~ 59.000
180LF-Freq-xxxxx	F6C-2ELF	±50PPM	0 ~ +70	1.500 ~ 59.000


• ELECTRICAL CHARACTERISTICS

PARAMETERS	MAX (unless otherwise noted)
Frequency Range (Fo)	1.500 ~ 59.000 MHz
Storage Temperature Range (T _{STG})	-55°C ~ +125°C
Supply Voltage (V _{DD})	5.0V ± 10%
Input Current (I _{DD})	
1.500 ~ 40.000 MHz	40mA
40.000+ ~ 59.000 MHz	60mA
Output Symmetry (50% V _{DD})	
1.500 ~ 50.000 MHz	45% ~ 55%
50.000+ ~ 59.000 MHz	40% ~ 60%
Rise Time (10% ~ 90% V _{DD}) (T _r)	
1.500 ~ 59.000 MHz	10 nS
Fall Time (90% ~ 10% V _{DD}) (T _f)	
1.500 ~ 59.000 MHz	10 nS
Output Voltage (V _{OL})	10% V _{DD}
(V _{OH})	90% V _{DD} Min
Output Current (I _{OL})	16mA Min
(I _{OH})	-16mA Min
Output Load	
TTL	10TTL
HCMOS	50pF
Start-up Time (T _s)	10mS
Output Enable/Disable Time ²	100nS

¹ Inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, aging, shock, and vibration.

² An internal pullup resistor from pin 1 to V_{DD} allows active output if pin 1 is left open.

All specifications subject to change without notice.



• ENABLE / DISABLE FUNCTION

INH (Pin 1)	OUTPUT (Pin 8)
OPEN ²	ACTIVE
'1' Level V _{IH} ≥ 2.2 V	ACTIVE
'0' Level V _{IL} ≤ 0.8 V	High Z

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fox:

[F5C2ELF-3200](#) [F5C2ELF-2000](#) [F5C2ELF-1600](#) [F5C2ELF-4000](#) [F5C2ELF-1000](#) [F5C2ELF-2400](#) [F5C2ELF-2500](#)
[F5C2ELF-1200](#)