




		1			2									3		4	
PRODUCT NR:		CONFIGURATION												DIM A	PCB THICKNESS		
	ROW#	1	2	3	4	5	6	7	8	9	10	11	12				
85868-X01	D	-	X	X	X	-	X	-	X	-	X	-	X	2.90	1.6		
	C	X	-	X	-	X	-	X	-	X	-	X	-				
85868-X01LF	B	-	X	X	X	-	X	-	X	-	X	-	X	2.90	1.6		
	A	X	-	X	-	X	-	X	-	X	-	X	-				
85868-X02	D	X	-	X	-	X	-	X	-	X	-	X	-	2.90	1.6		
	C	-	X	-	X	-	X	-	X	-	X	-	X				
85868-X02LF	B	X	-	X	-	X	-	X	-	X	-	X	-	2.90	1.6		
	A	-	X	-	X	-	X	-	X	-	X	-	X				
85868-X03	D	X	X	X	X	X	X	-	X	X	X	-	X	2.90	1.6		
	C	X	X	X	X	X	X	-	X	X	X	-	X				
85868-X03LF	B	X	X	X	X	X	X	-	X	X	X	-	X	2.90	1.6		
	A	X	X	X	X	X	X	-	X	X	X	-	X				

"-" POSITION NOT LOADED
 "X" POSITION LOADED




PRODUCT AFTER PC BOARD APPLICATION.

PC BOARD THICKNESS ±0.20
 SEE TABLE

NOTES:

- BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
- TERMINAL MATERIAL: PHOSPHOR BRONZE.
- PLATING SOLDER TAILS 2-8 μm SnPb 90-97.
OR 2-8 μm PURE Sn FOR PART NUMBER WITH LF SUFFIX.
- INDICATED HOLES ARE UNPLATED.
- PRODUCT MARKING: PART NUMBER & BATCH ID.
- DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260 DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL



RECOMMENDED HOLE PATTERN,
 COMPONENT SIDE.



mat'l code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
l'tecn	ndr	date	linear	projection	title	product family	code
H	T03-0430	Jeff	030926		4R RA RECEPTACLE	SIG24mm PRESS PEG	213
J	D604-0012	Clu	040225				1 of 3
K	D605-0061	Clu	050328				
L	D606-0478	Cenh	11/23/06	dir	Il. de Bil	980109	
M	D607-0169	Cenh	05/15/07	engr	P. Schalk	980109	
N	D608-0171	TER	8/26/08	chr	P. Schalk	980109	
P	D609-0068	Cenh	06/06/09	app	P. Schalk	980109	
sheet	revision	P	P				
index	sheet	1	2	3			

Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite de FCI BV.
All rights strictly reserved. Reproduction or issue to third parties in any form without written authority from the proprietor.
Property of FCI BV.
© FCI BV.





1					2									3 4				
PRODUCT NR:	ROW#	CONFIGURATION												DIM A	PCB THICKNESS			
		1	2	3	4	5	6	7	8	9	10	11	12					
85868-X20 85868-X20LF	D	X	-	X	-	X	-	X	-	X	-	X	-	2.90	1.6			
	C	X	-	-	X	-	X	-	X	-	X	-	X					
	B	X	-	X	-	X	-	X	-	X	-	X	-			X		
	A	X	-	-	X	-	X	-	X	-	X	-	X			-	X	
85868-X21 85868-X21LF	D	X	-	X	-	X	-	X	-	X	-	X	-	2.90	1.6			
	C	-	X	-	X	-	X	-	X	-	X	-	X			-	X	
	B	X	-	X	-	X	-	X	-	X	-	X	-			X	-	X
	A	-	X	-	X	-	X	-	X	-	X	-	X			-	X	-
85868-X22 85868-X22LF	D	X	X	X	X	X	X	-	X	X	X	-	X	2.90	1.6			
	C	X	X	X	X	X	X	-	X	X	X	-	X			-	X	
	B	X	X	X	X	X	X	-	X	X	X	-	X			-	X	
	A	X	X	X	X	X	X	-	X	X	X	X	-			X	-	X
85868-X23 85868-X23LF	D	-	X	X	X	-	X	-	X	-	X	-	X	2.90	1.6			
	C	X	-	X	-	X	-	X	-	X	-	X	-			X	-	X
	B	-	X	X	X	-	X	-	X	-	X	-	X			-	X	
	A	X	-	X	-	X	-	X	-	X	-	X	-			X	-	X
85868-X24 85868-X24LF	D	X	-	X	-	X	-	X	-	X	-	X	-	3.53	2.4			
	C	X	-	-	X	-	X	-	X	-	X	-	X			-	X	
	B	X	-	X	-	X	-	X	-	X	-	X	-			X	-	X
	A	X	-	-	X	-	X	-	X	-	X	-	X			-	X	


"-" POSITION NOT LOADED
"X" POSITION LOADED



PC BOARD THICKNESS ±0.20
SEE TABLE




- NOTES:
- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
 - 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - 3 PLATING SOLDER TAILS 2-8 μ m SnPb 90-97 OR PURE Sn FOR WITH LF SUFFIX.
 - 4 INDICATED HOLES ARE UNPLATED.
 - 5 PRODUCT MARKING: PART NUMBER & BATCH ID.
 - 6 SET BACK FOR PRESS BLOCK.
 - 7 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
 - 8 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
 - 9 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - 10 THE HOUSING WILL WITHSTAND EXPOSURE TO 245 DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.



14.64 REF. SEE NOTE 6

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL






RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

nat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
l	tr	ec	n	n	dr	date	
linear		projection		title		www.fciconnection	
angles		product family		METAL (tm)		code	
dr		D. de Bil		980220		213	
engr		P. Schalk		980220		sheet	
chr		P. Schalk		980220		2 of -	
app		P. Schalk		980220			
sheet	revision	scale		5:1			
index	sheet						


1					2								3		4	
PRODUCT NR:		CONFIGURATION												DIM A	PCB THICKNESS	
	ROW#	1	2	3	4	5	6	7	8	9	10	11	12			
85868-X30 85868-X30LF	D	X	-	X	-	X	-	X	-	X	-	X	-	X	2.90	1.6
	C	X	-	-	X	-	X	-	X	-	X	-	X			
	B	X	-	X	-	X	-	X	-	X	-	X	-			
	A	X	-	-	X	-	X	-	X	-	X	-	X			
85868-X31 85868-X31LF	D	X	-	X	-	X	-	X	-	X	-	X	-	X	2.90	1.6
	C	-	X	-	X	-	X	-	X	-	X	-	X			
	B	X	-	X	-	X	-	X	-	X	-	X	-			
	A	-	X	-	X	-	X	-	X	-	X	-	X			
85868-X32 85868-X32LF	D	X	X	X	X	X	X	-	X	X	X	-	X	2.90	1.6	
	C	X	X	X	X	X	X	-	X	X	X	-	X			
	B	X	X	X	X	X	X	-	X	X	X	-	X			
	A	X	X	X	X	X	X	-	X	X	X	-	X			
85868-X33 85868-X33LF	D	-	X	X	X	-	X	-	X	-	X	-	X	2.90	1.6	
	C	X	-	X	-	X	-	X	-	X	-	X	-			
	B	-	X	X	X	-	X	-	X	-	X	-	X			
	A	X	-	X	-	X	-	X	-	X	-	X	-			

"-" POSITION NOT LOADED
 "X" POSITION LOADED



PRODUCT AFTER PC BOARD APPLICATION.


PC BOARD THICKNESS ±0.20



NOTES:

- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 PLATING SOLDER TAILS 2-8 μ m SnPb 90-97.
OR 2-8 μ m PURE Sn FOR PART NUMBER WITH LF SUFFIX.
- 4 INDICATED HOLES ARE UNPLATED.
- 5 PRODUCT MARKING: PART NUMBER & BATCH ID.
- 6 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
- 7 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 8 THE HOUSING WILL WITHSTAND EXPOSURE TO 260 DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		F.C.I.	
l	tr	ec	n	dr	date	linear	projection
P						angles	mm
dr	Heaven Cen	11/23/06					
engr	Collins Lu	11/23/06					
chr	Beer Fu	11/23/06					
app	Joseph Hsia	11/23/06					
sheet	revision					scale	5:1
index	sheet						
title		product family		code		size	
4R RA RECEPTACLE		METAL (tm)		213		3 of 3	
SIG24mm PRESS PEG		A2		85868			