

# FL SWITCH LM 8TX

Order No.: 2832632



<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=2832632>

Ethernet lean managed switches with eight RJ45 ports, 10/100 Mbps, with auto crossing and auto negotiation, SNMP management (Simple Network Management Protocol), redundancy via Rapid Spanning Tree (IEEE 802.1w) and Fast Ring Detection, multicast filtering, VLAN, IGMP snooping, 24 V DC power supply, redundant

## Commercial data

|                          |                   |
|--------------------------|-------------------|
| EAN                      | 4 046356 078382   |
| Pack                     | 1                 |
| Customs tariff           | 85176200          |
| Country of Origin        | DE                |
| Catalog page information | Page 95 (AX-2011) |

## Product notes

WEEE/RoHS-compliant since:  
11/02/2008



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

## Product description

The compact lean managed switches (LM) make it possible to set up flexible and economical managed Ethernet networks in an automation environment. Its huge range of connection variants and extended temperature range of -40 °C to +70 °C enable it to perfectly cover the requirements of industrial applications. The integrated software allows networks to be redundantly set up, diagnosed and monitored using IT standard protocols.

## Technical data

### Interfaces

|                      |                                                          |
|----------------------|----------------------------------------------------------|
| Interface 1          | Ethernet                                                 |
| No. of ports         | 8 (RJ45 ports)                                           |
| Connection method    | RJ45 female connector, auto negotiation                  |
| Transmission physics | Copper                                                   |
| Transmission speed   | 10/100 MBit/s                                            |
| Interface 2          | Serial RS-232                                            |
| Connection method    | V.24 (RS-232-C), 6-pos. MINI-DIN female connector (PS/2) |
| Interface 3          | Serial (V.24 (RS-232))                                   |
| Connection method    | V.24 (RS-232-C), 6-pos. MINI-DIN female connector (PS/2) |

### Function

|                                  |                                                                                                                                                                                                                                              |
|----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Basic functions                  | Store and forward switch complies with IEEE 802.3 2 priority classes in acc. with IEEE802.1 P TCP/IP protocol, BootP-capable, port mirroring, integrated web server function, multicast filtering, IGMP snooping, Rapid Spanning Tree (RSTP) |
| Supported browsers               | Internet Explorer 5.5 or higher                                                                                                                                                                                                              |
| Redundancy                       | Rapid Spanning Tree 802.1w, Fast Ring Detection                                                                                                                                                                                              |
| Status and diagnostic indicators | Per Ethernet 2 status LEDs: LINK and status activity, 100, full duplex, supply voltage $U_{S1}$ and $U_{S2}$ (redundant supply voltage)                                                                                                      |

### Network expansion parameters

|                                          |                                          |
|------------------------------------------|------------------------------------------|
| Cascading depth                          | Network, linear, and star structure: any |
| Maximum conductor length ((twisted pair) | 100 m                                    |

### Supply voltage

|                             |                                                          |
|-----------------------------|----------------------------------------------------------|
| Supply voltage              | 24 V DC                                                  |
| Residual ripple             | 3.6 V <sub>PP</sub> (within the permitted voltage range) |
| Supply voltage range        | 18.5 V DC ... 30.5 V DC                                  |
| Typical current consumption | 250 mA (at $U_S = 24$ V DC)                              |

### General data

|               |                |
|---------------|----------------|
| Width         | 45 mm          |
| Height        | 99 mm          |
| Depth         | 112 mm         |
| Mounting type | DIN rail       |
| Type AX       | Block-oriented |

|                                          |                                           |
|------------------------------------------|-------------------------------------------|
| Weight                                   | 230 g                                     |
| Degree of protection                     | IP20                                      |
| Ambient temperature (operation)          | -40 °C ... 70 °C                          |
| Ambient temperature (storage/transport)  | -40 °C ... 85 °C                          |
| Permissible humidity (operation)         | 30 % ... 95 % (no condensation)           |
| Permissible humidity (storage/transport) | 30 % ... 95 % (no condensation)           |
| Air pressure (operation)                 | 80 kPa ... 108 kPa (2000 above sea level) |
| Air pressure (storage/transport)         | 70 kPa ... 108 kPa (3000 above sea level) |
| Noise emission                           | EN 61000-6-3/-4                           |
| Noise immunity                           | EN 61000-6-2:2005                         |

#### Conformity with EMC directives

|                                 |                                                    |
|---------------------------------|----------------------------------------------------|
| Developed in acc. with standard | IEC 61000-6.2                                      |
| Test standard                   | IEC 61000-4-2 (ESD)                                |
| Test result                     | Criterion B                                        |
| Test standard                   | IEC 61000-4-3 (immunity to radiated interference)  |
| Test result                     | Criterion A                                        |
| Test standard                   | IEC 61000-4-4 (burst)                              |
| Test result                     | Criterion B                                        |
| Test standard                   | IEC 61000-4-5 (surge)                              |
| Test result                     | Criterion B                                        |
| Test standard                   | IEC 61000-4-6 (immunity to conducted interference) |
| Test result                     | Criterion A                                        |
| Test standard                   | EN 60068-2-30                                      |

#### Certificates



Certification

BV, CUL, DNV, GL, UL

## Accessories

| Item                   | Designation         | Description                                                                                                                                                                                                                               |
|------------------------|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Cable/conductor</b> |                     |                                                                                                                                                                                                                                           |
| 2832250                | FL CAT5 PATCH 0,3   | Patch cable, CAT5, assembled, 0.3 m                                                                                                                                                                                                       |
| 2832263                | FL CAT5 PATCH 0,5   | Patch cable, CAT5, assembled, 0.5 m                                                                                                                                                                                                       |
| 2832276                | FL CAT5 PATCH 1,0   | Patch cable, CAT5, assembled, 1.0 m                                                                                                                                                                                                       |
| 2832221                | FL CAT5 PATCH 1,5   | Patch cable, CAT5, assembled, 1.5 m                                                                                                                                                                                                       |
| 2832629                | FL CAT5 PATCH 10,0  | Patch cable, CAT5, assembled, 10.0 m                                                                                                                                                                                                      |
| 2832289                | FL CAT5 PATCH 2,0   | Patch cable, CAT5, assembled, 2.0 m                                                                                                                                                                                                       |
| 2832292                | FL CAT5 PATCH 3,0   | Patch cable, CAT5, assembled, 3.0 m                                                                                                                                                                                                       |
| 2832580                | FL CAT5 PATCH 5,0   | Patch cable, CAT5, assembled, 5.0 m                                                                                                                                                                                                       |
| 2832616                | FL CAT5 PATCH 7,5   | Patch cable, CAT5, assembled, 7.5 m                                                                                                                                                                                                       |
| 2891369                | FL CAT6 PATCH 12,5  | Patch cable, CAT6, pre-assembled, 12.5 m                                                                                                                                                                                                  |
| 2891372                | FL CAT6 PATCH 15,0  | Patch cable, CAT6, pre-assembled, 15.0 m                                                                                                                                                                                                  |
| 2891576                | FL CAT6 PATCH 20,0  | Patch cable, CAT6, pre-assembled, 20.0 m                                                                                                                                                                                                  |
| 2730611                | PRG CAB MINI DIN    | Connection cable, to connect Remote Field Controllers to a PC (RS-232) for PC WORX, 3 m in length                                                                                                                                         |
| <b>General</b>         |                     |                                                                                                                                                                                                                                           |
| 0800886                | E/NS 35 N           | End clamp, width: 9.5 mm, color: gray                                                                                                                                                                                                     |
| 2891165                | FL PF 2TX CAT5E     | Patch field with two RJ45 CAT5e network connections                                                                                                                                                                                       |
| 2891178                | FL PF 8TX CAT5E     | Patch field with eight RJ45 CAT5e network connections                                                                                                                                                                                     |
| 2832991                | FL RJ45 PROTECT CAP | Dust protection caps for RJ45 female connector                                                                                                                                                                                            |
| <b>Plug/Adapter</b>    |                     |                                                                                                                                                                                                                                           |
| 2744571                | FL PLUG RJ45 GN/2   | RJ45 connector, shielded, with bend protection sleeve, 2 pieces, green for crossed cables, for assembly on site. For connections that are crossed, it is recommended that the connector set with green bend protection sleeves is used.   |
| 2744856                | FL PLUG RJ45 GR/2   | RJ45 connector, shielded, with bend protection sleeve, 2 pieces, gray for straight cables, for assembly on site. For connections that are not crossed, it is recommended that you use the connector set with gray bend protection sleeve. |
| <b>Software</b>        |                     |                                                                                                                                                                                                                                           |
| 2832166                | FL SNMP OPC SERVER  | SNMP-OPC server, German and English, for monitoring and configuration of SNMP-capable equipment in HMI and SCADA systems                                                                                                                  |
| 2831044                | FL SWT              | Factory Manager, multilingual, configuration and diagnostics software for ETHERNET networks in automation                                                                                                                                 |

**Tools**

|         |              |                                                                                           |
|---------|--------------|-------------------------------------------------------------------------------------------|
| 2744869 | FL CRIMPTOOL | Crimping pliers, for assembling the RJ45 connectors FL PLUG RJ45..., for assembly on site |
|---------|--------------|-------------------------------------------------------------------------------------------|

**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford / Shropshire / TF7 4PG, England  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.  
Technical modifications reserved;