

### Toshiba Mobile Display Co., Ltd

# 10.4 TYPE COLOR TFT-LCD MODULE LT104AC54100 (p-Si TFT)

All information is subject to change without notice. Please read bottom notes.

#### **RoHS** compatible

FEATURES: (1) 10.4 VGA color display with High Luminance (400cd/m²)

(2) Wide Viewing Angle (Vertical:120°, Horizontal:140°)


(3) Built in Long Life Lamps (MTTF:50,000h)

(4) Replaceable structure of lamp unit

## **Specification**

#### **TENTATIVE**

Display size	10.4type(26cm)
Number of Pixels	640(W) X 480(H) (VGA)
Display Mode	TFT-LCD (Transmissive type, Normally-White)
Pixel Pitch (mm)	0.33(W) X 0.33(H)
Luminance (typ.)	400cd/m <sup>2</sup> at $I_{FL}$ = 6.0mA(rms)
Response Time (typ.)	T <sub>ON</sub> =8ms, T <sub>OFF</sub> =17ms
Contrast (typ.)	500
Viewing Angle (CR≥10)	Vertical: (120) degrees, Horizontal: (140) degrees
I/F Format & Supply voltage	CMOS RGB 6bit, H/V sync+DE, V <sub>DD</sub> =3.3V or 5.0V
Operating Temperature	-20 to 70 degree C
Outline dimension (mm)	238.5(W) X 177.5(H) X 12.0max.(D)mm
Weight (approximately)	(550)G
Backlight	Sidelight (2 CCFLs)
Power Consumption	(6.4)W (Except the efficiency of FL inverter)



Rev.0.1R (2010/01/19)

<sup>\*</sup>The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by Toshiba Mobile Display Co., Ltd or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Toshiba Mobile Display Co., Ltd or others. \*The information contained herein may be changed without prior notice. It is therefore advisable to contact Toshiba Mobile Display Co., Ltd before proceeding with the design of equipment incorporating this product.