

LED-25-8V/12V/24V DC P

Standards


Converter meets CE standard
UL class 2 recognized component
File # E164062

Available Versions

901025008P-LED 25 8V DC P
901025012P-LED 25 12V DC P
901025024P-LED 25 24V DC P

Mechanical and Thermal

Dimensions (mm) 30.5 x 40 x 133
Dimensions (in.) 1.2 x 1.57 x 5.24
Weight 300 grams, 10.58 ounces
Tc Max 90°C
Ta Max 50°C
Aluminium casing
Output wire 0.75mm²/18 AWG Teflon
Input wire 0.75mm²/18 AWG 300V
180°C/200°C
Waterproof potting



Electrical

Load 1-25VA
Input 100-277V 0/50/60Hz
Output Voltage (Max. load) 8V/12V/24VDC
Efficiency 80%
EMC (RFI) FCC Class B/EN 55015
Harmonics EN 61000-3-2
Electrostatic Discharge IEC61000-4-2
EMC Immunity IEC61000-4-3
Burst IEC61000-4-4
Surge IEC61000-4-5
Injected RF IEC61000-4-6
Mains interruption IEC61000-4-11
Immunity EN 61547/61047
Safety EN 61347-2-2
SELV

Protection and Regulation

Electronic internal resettable short circuit protection.
Overload and thermal regulation.
Voltage Regulation.

See reverse side for more information →





LIGHTTECH™
WWW.LIGHTTECHINC.COM

www.lighttechinc.com

SPECIFICATIONS

LED-25-8V/12V/24V DC P

Mounting Instructions



Safety Instructions:

1. Always disconnect power before installation and/or removal of the unit.
2. Install in accordance with national and local electrical codes.
3. Wires: Input and output wires 0.75mm² or 18AWG.