

INTERCONNECTS

SERIES 335, 364, 435, 464 • .100" GRID (.018" DIA. PINS), LOW PROFILE • SINGLE AND DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3





FIG. 4

- Series 335 and 435 single and double row PCB interconnects offer a .070" profile, the lowest available
- Series 364 and 464 single and double row PCB interconnects offer .085" profile above board
- Series 335 and 435 use MM #3516 pins. See page 212 for details
- Series 364 and 464 use MM #6458 pins. See page 213 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 335...160	Single Row .070" Profile Pin Header
	335-XX-1	-00-160000 Specify number of pins 01-32
FIG. 2	Series 435...160	Double Row .070" Profile Pin Header
	435-XX-2	-00-160000 Specify number of pins 04-72
FIG. 3	Series 364...580	Single Row .085" Profile Pin Header
	364-10-1	-00-580000 Specify number of pins 01-32
FIG. 4	Series 464...580	Double Row .085" Profile Pin Header
	464-10-2	-00-580000 Specify number of pins 04-72
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264		
SPECIFY PLATING CODE XX=		
Pin Plating	10	90
	10 μ " Au	200 μ " Sn/Pb
		40
		200 μ " Sn

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[335-90-104-00-160000](#) [435-90-272-00-160000](#) [335-90-132-00-160000](#) [335-90-120-00-160000](#) [435-90-226-00-160000](#) [464-10-272-00-580000](#) [464-10-206-00-580000](#) [435-40-272-00-160000](#) [335-40-132-00-160000](#) [335-10-132-00-160000](#) [335-10-111-00-160000](#) [335-10-112-00-160000](#) [435-10-272-00-160000](#) [464-10-212-00-580000](#) [364-10-132-00-580000](#) [435-40-224-00-160000](#) [335-40-113-00-160000](#) [335-40-104-00-160000](#) [0464-0-15-00-00-00-04-0](#)
[0464-0-15-15-10-14-04-0](#)