



North America: Danboro, PA • E-mail: info@pemnet.com • Tel: +1-215-766-8853

Europe: Galway, Ireland • E-mail: europe@pemnet.com • Tel: +353-91-751714

Asia/Pacific: Singapore • E-mail: singapore@pemnet.com • Tel: +65-6-745-0660
Shanghai, China • E-mail: china@pemnet.com • Tel: +86-21-5868-3688

Part # STKB-256-10, Molded-in Threaded Inserts, Thru-Threaded, Knurled - Unified

- Uniform knurl diameter reduces the risk of sink marks.
- Available in varying lengths for injection molding assemblies.
- Aluminum inserts ideal for light weight designs.
- Aluminum and stainless steel inserts offer lead-free alternative.



Specifications


Thread Size .086-56 (#2-56)

Type STKB

Thread Code¹ 256

Length Code 10

L - Length ± .005 .312 in



E Nom. .156 in

Minor Dia.Min. .067 in

Minor Dia.Max.	.0737 in
Thread Specification	2B per ASME B1.1
Standard Material	Free-machining, Leaded Brass
Standard Finish	Plain
CAD Supplier	PennEngineering® (SI®)

¹ Thread tapped thru, Class 3A/4h screw must pass with finger torque, but basic go gauge may stop at last thread.