




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		K	REVISED PER ECR-12-013445	09NOV12	KH	PD


- 1
- CONTINUOUS STRIP ON REELS
- 2
- ACCEPTS #14#10 AWG OR TWO #14's WIRE SIZES, CRIMP WIDTH, .140, F TYPE
- 3
- INSULATION RANGE IS .225-.275 DIA OR TWO AT .140 MAX. CRIMP WIDTH, .310, F TYPE
- 4
- MATING TAB THK IS .032±.001.



SECTION C-C



SECTION A-A



SECTION B-B

-	60635-3
.000150 MIN SILVER	60635-2
TIN	60635-1
FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH	27JUN02	 TE Connectivity						
		CHK P DESANTIS	28JUN02							
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD P DESANTIS	28JUN02	NAME RECEPTACLE, FASTON, .250 SERIES —						
	0 PLC ± —	PRODUCT SPEC								
	1 PLC ± —	—								
	2 PLC ± —	APPLICATION SPEC								
	3 PLC ± .010	—								
	4 PLC ± —			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL	FINISH	WEIGHT	—	A2	00779	C=60635	—			
BRASS	SEE TABLE	CUSTOMER DRAWING			SCALE	8:1	SHEET	1 of 1	REV	K