






P.C. MOUNTING



ISOMETRIC



| O.P. (MM)  | P.T. (MM) |
|------------|-----------|
| 14.7 ± 0.5 | 2.0 MAX.  |

O.P. = OPERATING POINT  
P.T. = PRE-TRAVEL

COM   NO  
CIRCUIT: SPST  
NORMALLY OPEN

## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X ± 0.4  
X.XX ± 0.25
3. RATING: 15A @125/250VAC UL, CUL, VDE APPROVED
4. OPERATING FORCE: 100 ± 30 GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP. 
8. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
9. DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI-OHMS MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2002/95/EC (ROHS) COMPLIANT 



|     |        |                         |          |    |
|-----|--------|-------------------------|----------|----|
| C   | 15632  | CHANGES NOTED           | 12/21/05 | PH |
| B   | 15554  | EDIT CIRCUIT LAYOUT     | 11/21/05 | PH |
| A   | 15226  | RELEASED FOR PRODUCTION | 8/31/05  | PH |
| REV | PCR NO | DESCRIPTION             | DATE     | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

**E-SWITCH®**

TITLE LS0851500F100V2C

SCALE 1.5:1

DATE 8/31/2005

DR PH

DWG Q950018

REV C