





TJG112711

REV	ECN	APP'D
-	6321	JT 2/5/09

INDEXING
INDICATORMARKING
COLOR: WHITE

NOTES:

1. MODULE MEETS ALL REQUIREMENTS OF SAE-AS81714/27, CLASS D, EXCEPT AS SHOWN.
2. MODULE ASSEMBLY CONSTRUCTION:
 - A. HOUSING - POLYETHERIMIDE, COLOR: BLACK.
 - B. SEALING GROMMET - SILICONE PER A-A-59588, COLOR: BLUE.
 - C. INTERNAL SOCKET CONTACTS - COPPER ALLOY, GOLD PLATED PER MIL-G-45204, TYPE I, GRADE C, CLASS 1.
 - D. STUD - COPPER ALLOY, GOLD PLATED.
3. MODULE MARKING AND IDENTIFICATION IS FLUSH WITH SURFACES, COLOR: WHITE.
4. RECOMMENDED EXTERNAL PIN CONTACT SERVICE TOOLS -
 - A. CRIMP TOOL #M22520/1-101 WITH POSITIONER #M22520/1-02.
 - B. INSTALLING/REMOVAL TOOL #M81969/14-04, APCD #CNA078003.
5. MODULE ACCEPTS -
 - A. MATING PIN CONTACTS #M39029/1-103, APCD #CNP072000
 - B. SEALING PLUGS #MS27488-12, APCD #CNA032403
6. (9) PIN CONTACTS AND SEALING PLUGS SUPPLIED WITH EACH MODULE.
7. MOUNTING HARDWARE SUPPLIED WITH EACH MODULE -
 - (2) FLAT WASHERS PER AN-960-C-10L
 - (1) LOCK WASHER PER MS35338-138
 - (1) NUT PER MS35650-304

DIMENSIONS		TOLERANCES		PROJECTION		TITLE	
ANSI Y14.5M		.XX ± 0.01				TERMINAL JUNCTION GROUNDING MODULE, SIZE 12, CLASS D STAINLESS STEEL HARDWARE	
UNITS: INCHES		.XXX ± 0.005					
Pro/E FILE		ANGLES ± 2.0 °		ENGR			
				M. DiGIACOMO 1/26/09			
ORIGINAL 		THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC., BEVERLY, MA		CHKD		SIZE	
				 2/5/09		DWG NO.	
				APPD		B	
				 2/5/09		TJG112711	
						REV	
						-	
						CODE: 58982	
						SCALE: 2.000	
						SHEET 1 OF 1	