

TENMA®


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART, CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1355	A	RELEASED	JWM	1/2/04	HO	1/14/04	JC	1/23/04

**NOTES:**

1. Rating: 1,200V, 12 Amps AC/DC
2. Materials:
Body-Polyamide (Nylon)
Plug - Bronze & Brass Nickel Plated
3. Lead Wire:
Jacket - Flexible PVC, Black
Conductor: 0.75mm²
4. Temperature: -20°C ~ +80°C
5. Internal Resistance: 20 milliohms

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:	DATE:
Jeff McVicker	1/2/04
CHECKED BY:	DATE:
Hisham Odish	1/14/04
APPROVED BY:	DATE:
John Cole	1/23/04

DRAWING TITLE:			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	76-120	84N2157.dwg	A
SCALE: NTS		U.O.M.: INCHES [mm]	SHEET: 1 OF 1