




4



3

2

1

| LOC | DIST | REVISIONS |     |             |      |     |      |
|-----|------|-----------|-----|-------------|------|-----|------|
|     |      | P         | LTR | DESCRIPTION | DATE | DWN | APVD |
| A1  | -    |           | -   | SEE SHEET 1 | -    | -   | -    |
|     |      |           |     |             |      |     |      |
|     |      |           |     |             |      |     |      |
|     |      |           |     |             |      |     |      |

| POS.<br>PER<br>ROW | L<br>-0.8 | PART - NO.    |    | POS.<br>PER<br>ROW | L<br>-0.8 | PART - NO. |    |
|--------------------|-----------|---------------|----|--------------------|-----------|------------|----|
| -                  | -         | -             | -  | 26                 | 66.04     | 7-         | -6 |
| 2                  | 5.08      | 5-            | -2 | 27                 | 68.58     | 7-         | -7 |
| 3                  | 7.62      | 5-            | -3 | 28                 | 71.12     | 7-         | -8 |
| 4                  | 10.16     | 5-            | -4 | 29                 | 73.66     | 7-         | -9 |
| 5                  | 12.70     | 5-            | -5 | 30                 | 76.20     | 8-         | -0 |
| 6                  | 15.24     | 5-            | -6 | 31                 | 78.74     | 8-         | -1 |
| 7                  | 17.78     | 5-            | -7 | 32                 | 81.28     | 8-         | -2 |
| 8                  | 20.32     | 5-            | -8 | 33                 | 83.82     | 8-         | -3 |
| 9                  | 22.86     | 5-825 492-9/2 | 34 | 86.36              | 8-        | -4         |    |
| 10                 | 25.40     | 6-            | -0 | 35                 | 88.90     | 8-         | -5 |
| 11                 | 27.94     | 6-            | -1 | 36                 | 91.44     | 8-         | -6 |
| 12                 | 30.48     | 6-            | -2 | 37                 | 93.98     | 8-         | -7 |
| 13                 | 33.02     | 6-            | -3 | 38                 | 96.52     | 8-         | -8 |
| 14                 | 35.56     | 6-            | -4 | 39                 | 99.06     | 8-         | -9 |
| 15                 | 38.10     | 6-            | -5 | 40                 | 101.60    | 9-         | -0 |
| 16                 | 40.64     | 6-            | -6 | 41                 | 104.14    | 9-         | -1 |
| 17                 | 43.18     | 6-            | -7 | 42                 | 106.68    | 9-         | -2 |
| 18                 | 45.72     | 6-            | -8 | 43                 | 109.22    | 9-         | -3 |
| 19                 | 48.26     | 6-            | -9 | 44                 | 111.76    | 9-         | -4 |
| 20                 | 50.80     | 7-            | -0 | 45                 | 114.30    | 9-         | -5 |
| 21                 | 53.34     | 7-            | -1 | 46                 | 116.84    | 9-         | -6 |
| 22                 | 55.88     | 7-            | -2 | 47                 | 119.38    | 9-         | -7 |
| 23                 | 58.42     | 7-            | -3 | 48                 | 121.92    | 9-         | -8 |
| 24                 | 60.96     | 7-            | -4 | 49                 | 124.46    | 9-         | -9 |
| 25                 | 63.50     | 7-            | -5 | 50                 | 127.00    | 5-         | -0 |



- 1

0.8 μm GOLD OVER NICKEL (PRE GOLD PLATED)
- 2

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

|              |          |                             |
|--------------|----------|-----------------------------|
| <div>1</div> | Cu Sn    | CONTACT PIN<br>KONTAKTSTIFT |
| COLOUR GREEN | PBT GV   | PINHOUSING<br>STIFTGEHAEUSE |
| REMARK       | MATERIAL | DESCRIPTION<br>BEZEICHNUNG  |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.2

1 PLC ±0.2

2 PLC ±0.2

3 PLC ±

4 PLC ±

ANGLES ±2°

FINISH -

DWN DAHLHEIMER 05DEC 1975

CHK BÖCK 17DEC 1975

APVD -

PRODUCT SPEC 108-18012

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

AMPMODU II ECONOMY LINE  
PINHEADER SINGLE ROW, GOLD-VERSION  
STIFTELEISTE EINREIHIG, GOLD-VERSION

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

©-825492

-

SCALE 5:1

SHEET 2 OF 2

REV T3