



FCIconnect.com

Copyright FCI

form: A3

APPLICATION SPECIFIC				
PIN	STYLE	MATING	SOLDER	OAL
01		5.72	2.54	10.8
02		5.84	3.43	11.81
03		5.72	5.08	13.34
04		5.72	7.62	15.88
05		5.72	10.16	18.42
06		5.72	12.7	20.96
07		5.72	15.24	23.5
08		5.72	17.78	26.04
09		5.72	20.32	28.58
10		5.72	22.86	31.12
11		5.72	5.97	14.22
12		5.72	8.51	16.76
13		5.72	11.05	19.3
14		5.72	16.13	24.38
15		8.51	2.54	13.59
16		8.51	5.51	16.56
17		8.51	10.59	21.64
18		5.72	3.05	11.3
19		12.83	3.05	18.42
20		15.37	3.05	20.96

APPLICATION SPECIFIC				
PIN	STYLE	MATING	SOLDER	OAL
21		20.45	3.05	26.04
22		7.75	3.05	13.34
24		7.21	3.05	12.8
25		8.51	3.18	14.22
26		15.57	2.84	20.96
27		6.6	2.67	11.81
28		6.6	4.19	13.34
29		17.53	3.43	23.5
30		22.61	3.43	28.58
31		8.2	2.84	13.59
32		2.41	3.05	8
33		1.6	29.38	33.52
34		12.21	2.9	17.65
35		25.21	3.37	31.12
36		11.5	12	26.04
38		30	0.98	33.52
39		1.6	31.58	35.72
40		10.29	3.05	15.88
41		9.1	3.34	14.98
42		13.25	3.3	19.09


APPLICATION SPECIFIC				
PIN	STYLE	MATING	SOLDER	OAL
43		13.02	13.02	28.58
48		5.84	2.42	10.8
49		1.5	27.08	31.12
50		5.84	3.12	11.5
52		9.5	3.05	15.09
56		5.72	3.05	11.3
58		14.47	3.05	20.06
70		6.54	3.5	12.57
79		3.3	3.3	9.14
82		19.27	4.23	26.04
92		17.45	3	23
94		4.79	3	10.33
95		27.58	1	31.12
98		13.28	2.6	18.42
AA		5.84	3.43	11.81
AB		12.83	3.05	18.42
AC		6.60	4.19	13.34
AD		13.28	2.60	18.42
AE		5.84	1.95	10.33
AF		24.46	3.00	29.98
AG		6.00	6.00	14.47
AH		4.80	4.80	12.10

mat'l. code				surface	tolerance	projection	product family			
				ISO 1302	ISO 406 ISO 1101		BERGSTIK			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title			
BG	F10-0210	LMU	10.09.17	angles	linear					
BH	F11-0055	LMU	11.05.12			scale 1:1	HEADER STR			
							DOUBLE ROW			
BC	F20301	LMU	02.04.22	dr	COMPAGNON J	95.07.10	dwg no		sheet 2 of -	size
BD	F05-0186	LMU	05.05.24	enr	JMC	95.07.10	75844			A3
BE	F06-0169	LMU	06.04.21	chr			type		CUSTOMER	Drawing
BF	F06-0196	LMU	06.06.20	appd	JMC	95.07.10				
sheet	revision									
index	sheet									




FCIconnect.com

Copyright FCI



NOTES:

- 1 - PART NUMBER 75844-YXXRXXLF
- 2 - PINS "A" AND "B" USED FOR RETENTION.
- 3 - DIRECTION OF RETENTION SHOWN BY ARROWS.
- 4 - RETENTION VERSION ONLY AVAILABLE WHEN DIM "B" IS 2.9mm UP TO 3.5mm..
- "R" INDICATES A RETENTION HEADER.



mat'l. code				surface	tolerance	projection	product family		
				ISO 1302	ISO 406 ISO 1101		BERGSTIK		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
BG	F11-0055	LMU	11.05.12	angles	.x ±0.3	mm	HEADER STR DOUBLE ROW		
BH	B-19264	LMU	14.11.03	linear	.xx ±0.15				
					xxx ±0.05	scale 1:1			
BC	F20607	LMU	03.12.03	dr	COMPAGNON J	95.07.10	FCI	dwg no	sheet 3 of - size
BD	F03079	LMU	03.04.04	enrg	JMC	95.07.10		75844	A3
BE	F05-0186	LMU	05.05.24	chr					
BF	F06-0196	LMU	06.06.20	appd	JMC	95.07.10		type	CUSTOMER Drawing
sheet index	revision sheet								