

## - RC-07P1N121500 - 1594269

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable connector, with Pg9 connection thread, straight, shielded: No, Screw locking, M23, Number of positions: 7, Type of contact: Male connector, Solder connection, Cable diameter: 6 mm ... 10 mm

The figure shows the 12-pos. product version



### Key commercial data

|                      |          |
|----------------------|----------|
| Packing unit         | 1 pc     |
| Custom tariff number | 85366990 |
| Country of origin    | Germany  |

### Technical data

|                     |                                             |
|---------------------|---------------------------------------------|
| Product type        | Circular connector (cable-side)             |
| Cable diameter      | 6 mm ... 10 mm                              |
| Coding              | N                                           |
| Type                | Cable connector, with Pg9 connection thread |
| Number of positions | 7                                           |
| Thread              | M23                                         |
| Rated voltage (IEC) | 300                                         |
| Rated current (IEC) | 20                                          |
| Knurl material      | Metal                                       |
| Shielding           | No                                          |
| Signal type         | Signal                                      |
| Connection method   | Solder connection                           |

## - RC-07P1N121500 - 1594269

### Classifications

eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260708 |
| eCl@ss 7.0 | 27440312 |
| eCl@ss 8.0 | 27440102 |

ETIM


|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC001121 |
| ETIM 5.0 | EC001121 |

UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 43172015 |
| UNSPSC 7.0901 | 43201404 |
| UNSPSC 11     | 43172015 |
| UNSPSC 12.01  | 43201404 |
| UNSPSC 13.2   | 43201404 |

### Drawings

Schematic diagram



Dimensioned drawing

