

CMOS Logic MN4000B Series

6932852 PANASONIC INDL/ELECTRONIC

MN4068B/MN4068BS

66C 05037 D T-43-21


MN4068B / MN4068BS

8-Input NAND Gates


■ Description

The MN4068B/S are positive 8-input NAND gates. The outputs are fully buffered to improve the propagation characteristics between the input and output which are affected by increasing load capacitance and minimizes propagation delay time.

■ Logic Diagram



P-1




14-Pin • Plastic DIL Package

P-2



14-Pin • Pinflat Package (SO-14D)

Pin Configuration



■ Maximum Ratings (Ta=25°C)

Item	Symbol	Ratings	Unit
Supply Voltage	V_{DD}	$-0.5 \sim +18$	V
Input Voltage	V_I	$-0.5 \sim V_{DD} + 0.5^*$	V
Output Voltage	V_O	$-0.5 \sim V_{DD} + 0.5^*$	V
Peak Input • Output Current	$\pm I_I$	max. 10	mA
Power Dissipation (per package)	$T_a = -40 \sim +60^\circ\text{C}$	max. 400	mW
	$T_a = +60 \sim +85^\circ\text{C}$	Decrease up to 200mW rating at 8mW/°C	
Power Dissipation (per output terminal)	P_D	max. 100	mW
Operating Ambient Temperature	T_{opr}	$-40 \sim +85$	°C
Storage Temperature	T_{stg}	$-65 \sim +150$	°C

* $V_{DD} + 0.5V$ should be under 18V

Panasonic

— 146 —

CMOS Logic MN4000B Series

6932852 PANASONIC INDL ELECTRONIC

MN4068B/MN4068BS


66C 05038 D T-43-21

■ DC Characteristics ($V_{SS}=0V$)

Item	V_{DD} (V)	Sym- bol	Conditions	$T_a=-40^\circ C$		$T_a=25^\circ C$		$T_a=85^\circ C$		Unit
				min.	max.	min.	max.	min.	max.	
Quiescent Power Supply Current	5	I_{DD}	$V_I=V_{SS}$ or V_{DD}	—	1	—	1	—	7.5	μA
	10			—	2	—	2	—	15	
	15			—	4	—	4	—	30	
Output Voltage Low Level	5	V_{OL}	$V_I=V_{SS}$ or V_{DD} $ I_O < 1\mu A$	—	0.05	—	0.05	—	0.05	V
	10			—	0.05	—	0.05	—	0.05	
	15			—	0.05	—	0.05	—	0.05	
Output Voltage High Level	5	V_{OH}	$V_I=V_{SS}$ or V_{DD} $ I_O < 1\mu A$	4.95	—	4.95	—	4.95	—	V
	10			9.95	—	9.95	—	9.95	—	
	15			14.95	—	14.95	—	14.95	—	
Input Voltage Low Level	5	V_{IL}	$ I_O < 1\mu A$ $V_O=0.5V$ or $4.5V$	—	1.5	—	1.5	—	1.5	V
	10			—	3	—	3	—	3	
	15			—	4	—	4	—	4	
Input Voltage High Level	5	V_{IH}	$ I_O < 1\mu A$ $V_O=0.5V$ or $4.5V$	3.5	—	3.5	—	3.5	—	V
	10			7	—	7	—	7	—	
	15			11	—	11	—	11	—	
Output Current Low Level	5	I_{OL}	$V_O=0.4V$, $V_I=0$ or $5V$	0.52	—	0.44	—	0.36	—	mA
	10			1.3	—	1.1	—	0.9	—	
	15			3.6	—	3	—	2.4	—	
Output Current High Level	5	$-I_{OH}$	$V_O=4.6V$, $V_I=0$ or $5V$	0.52	—	0.44	—	0.36	—	mA
	10			1.3	—	1.1	—	0.9	—	
	15			3.6	—	3	—	2.4	—	
Output Current High Level	5	$-I_{OH}$	$V_O=2.5V$, $V_I=0$ or $5V$	1.7	—	1.4	—	1.1	—	mA
Input Leakage Current	15	$\pm I_I$	$V_I=0$ or $15V$	—	0.3	—	0.3	—	1	μA

■ Switching Characteristics ($T_a=25^\circ C$, $V_{SS}=0V$, $C_L=50pF$)

Item	V_{DD} (V)	Symbol	min.	typ.	max.	Unit
Output Rise Time	5	t_{TLH}	—	60	180	ns
	10		—	30	90	
	15		—	20	60	
Output Fall Time	5	t_{THL}	—	60	180	ns
	10		—	30	90	
	15		—	20	60	
Propagation Delay Time I—O (H→L)	5	t_{PHL}	—	95	285	ns
	10		—	40	120	
	15		—	30	90	
Propagation Delay Time I—O (L→H)	5	t_{PLH}	—	80	240	ns
	10		—	35	105	
	15		—	30	90	
Input Capacitance		C_i	—	—	7.5	pF

1. Switching Time Test Circuit**2. Waveforms**