


# HFD3876

## Silicon PIN Photodiode


### FEATURES

- Low capacitance
- High speed:  $t_r = 1.2$  ns typical
- High responsivity: 0.33 A/W typical
- Industry standard ST®-LP fiber connector
- Housing electrically isolated
- Wave solderable



FIBER209.TIF

### OUTLINE DIMENSIONS in inches (mm)



FIBER103.DIM

### Pinout

1. Anode
2. Cathode
3. Not connected

ST is a registered trademark of AT & T.

Honeywell reserves the right to make changes in order to improve design and supply the best products possible.

# Honeywell

# HFD3876

## Silicon PIN Photodiode

### ELECTRO-OPTICAL CHARACTERISTICS ( $T_c = 25^\circ\text{C}$ unless otherwise stated)

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	TEST CONDITIONS
Flux Responsivity, $\lambda = 850 \text{ nm}$	R	0.30	0.33		A/W	50 $\mu\text{m}$ core fiber
Dark Current	$I_d$		0.05	1.5	nA	$V_R = 30 \text{ V}$
Total Capacitance	C		1.5		pF	$V_R = 5 \text{ V}$
Response Time 10-90%	$t_R$		1.2	3	ns	$V_R = 3.5 \text{ V}$
90-10%	$t_F$		1.2	3	ns	$V_R = 3.5 \text{ V}$
Field of View	FoV		32		Degrees	

### ABSOLUTE MAXIMUM RATINGS

( $T_{\text{case}} = 25^\circ\text{C}$  unless otherwise noted)

Storage temperature  $-40$  to  $+100^\circ\text{C}$

Operating temperature  $-40$  to  $+100^\circ\text{C}$

Lead solder temperature  $260^\circ\text{C}$  for 10 s

Reverse voltage 50 V

Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational section of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods of time may affect reliability.

### ORDER GUIDE

Description Catalog Listing

Standard silicon PIN photodiode HFD3876-002

### CAUTION

The inherent design of this component causes it to be sensitive to electrostatic discharge (ESD). To prevent ESD-induced damage and/or degradation to equipment, take normal ESD precautions when handling this product.



### FIBER INTERFACE

Honeywell detectors are designed to interface with multimode fibers with sizes (core/cladding diameters) ranging from 50/125 to 200/230 microns. Honeywell performs final tests using 50/125 micron core fiber. The fiber chosen by the end user will depend upon a number of application issues (distance, link budget, cable attenuation, splice attenuation, and safety margin). The 50/125 and 62.5/125 micron fibers have the advantages of high bandwidth and low cost, making them ideal for higher bandwidth installations. The use of 100/140 and 200/230 micron core fibers results in greater power being coupled by the transmitter, making it easier to splice or connect in bulkhead areas. Optical cables can be purchased from a number of sources.

# HFD3876

## Silicon PIN Photodiode

Fig. 1 Relative Response vs Polar Angle




Fig. 2 Spectral Responsivity




Fig. 3 Relative Responsivity vs Temperature





Fig. 4 Dark Leakage Current vs Temperature



Honeywell reserves the right to make changes in order to improve design and supply the best products possible.

**Honeywell**