

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [10-08-1061](#)
Status: **Active**
Overview: [KK® Interconnection System](#)
Description: 5.08mm Pitch KK® Header, Vertical, Round Pin, 6 Circuits, Tin (Sn) Plating, Pin Length 19.05mm

Documents:
[3D Model](#) [Product Specification PS-99020-0087 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family PCB Headers
Series [3003](#)
Application Board-to-Board, Power, Wire-to-Board
Overview [KK® Interconnection System](#)
Product Name KK®
UPC 800753612181

Physical

Breakaway No
Circuits (Loaded) 6
Circuits (maximum) 6
Color - Resin Natural
Durability (mating cycles max) 25
First Mate / Last Break No
Flammability 94V-2
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 1.504/g
Number of Rows 1
Orientation Vertical
PC Tail Length 3.94mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Bag
Pitch - Mating Interface 5.08mm
Pitch - Termination Interface 5.08mm
Plating min - Mating 5.080µm
Plating min - Termination 5.080µm
Polarized to Mating Part No
Polarized to PCB No
Shrouded No
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating 0°C to +50°C




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[3003Series](#)

Mates With
KK® Crimp Housing 3001 , [5058](#) , [3002](#)
KK® PC Board Connector

Termination Interface: Style

Through Hole

Electrical

onlinecomponents.com
THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

Current - Maximum per Contact

7A

Voltage - Maximum

250V

Solder Process Data

Duration at Max. Process Temperature (seconds)

10

Lead-free Process Capability

Wave Capable (TH only)

Process Temperature max. C

260

Material Info

Old Part Number

3003-06A

Reference - Drawing Numbers

Product Specification

PS-99020-0087

Sales Drawing

SDAE-3003-N*

This document was generated on 10/17/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION