



# QMI2582

## Dual Port 8Gb FC to PCIe Expansion Card (C10v) for IBM® BladeCenter® Servers

IBM Part Number: 44X1945

### Benefits

- Lowest power consumption
- Highest data integrity on data and control paths
- Enhanced security protection
- Faster driver deployment and reduced interoperability issues with unified driver model

### Features

- Fibre Channel 8Gb to PCI Express (PCIe) x8
- 1600 MBps (full-duplex) per port
- 200,000 initiator IOPS per port
- StarPower™ with Dynamic Power Management and Cool HBA™ technologies

DATA SHEET



**QMI2582 Host Bus Adapter.** The QMI2582 is a PCI Express (PCIe), dual port, 8Gb FC expansion card for IBM BladeCenter servers.

**Virtualization Optimized.** The QMI2582 supports N\_Port ID Virtualization (NPIV) by allowing multiple logical (virtual) connections to share the same physical port. Each logical connection has its own resources and the ability to be managed independently.

**Power Optimized.** The QMI2582 takes advantage of QLogic StarPower technology, ensuring power efficiency. QLogic StarPower technology offers dynamic power management to provide the necessary PCI Express bandwidth at the lowest power consumption. Low-power switching power supplies and thermally efficient layout allows the QMI2582 to operate without any additional airflow, making it a *Cool HBA*.

**RAS Optimized.** The QMI2582 provides the highest data integrity by ensuring Overlapping Protection Domains (OPD) on both the control and data paths. The dual-port design protects against “single point of failure” via BladeCenter midplane routing to redundant switch modules.

**Security Optimized.** The QMI2582 enables SAN-level authentication by supporting Fibre Channel-Security Protocol (FC-SP).

**Management Optimized.** The QMI2582 is backward compatible with 2Gb and 4Gb speeds. A single common driver per operating system for two generations of FC HBAs (4Gb and 2Gb) simplifies deployment. QLogic's unified driver model (firmware embedded in the driver) eliminates potential interoperability issues between firmware and driver versions. The QMI2582's API compatibility with 2Gb and 4Gb products accelerates deployment while ensuring application compatibility.

**Investment Protection.** For over 15 years, QLogic has been a technological leader with products that address the current needs of customers, yet provide strong investment protection to support emerging technologies and standards. QLogic stands alone in the industry with its product portfolio depth and experience in successfully delivering technological solutions that address the needs of today and tomorrow.

## QMI2582 Dual Port 8Gb FC to PCIe Expansion Card (C10v) for IBM® BladeCenter® Servers

## Fibre Channel Specifications

## Negotiation

- 8/4/2-Gbps auto-negotiation

## IOPS

- 200,000 initiator IOPS per port

## Class of service

- 3

## Topology

- FC-AL, FC-AL2, point-to-point, switched fabric

## Protocols

- FCP-3-SCSI
- FC-Tape (FCP-2)

## PCI Express Interface

## Compliance

- PCI Express Base Specification rev. 2.0
- PCI Bus Power Management Interface Specification rev. 1.2

## Physical and electrical

- IBM BladeCenter PCIe mezzanine slot connector
- StarPower link training
  - Maximum x4 lanes for Gen2 rate
  - Maximum x8 lanes for Gen1 rate

## HBA Specifications

## Airflow

- Provided by BladeCenter enclosure

## Power consumption

- 8.5 watts (typical) — Gen1 x8
- 7.3 watts (typical) — Gen2 x4

## Form factor

- IBM C10v form factor

## Temperature

- 0°C/32°F to 55°C/131°F (operating)
- -40°C/-40°F to 70°C/158°F (non-operating)

## Relative Humidity

- 10% to 90% (operating, non-condensing)
- 5% to 93% (non-operating, non-condensing)

## RoHS compliance

- RoHS 6

## Tools and Utilities

## Management tools

- SANsurfer® FC HBA Manager
- SANsurfer FC HBA CLI

## Device utilities

- Utilities for flashing bootcode
- Linux® scripting tools

## Boot support

- BIOS, FCode, UEFI

## APIs

- SNIA HBA API V2, SMI-S, FDMI

## Platform/Operating System Support

## Hardware platforms (BladeCenter servers)

- HS22
- JS23

## Operating systems

- Windows Server® 2003 and 2008
- Linux Red Hat® AS 4.x, 5.x
- Novell® SLES 9, 10
- NetWare® 6.5
- Solaris™ 10
- VMware® ESX/ESXi 3.5 and ESX/ESXi 4.0 (targeted versions)
- AIX® (IBM supplied driver)

## Agency Approvals—EMI and EMC

## US/Canada

- FCC Part 15, Subpart B, Class A; ICES-003, Class A

## Europe

- EN55022, Class A

## New Zealand/Australia

- AS/NZS 3548 Class A

## Japan

- VCCI V-3/2004.4, Class A

## Korea

- MIC

## Taiwan

- BSMI (CNS 13438)

## Agency Approvals—Safety

## US/Canada

- UL, cUL: UL60950, CSA C22.2 No.60950

## Europe

- 73/23/ECC Low Voltage Directive:
  - TUV: EN60950-1:2001, EN60825-1:1994+A1+A2, EN60825-2:1994+A1

## Ordering Information

## QMI2582

- The QMI2582 is available from IBM (IBM part number: 44X1945)



Corporate Headquarters

Europe Headquarters

QLogic Corporation

QLogic (UK) LTD.

26650 Aliso Viejo Parkway

Quatro House

Aliso Viejo, CA 92656

Lyon Way, Frimley

949.389.6000

Camberley Surrey, GU16 7ER UK

www.qlogic.com

+44 (0) 1276 804 670

© 2009 QLogic Corporation. Specifications are subject to change without notice. All rights reserved worldwide. QLogic and the QLogic logo, StarPower, SANsurfer, and Cool HBA are trademarks or registered trademarks of QLogic Corporation. IBM, BladeCenter, and AIX are registered trademarks of IBM Corporation. Windows is a registered trademark of Microsoft Corporation. Linux is a registered trademark of Linus Torvalds. Red Hat is a registered trademark of Red Hat Software, Inc. Novell and NetWare are registered trademarks of Novell, Inc. VMware is a registered trademark of VMware, Inc. Solaris is a trademark of Sun Microsystems, Inc. All other brand and product names are trademarks or registered trademarks of their respective owners. Information supplied by QLogic Corporation is believed to be accurate and reliable. QLogic Corporation assumes no responsibility for any errors in this brochure. QLogic Corporation reserves the right, without notice, to make changes in product design or specifications.