



Copyright FCI.

PRODUCT NUMBER

XXXXX-YYY HTLF

LEAD FREE OPTION
SEE NOTE 1,11


TUBE PACKAGING OPTION
SEE NOTE 1

HIGH TEMPERATURE PLASTIC
SEE NOTE 1


NO OF
POSITIONS
SEE NOTE 1

PIN PLATING
SEE SHEET 2


BASE PART NO.



TOP VIEW




SIDE VIEW



END VIEW

Ø.020/0.51 (M) U (M) V (S) W

NOTE 4



DETAIL P
TYP BOTH ENDS

rev	ecn no	dr	date
AK	ELX-N-16105	ZK	2013-10-22
AL	ELX-N-17149	ZK	2014-03-07
CU	M05-0072	MHT	5/03/05
CV	M06-0435	MHT	10/31/06
AH	M08-0291	MHT	10/06/08
AJ	N11-0118	J.Z	2011-04-11

www.fciconnect.com			surface 6.4 ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		INCH/MM ↔				
			TOLERANCES UNLESS		OTHERWISE SPECIFIED								
Dr	D.WHITING	04/07/93	ANGULAR		LINEAR	0.X	±0.3	size A4	Scale 1.000				
Eng	T.HANNA	04/07/93				0.XX	±0.15						
Chr	T.HANNA	04/07/93	0° ±2°			0.XXX	±0.05		ECN				
Appr	T.HANNA	04/07/93	Product family			BERGSTIK		Spec ref					
		title				BERGSTIK® II HEADER				dwg no 69191		Rev AL	
						.100 SR R/A SELF-RET							
catalog no						CUSTOMER				sheet 1 of 4			

PIN PLATING CODES:

XXXX-1YY	30u"/0.76u MIN (SEE NOTE 12) OVER 50u"/1.27u MIN Ni
XXXX-2YY	15u"/0.38u MIN (SEE NOTE 12) OVER 50u"/1.27u MIN Ni
XXXX-3YY	50u"/1.27u MIN (SEE NOTE 12) OVER 50u"/1.27u MIN Ni
XXXX-4YY	100u"/2.54u MIN Sn OVER 50u"/1.27u MIN Ni (SEE NOTE 1,13)
XXXX-4YYHLF	
XXXX-5YY	15u"/0.38u MIN (SEE NOTE 12) OVER 50u"/1.27u MIN Ni
XXXX-6YY	30u"/0.76u MIN (SEE NOTE 12) OVER 50u"/1.27u MIN Ni
XXXX-7YY	30u"/0.76u MIN (SEE NOTE 12) OVER 50u"/1.27u MIN Ni
XXXX-8YY	15u"/0.38u MIN (SEE NOTE 12) OVER 50u"/1.27u MIN Ni
XXXX-9YY	15u"/0.38u MIN (SEE NOTE 12) OVER 50u"/1.27u MIN Ni
XXXX-0YY	30u"/0.76u MIN (SEE NOTE 12) OVER 50u"/1.27u MIN Ni

NOTES

①. PART NUMBER OPTIONS:

PIN PLATING CODES (SEE ABOVE)

HIGH TEMP. MATERIAL:

FOR HIGH-TEMPERATURE APPLICATIONS, SPECIFY AN "H" AT THE END OF THE PART NUMBER, AND PCT WILL BE SUPPLIED.

NUMBER OF POSITION:

ANY NUMBER OF POSITIONS FROM 2 THRU 36.

PACKAGING:

PACKAGED IN POLY BAGS.

EIGHT DIGIT PART NUMBERS FOLLOWED BY A "T" ARE PACKAGED IN TUBES. SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.

LEAD FREE:

ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION, NOT AVAILABLE FOR -5YY, -5YYH, -6YY & -6YYH.

②. BODY MATERIAL:

MANUFACTURER'S OPTION OF NYLON OR PCT, GLASS FIBER REINFORCED, FLAME RETARDANT PER UL-94V-0.

COLOR: BLACK, OR MINERAL FILLED LCP, COLOR BLACK FLAME RETARDANT PER UL-94V-0

PART NUMBERS WITH "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

PART NUMBERS WITHOUT "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR WAVE SOLDER PROCESS.

③. PIN MATERIAL: PHOS-BRONZE.

④. MEASURED WITH PART IN RESTRAINED CONDITION.

5. TWO SIDES OF PIN TIPS NOT PLATED, TYPICAL BOTH ENDS.

⑥. 2LBS/0.9KG MIN PIN RETENTION IN EITHER DIRECTION.

⑦. ±.010/0.25 ON DIM "F" APPLIES TO THIS PART ONLY.

8. 5LB/2.3KG MAX INSERTION FORCE AND .25LB/.1KG MIN RETENTION FORCE PER RETENTIVE PIN USING .062/1.57 THICK CIRCUIT BOARDS AND RECOMMENDED HOLE PATTERN.

⑧. DETAIL N DIMENSIONS APPLY TO 2 POSITION PARTS ONLY

⑨. SECTION R-R DIMENSIONS ONLY APPLY TO RETENTION. PIN POSITIONS FOR 3 POSITION PARTS AND LARGER. RETENTION PIN POSITIONS LOCATED AT MANUFACTURES OPTION.

⑩. SECTION S-S DIMENSIONS APPLY TO DUAL RETENTION PIN POSITIONS ONLY. SEE PRODUCT PART NUMBER FOR SINGLE OR DUAL SIDE RETENTION. LOCATED AT MANUFACTURER'S OPTION.

⑪. THESE PRODUCTS MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

⑫. PLATING OPTIONS: PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON POST OR TAIL, OPTIONALLY (.78~2.95u"/2~7.5u) TIN ON TAIL.

⑬. "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."

.100±.003 [2.54±.08]
TYP. NON-ACCUMULATIVE

Ø.040±.003 [1.02±.08]
TYP.

RECOMMENDED HOLE PATTERN

www.fciconnect.com			surface ISO 1302 ✓	tolerance std ISO 406 ISO 1101	projection A4	INCH/MM Scale 1.000
Dr	D.WHITING	04/07/93	ANGULAR 0° ±2°	LINEAR	size	ECN
Eng	T.HANNA	04/07/93		0.X	±0.3	
Chr	T.HANNA	04/07/93		0.XX	±0.15	
Appr	T.HANNA	04/07/93	Product family		Spec ref	
FCI			title		dwg no	Rev.
			BERGSTIK® II HEADER		69191	AL
			catalog no		CUSTOMER	sheet 2 of 4

A

B

C


D

A



B

C


D




PDS. 2 ETC
PDS. 1



SECTION R-R
NOTE 9



SECTION S-S
NOTE 10



DETAIL N
NOTE 8

Copyright FCI.

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		INCH/MM 			
			TOLERANCES UNLESS		OTHERWISE SPECIFIED							
Dr	D.WHITING	04/07/93	ANGULAR 0° ±2°	LINEAR	0.X ±0.3		size	A4	Scale			
Eng	T.HANNA	04/07/93			0.XX ±0.15		1.000					
Chr	T.HANNA	04/07/93			0.XXX ±0.05		ECN					
Appr	T.HANNA	04/07/93	Product family BERGSTIK				Spec ref					
	title				BERGSTIK® II HEADER .100 SR R/A SELF-RET				dwg no		69191	Rev
	catalog no								CUSTOMER		sheet 3 of 4	
											AL	

1

2

3

4

PRODUCT NUMBER	MATING LENGTH		TAIL LENGTH		BEND DIM		RETENTION	PACKAGING	NOTES	LF OPTION
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H				
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC				
69191-XXY	0.230	5.84	0.120	3.05	0.060	1.52	G TAIL	POLY BAGS/TUBES	-	NOTE 1,11
72375-XXXH	0.240	6.10	0.120	3.05	0.060	1.52	G TAIL	POLY BAGS	-	OB
78554-XXY	0.318	8.08	0.120	3.05	0.060	1.52	G TAIL	POLY BAGS/TUBES	-	
78940-XXY	0.120	3.05	0.120	3.05	0.060	1.52	F MATE & G TAIL	POLY BAGS	7	OB
78952-XXY	0.120	3.05	0.318	8.08	0.135	3.43	F MATE	POLY BAGS	7	OB
79253-XXY	U N A V A I L A B L E									
84825-XXXH	0.354	9.00	0.102	2.60	0.060	1.52	G TAIL	POLY BAGS	-	OB
84851-XXXH	0.140	3.56	0.290	7.37	0.153	3.89	G TAIL	POLY BAGS	-	OB
86641-XXY	0.120	3.05	0.120	3.05	0.060	1.52	G TAIL	POLY BAGS	-	
87018-XXY	U N A V A I L A B L E									
87844-XXY	U N A V A I L A B L E									
87965-XXY	U N A V A I L A B L E									
88869-XXY	0.120	3.05	0.230	5.84	0.135	3.43	F MATE	POLY BAGS	7	OB
90304-XXY	0.165	4.19	0.120	3.05	0.060	1.52	G TAIL	POLY BAGS	-	OB
90604-XXY	U N A V A I L A B L E									
90609-XXY	U N A V A I L A B L E									NOTE 1,11
90638-XXY	0.120	3.05	0.262	6.65	0.060	1.52	F MATE	POLY BAGS/TUBES	7	OB
90640-XXY	0.120	3.05	0.262	6.65	0.127	3.23	F MATE	POLY BAGS	7	OB
94669-XXXH	0.230	5.84	0.085	2.16	0.060	1.52	G TAIL	POLY BAGS	-	OB
94670-XXXH	0.400	10.16	0.085	2.16	0.060	1.52	G TAIL	POLY BAGS	-	OB
10100500-XXXH	0.177	4.50	0.120	3.05	0.043	1.10	G TAIL	POLY BAGS	-	

REV F - 2006-04-17

1

2

3

4

PDS: Rev :AL

STATUS:Released

Printed: Mar 10, 2014



Copyright FCI.

D

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		INCH/MM ←————→	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	D.WHITING	04/07/93	ANGULAR	LINEAR	0.X	±0.3	size	A4	Scale 1.000	
Eng	T.HANNA	04/07/93			0.XX	±0.15				
Chr	T.HANNA	04/07/93			0° ±2°	0.XXX	±0.05	ECN		
Appr	T.HANNA	04/07/93	Product family BERGSTIK				Spec ref			
		title BERGSTIK® II HEADER 100 SR R/A SELF-RET				dwg no 69191		Rev AL		
		catalog no								
						CUSTOMER		sheet 4 of 4		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI:](#)

[69191-102](#) [69191-103H](#) [69191-104](#) [69191-106](#) [69191-107](#) [69191-108](#) [69191-111H](#) [69191-112](#) [69191-114](#)
[69191-116](#) [69191-120](#) [69191-136](#) [69191-204](#) [69191-206](#) [69191-207](#) [69191-208](#) [69191-212H](#) [69191-216](#) [69191-220](#) [69191-236](#) [69191-406](#) [69191-408](#) [69191-409](#) [69191-412](#) [69191-414](#) [69191-436](#) [69191-502](#) [69191-503](#)
[69191-504](#) [69191-505](#) [69191-510](#) [69191-512](#) [69191-514](#) [69191-515](#) [69191-516](#) [69191-517H](#) [69191-520](#) [69191-536](#) [69191-602](#) [69191-603](#) [69191-604](#) [69191-606H](#) [69191-608](#) [69191-610](#) [69191-615](#) [69191-616H](#) [69191-620H](#) [69191-622H](#) [69191-634H](#) [69191-410](#) [69191-404](#) [69191-402](#) [69191-405](#) [69191-126](#) [69191-202](#) [69191-203](#) [69191-205](#) [69191-210](#) [78554-105H](#) [78554-110](#) [78554-112](#) [78554-207](#) [78554-216](#) [78554-220H](#) [78554-236](#) [78554-404](#) [78554-405](#) [78554-406](#) [78554-407](#) [78554-408](#) [78554-411](#) [78554-423H](#) [78554-436](#) [78554-506H](#) [78940-520](#) [69191-402HLF](#) [69191-105](#) [78554-110HLF](#) [78554-206HLF](#) [78554-236HLF](#) [78554-404HLF](#) [78554-405HLF](#) [78554-406HLF](#) [78554-408HLF](#) [78554-411HLF](#) [78554-436HLF](#) [78940-220HLF](#) [94669-236HLF](#) [69191-102HLF](#) [69191-104H](#) [69191-106HLF](#) [69191-107HLF](#) [69191-110HLF](#) [69191-112HLF](#) [69191-115HLF](#) [69191-122HLF](#) [69191-134HLF](#) [69191-202H](#) [69191-204HLF](#) [69191-206HLF](#)