

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

LOC

DIST

REVISIONS

©

COPYRIGHT 20

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.

FT

0

P

LTR

DESCRIPTION

DATE

DWN

APVD


CI

REVISED PER ECO-12-007964

02MAY2012

KH

MS



282965-3 AS SHOWN



MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.


2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.

3 RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC., FILE N° E60677.



4 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.



NOT CUMULATIVE TOLERANCE.




12.0



89.64	12	1-282965-2
82.02	11	1-282965-1
74.40	10	1-282965-0
66.78	9	282965-9
59.16	8	282965-8
51.54	7	282965-7
43.92	6	282965-6
36.30	5	282965-5
28.68	4	282965-4
21.06	3	282965-3
13.44	2	282965-2

DIM. A N° OF POS. PART NUMBER

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±.3
1 PLC ±.25
2 PLC ±.25
3 PLC ±.25
4 PLC ±.25
ANGLES ±.2

MATERIAL

FINISH

DWN

E. ZANOLINI

CHK

D. BIEVENOUR

APVD

D. BIEVENOUR

PRODUCT SPEC

108-20166

APPLICATION SPEC

114-20079

WEIGHT

-

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 1

REV C



TE Connectivity

NAME
TERMINAL BLOCK HEADER ASSEMBLY
90 DEGREE, OPEN ENDS
7.62mm PITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-282965

-