

PTC/CAD

GLH

22 SEP 97

CHECK

GLH

11 AUG 98

CHECK

REVISIONS

1

ISSUE

1

DRAWING NUMBER

1


REPLACES

PR-23065

PAGE 1 OF 1

GLAA01A2D-F024

ANGULAR ACTUATION						
CONTACT BLOCK DIAGRAM	NOMINAL TRAVELS AND RELATED TERMINALS ■ - CONTACT CLOSED, □ - CONTACT OPEN, ▨ - CONTACT CLOSED DIFFERENTIAL TRAVEL, ** POSITIVE OPENING TO IEC 947-5-1	MAXIMUM OPERATING TORQUE	MAXIMUM DISCONNECT TORQUE	MAX OPERATE DEGREE/S	MIN OPERATE DEGREE/S	MAX OPERATE FREQUENCY OPS/MIN
		$\frac{\text{N}\cdot\text{m}}{\text{LB}\cdot\text{IN}}$	$\frac{\text{N}\cdot\text{m}}{\text{LB}\cdot\text{IN}}$			
SNAP - ACTION CONTACTS SINGLE POLE 		$\frac{.330}{2.9}$	$\frac{.385}{3.4}$	1290	13	250



MASTER REDUCED
ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

MICRO SWITCH

a Honeywell Division

FED. MFG. CODE 91929

SWITCH, ENCLOSED

CATALOG LISTING
GLAA01A2D-F024

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

NO PLACE (0) ± 1 MM

ONE PLACE (0,0) ± 0,4 MM

TWO PLACE (0,00) ± 0,15 MM

ANGLES ±

WEIGHT