






N- and P-Channel 30-V (D-S) MOSFET

PRODUCT SUMMARY

	V_{DS} (V)	$R_{DS(ON)}$ (Ω)	I_D (A)
N-Channel	30	0.065 @ $V_{GS} = 10$ V	± 3.9
		0.095 @ $V_{GS} = 4.5$ V	± 3.1
P-Channel	-30	0.085 @ $V_{GS} = -10$ V	± 3.5
		0.19 @ $V_{GS} = -4.5$ V	± 2.5



N-Channel MOSFET



P-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

PARAMETER		SYMBOL	N-CHANNEL	P-CHANNEL	UNIT
Drain-Source Voltage		V_{DS}	30	−30	V
Gate-Source Voltage		V_{GS}	±20	±20	
Continuous Drain Current ($T_J = 150^{\circ}\text{C}$) ^A	$T_A = 25^{\circ}\text{C}$	I_D	±3.9	±3.5	A
	$T_A = 70^{\circ}\text{C}$		±3.1	±2.8	
Pulsed Drain Current		I_{DM}	±20	±20	
Continuous Source Current (Diode Conduction) ^A		I_S	1.7	−1.7	
Maximum Power Dissipation ^A	$T_A = 25^{\circ}\text{C}$	P_D	2.0		W
	$T_A = 70^{\circ}\text{C}$		1.3		
Operating Junction and Storage Temperature Range		T_J, T_{stg}	−55 to 150		$^{\circ}\text{C}$

THERMAL RESISTANCE RATINGS

PARAMETER	SYMBOL	N- OR P-CHANNEL	UNIT
Maximum Junction-to-Ambient ^A	R_{thJA}	62.5	$^\circ\text{C/W}$

Notes

A. Surface Mounted on FR4 Board, $t \leq 10$ sec.

Updates to this data sheet may be obtained via facsimile by calling Siliconix FaxBack, 1-408-970-5600. Please request FaxBack document #70155.
For SPICE model information via the Worldwide Web: <http://www.siliconix.com/www/product/spice.htm>

SPECIFICATIONS (T_J = 25°C UNLESS OTHERWISE NOTED)

PARAMETER	SYMBOL	TEST CONDITION		MIN	TYP	MAX	UNIT
STATIC							
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA	N-Ch	1.0			V
		V _{DS} = V _{GS} , I _D = −250 μA	P-Ch	−1.0			
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ±20 V	N-Ch			±100	nA
			P-Ch			±100	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 30 V, V _{GS} = 0 V	N-Ch			1	μA
		V _{DS} = −30 V, V _{GS} = 0 V	P-Ch			−1	
		V _{DS} = 30 V, V _{GS} = 0 V, T _J = 55°C	N-Ch			25	
		V _{DS} = −30 V, V _{GS} = 0 V, T _J = 55°C	P-Ch			−25	
On-State Drain Current ^B	I _{D(on)}	V _{DS} ≥ 5 V, V _{GS} = 10 V	N-Ch	15			A
		V _{DS} ≥ −5 V, V _{GS} = −10 V	P-Ch	−15			
Drain-Source On-State Resistance ^B	r _{DS(on)}	V _{GS} = 10 V, I _D = 3.9 A	N-Ch		0.043	0.065	Ω
		V _{GS} = −10 V, I _D = −2.5 A	P-Ch		0.066	0.085	
		V _{GS} = 4.5 V, I _D = 3.1 A	N-Ch		0.075	0.095	
		V _{GS} = −4.5 V, I _D = −1.8 A	P-Ch		0.125	0.19	
Forward Transconductance ^B	g _{fs}	V _{DS} = 15 V, I _D = 3.9 A	N-Ch		7		S
		V _{DS} = −15 V, I _D = −2.5 A	P-Ch		5		
Diode Forward Voltage ^B	V _{SD}	I _S = 1.7 A, V _{GS} = 0 V	N-Ch		0.8	1.2	V
		I _S = −1.7 A, V _{GS} = 0 V	P-Ch		−0.8	−1.2	
DYNAMICA							
Total Gate Charge	Q _g	N-Channel V _{DS} = 10 V, V _{GS} = 10 V, I _D = 3.9 A P-Channel V _{DS} = −10 V, V _{GS} = −10 V, I _D = −2.5 A	N-Ch		9.8	15	nC
Gate-Source Charge	Q _{gs}		P-Ch		8.7	15	
			N-Ch		2.1		
Gate-Drain Charge	Q _{gd}		P-Ch		1.9		
		N-Ch		1.6			
Turn-On Delay Time	t _{d(on)}	P-Ch		1.3			
		N-Ch		9	15		
Rise Time	t _r	P-Ch		7	15		
		N-Ch		6	18		
Turn-Off Delay Time	t _{d(off)}	P-Ch		9	18		
		N-Ch		18	27		
Fall Time	t _f	P-Ch		14	27		
		N-Ch		6	15		
Source-Drain Reverse Recovery Time	t _{rr}	P-Ch		8	15		
		N-Ch		52	80		
		I _F = 1.7 A, di/dt = 100 A/μs	N-Ch		52	80	
		I _F = −1.7 A, di/dt = 100 A/μs	P-Ch		50	80	







Notes

- A. Guaranteed by design, not subject to production testing.
 B. Pulse test; pulse width ≤ 300 μs, duty cycle ≤ 2%.








TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)

N-CHANNEL



TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)







N-CHANNEL










TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)

P-CHANNEL



TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)

P-CHANNEL





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[SI4532DY](#) [SI4532DY-T1-E3](#) [SI4532DY-E3](#) [SI4532ADY-T1](#)