


FK25SM-5

HIGH-SPEED SWITCHING USE


FK25SM-5



- V_{DS} 250V
- $r_{DS(ON)} (MAX)$ 0.16Ω
- I_D 25A
- Integrated Fast Recovery Diode (MAX.) 150ns

OUTLINE DRAWING

Dimensions in mm



TO-3P

APPLICATION

Servo motor drive, Robot, UPS, Inverter Fluorecent lamp, etc.



MAXIMUM RATINGS (Tc = 25°C)







Symbol	Parameter	Conditions	Ratings	Unit
V_{DS}	Drain-source voltage	$V_{GS} = 0V$	250	V
V_{GSS}	Gate-source voltage	$V_{DS} = 0V$	± 30	V
I_D	Drain current		25	A
I_{DM}	Drain current (Pulsed)		75	A
I_S	Source current		25	A
I_{SM}	Source current (Pulsed)		75	A
P_D	Maximum power dissipation		250	W
T_{ch}	Channel temperature		-55 ~ +150	°C
T_{stg}	Storage temperature		-55 ~ +150	°C
—	Weight	Typical value	4.8	g

ELECTRICAL CHARACTERISTICS (T_{ch} = 25°C)


Symbol	Parameter	Test conditions	Limits			Unit
			Min.	Typ.	Max.	
V (BR) DSS	Drain-source breakdown voltage	I _D = 1mA, V _{GS} = 0V	250	—	—	V
V (BR) GSS	Gate-source breakdown voltage	I _G = ±100μA, V _{DS} = 0V	±30	—	—	V
I _{GSS}	Gate-source leakage current	V _{GS} = ±25V, V _{DS} = 0V	—	—	±10	μA
I _{DSS}	Drain-source leakage current	V _{DS} = 250V, V _{GS} = 0V	—	—	1	mA
V _{GS} (th)	Gate-source threshold voltage	I _D = 1mA, V _{DS} = 10V	2	3	4	V
r _{DS} (ON)	Drain-source on-state resistance	I _D = 12A, V _{GS} = 10V	—	0.12	0.16	Ω
V _{DS} (ON)	Drain-source on-state voltage	I _D = 12A, V _{GS} = 10V	—	1.44	1.92	V
y _{fs}	Forward transfer admittance	I _D = 12A, V _{DS} = 10V	7.0	11	—	S
C _{iss}	Input capacitance	V _{DS} = 25V, V _{GS} = 0V, f = 1MHz	—	2100	—	pF
C _{oss}	Output capacitance		—	420	—	pF
C _{rss}	Reverse transfer capacitance		—	90	—	pF
t _d (on)	Turn-on delay time	V _{DD} = 150V, I _D = 12A, V _{GS} = 10V, R _{GEN} = R _{GS} = 50Ω	—	35	—	ns
t _r	Rise time		—	85	—	ns
t _d (off)	Turn-off delay time		—	240	—	ns
t _f	Fall time		—	100	—	ns
V _{SD}	Source-drain voltage	I _S = 12A, V _{GS} = 0V	—	1.5	2.0	V
R _{th} (ch-c)	Thermal resistance	Channel to case	—	—	0.50	°C/W
t _{rr}	Reverse recovery time	I _S = 25A, di/dt = -100A/μs	—	—	150	ns

PERFORMANCE CURVES




**OUTPUT CHARACTERISTICS
(TYPICAL)**

**OUTPUT CHARACTERISTICS
(TYPICAL)**

**ON-STATE VOLTAGE VS.
GATE-SOURCE VOLTAGE
(TYPICAL)**

**ON-STATE RESISTANCE VS.
DRAIN CURRENT
(TYPICAL)**

**TRANSFER CHARACTERISTICS
(TYPICAL)**

**FORWARD TRANSFER ADMITTANCE
VS. DRAIN CURRENT
(TYPICAL)**



CAPACITANCE VS.
DRAIN-SOURCE VOLTAGE
(TYPICAL)




SWITCHING CHARACTERISTICS
(TYPICAL)




GATE-SOURCE VOLTAGE
VS. GATE CHARGE
(TYPICAL)



SOURCE-DRAIN DIODE
FORWARD CHARACTERISTICS
(TYPICAL)



ON-STATE RESISTANCE VS.
CHANNEL TEMPERATURE
(TYPICAL)



THRESHOLD VOLTAGE VS.
CHANNEL TEMPERATURE
(TYPICAL)

