



Suspension Systems - NEMA 12, 13

Tara Plus Suspension System

Operator Interface Enclosure



Measurement Conversions

1 kg = 9.81 N 1 lb = 4.44 N
e.g. 500 Newtons = 51 kg = 112.4 lbs
 300 Newtons = 30.6 kg = 67.4 lbs
 100 Newtons = 10.2 kg = 22.5 lbs
1 foot = 0.305 m

Suspension System

Application

- Taraplus enclosure suspension systems are designed for light and medium loads.
- The strength of tube and cast fittings provide a highly flexible robust system.

Construction


- Enclosure coupling and elbow coupling fittings are die-cast from G AL SI 12 aluminum.
- Suspension tubing is steel.

Finish

- Fittings are finished in RAL 7040 window gray.
- Suspension tubing is RAL 7035 light gray.

Standards

- **Complies with**
 - IEC 60529 IP54



Suspension Tube


Part No.	Outside mm	Inside mm	Tolerance	Length Metres	Length Feet	Ship Wt. lbs
Round Tubes						
R144-301-000	48	42	±0.25	1	3.28	10
R144-321-000	70	62	±0.25	1	3.28	25
R144-321-500	70	62	±0.25	1.5	4.92	38
Rectangular Tubes						
R144-311-000	60 x 40	54 x 34	±0.50	1	3.28	13
R144-311-500	60 x 40	54 x 34	±0.50	1.5	4.92	26

Technical references and CAD downloads available at www.hammondmfg.com

All dimensions in inches unless specified otherwise

Suspension Systems - NEMA 12, 13


Operator Interface Enclosure



Part No.	Mounting Position
R149-025-500	Top
R149-025-501	Bottom

Coupling



- Attaches to enclosure.
- Accepts 48mm round tube. perpendicular to enclosure top/bottom.
- Die-cast Aluminum G Al Si 12.
- Adjustable torque resistance.
- Rotates 300°.



Part No. R149-025-001

Tilt Coupling


- Attaches to enclosure.
- Accepts 48mm round tube perpendicular to enclosure top/bottom.
- Die-cast Aluminum G Al Si 12.
- Rotates 300°.
- Features an adjustable tilt mechanism up to 35°.



Part No.	R149-035-000
----------	--------------

Elbow Coupling

- Attaches to enclosure.
- Accepts 60x40mm rectangular tube parallel to enclosure top/bottom.
- Die-cast Aluminum G Al Si 12.
- Adjustable torque resistance.
- Rotates 300°.
- Accessible from the top.



Technical references and CAD downloads available at www.hammondmfg.com

All dimensions in inches unless specified otherwise


Quality Products. Service Excellence.

Suspension Systems - NEMA 12, 13


Tara Plus Suspension System

Tilt Elbow Coupling

- Attaches to enclosure.
- Accepts 60x40mm rectangular tube parallel to enclosure top/bottom.
- Die-cast Aluminum G Al Si 12.
- Rotates 300°.
- Features an adjustable tilt. mechanism up to 35°.




Part No. **R149-035-001**




Fixed Elbow 48

- For use with 48mm round tube and 60x40mm rectangular tube.
- Vertical 48mm tube connection for use with Couplings only (not Base 48).
- Die-cast Aluminum G Al Si 12.
- Large cover opening for easier cable pull through.
- No rotation.
- Accessible from the top.



Part No. **R149-020-000**




Fixed Elbow 70

- For use with 70mm round tube and 60x40mm rectangular tube.
- Die-cast Aluminum G Al Si 12.
- No rotation.
- Accessible from the top.



Part No. **R149-020-001**




Technical references and CAD downloads available at www.hammondmfg.com

All dimensions in inches unless specified otherwise



Suspension Systems - NEMA 12, 13

Tara Plus Suspension System


Part No. **R149-040-000**



Rotating Elbow

- For use with 70mm round tube and 60x40mm rectangular tube.
- Die-cast Aluminum G Al Si 12.
- Rotates 300°.
- Accessible from the top.


Part No. **R149-030-000**


Base 48

- For use with 48mm round tube.
- Not for use with any horizontal configurations.
- Compatible with tube up or tube down configurations.
- Die-cast Aluminum G Al Si 12.
- No rotation.


Part No. **R149-030-001**

Base 70

- For use with 70 mm tube.
- Compatible with all vertical and horizontal configurations.
- Compatible with tube up or tube down configurations.
- Die-cast Aluminum G Al Si 12.
- No rotation.



Technical references and CAD downloads available at www.hammondmfg.com

All dimensions in inches unless specified otherwise

Quality Products. Service Excellence.

Suspension Systems - NEMA 12, 13

Tara Plus Suspension System





Part No. **R149-005-001**


Rotating Base 70

- For use with 70 mm tube.
- Compatible with all vertical and horizontal configurations.
- Compatible with tube up or tube down configurations.
- Die-cast Aluminum G Al Si 12.
- Rotates 300°.
- Integrated movement stop.
- Service free bearings.


Hole Pattern




Front Section



End View



TopView





Part No. **R149-005-000**


Socket Joint

- Accepts 60x40mm rectangular tube parallel to its mounting surface.
- Die-cast Aluminum G Al Si 12.
- Integrated movement stop.
- Service free bearings.
- Rotates 300°.
- Adjustment screws (red screws).
- Accessible from the top.


Hole Pattern



**Front Section Socket
Joint**



End View



TopView

Technical references and CAD downloads available at www.hammondmfg.com


All dimensions in inches unless specified otherwise

Suspension Systems - NEMA 12, 13

Tara Plus Suspension System

Operator Interface Enclosure


Suspension System



Part No. **R149-010-000**

Wall Joint



- Accepts 60x40mm rectangular tube perpendicular to its mounting surface.
- Die-cast Aluminum G Al Si 12.
- Rotates 186°.
- Accessible from the top.



Part No. **R149-010-001**

Vertical Wall Joint


- Accepts 70mm tube parallel to its mounting surface.
- Die-cast Aluminum G Al Si 12.
- Rotates 316°.



Part No. **R149-015-000**

Intermediate Joint

- Accepts 60x40mm rectangular tube.
- Die-cast Aluminum G Al Si 12.
- Integrated movement stop.
- One piece below.
- Rotates 300°.



Technical references and CAD downloads available at www.hammondmfg.com

All dimensions in inches unless specified otherwise

Quality Products. Service Excellence.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Hammond:

[R144-301-000](#) [R149-025-000](#) [R149-025-001](#) [R144-311-500](#) [R149-015-000](#) [R144-311-000](#) [ECPP1616](#) [ECP12126](#)
[ECP12168](#) [ECPP1620](#) [ECPH12](#) [ECPH16](#) [R149-030-000](#) [R149-030-001](#) [ECPP2024](#) [ECPH24](#) [ECPH20](#) [R149-](#)
[020-000](#) [R149-020-001](#) [R149-010-000](#) [ECP162010](#) [R149-010-001](#) [R149-035-000](#) [R144-321-500](#) [R149-040-000](#)
[ECP202412](#) [ECP161610](#) [R144-321-000](#) [R149-005-000](#) [R149-005-001](#) [ECPP1216](#) [ECPP1212](#) [R149-035-001](#)