

## LD Series

### Metalized Drum Core Power Inductor



#### Description

- Metalized drum core design utilizes board space
- Current Range from 4.46 amps to 0.52 amps
- Inductance range from 1.0μH to 470μH
- Ferrite core material

#### Applications

- Buck or boost inductor
- Noise filtering and output filter chokes
- Computers
- Power supplies
- Test equipment instrumentation

RoHS  
2002/95/EC

#### Environmental Data

- Storage temperature: -40°C to +125°C
- Operating temperature: -40°C to +125°C (range is application specific). Temperature rise is approximately 40°C at rated rms current.
- Solder reflow temperature: 260°C max. for 10 seconds max.

#### Packaging

- Supplied in tape and reel packaging, LD1 (2,000), LD2 (1,000) parts per reel

| Part Number | Rated Inductance (μH) | OCL <sup>(1)</sup> Nominal | I <sub>rms</sub> <sup>(2)</sup> Amps | I <sub>sat</sub> <sup>(3)</sup> Amps | DCR <sup>(4)</sup> (Ω) (Max.) |
|-------------|-----------------------|----------------------------|--------------------------------------|--------------------------------------|-------------------------------|
| LD1-1R0-R   | 1.0                   | 1.00                       | 2.66                                 | 4.46                                 | 0.0330                        |
| LD1-1R4-R   | 1.4                   | 1.40                       | 2.47                                 | 3.41                                 | 0.0380                        |
| LD1-1R8-R   | 1.8                   | 1.80                       | 2.35                                 | 3.05                                 | 0.0420                        |
| LD1-2R2-R   | 2.2                   | 2.20                       | 2.22                                 | 2.76                                 | 0.0470                        |
| LD1-2R7-R   | 2.7                   | 2.70                       | 2.11                                 | 2.52                                 | 0.0520                        |
| LD1-3R3-R   | 3.3                   | 3.30                       | 2.00                                 | 2.32                                 | 0.0580                        |
| LD1-3R9-R   | 3.9                   | 3.90                       | 1.75                                 | 2.14                                 | 0.0760                        |
| LD1-4R7-R   | 4.7                   | 4.70                       | 1.57                                 | 2.00                                 | 0.0940                        |
| LD1-5R6-R   | 5.6                   | 5.60                       | 1.51                                 | 1.75                                 | 0.1010                        |
| LD1-6R8-R   | 6.8                   | 6.80                       | 1.41                                 | 1.56                                 | 0.1170                        |
| LD1-8R2-R   | 8.2                   | 8.20                       | 1.32                                 | 1.41                                 | 0.1320                        |
| LD1-100-R   | 10                    | 10.0                       | 1.13                                 | 1.28                                 | 0.1820                        |
| LD1-120-R   | 12                    | 12.0                       | 1.05                                 | 1.18                                 | 0.2100                        |
| LD1-150-R   | 15                    | 15.0                       | 0.99                                 | 1.05                                 | 0.2350                        |
| LD1-180-R   | 18                    | 18.0                       | 0.83                                 | 0.98                                 | 0.3380                        |
| LD1-220-R   | 22                    | 22.0                       | 0.78                                 | 0.89                                 | 0.3780                        |
| LD1-270-R   | 27                    | 27.0                       | 0.67                                 | 0.87                                 | 0.5220                        |
| LD1-330-R   | 33                    | 33.0                       | 0.66                                 | 0.75                                 | 0.5400                        |
| LD1-390-R   | 39                    | 39.0                       | 0.63                                 | 0.68                                 | 0.5870                        |
| LD1-470-R   | 47                    | 47.0                       | 0.52                                 | 0.61                                 | 0.8440                        |
| LD1-560-R   | 56                    | 56.0                       | 0.50                                 | 0.57                                 | 0.9370                        |
| LD1-680-R   | 68                    | 68.0                       | 0.46                                 | 0.52                                 | 1.12                          |

#### Notes:

- 1) Open Circuit Inductance Test Parameters: 100kHz, 0.25V<sub>rms</sub>, 0.0Adc  
+/-20% except for LD1-330-R to LD1-331-R and LD2-470-R to LD2-471-R which is +/-10%
- 2) RMS current for an approximate ΔT of 40°C. It is recommended that the temperature of the part not exceed 125°C
- 3) Peak current for an approximate 10% rolloff at 20°C

4) DCR limits @ 20°C

5) Part number definition: LDx-yyy-R

LDx = product code and size, -yyy = inductance value in μH,  
R = decimal point. If no R is present, third character = # of zeros  
-R suffix = RoHS compliant

| Part Number | Rated Inductance (μH) | OCL <sup>(1)</sup> Nominal | I <sub>rms</sub> <sup>(2)</sup> Amps | I <sub>sat</sub> <sup>(3)</sup> Amps | DCR <sup>(4)</sup> (Ω) (Max.) |
|-------------|-----------------------|----------------------------|--------------------------------------|--------------------------------------|-------------------------------|
| LD1-820-R   | 82                    | 82                         | 0.43                                 | 0.50                                 | 1.28                          |
| LD1-101-R   | 100                   | 100                        | 0.36                                 | 0.45                                 | 1.72                          |
| LD1-151-R   | 150                   | 150                        | 0.29                                 | 0.40                                 | 2.68                          |
| LD1-221-R   | 220                   | 220                        | 0.26                                 | 0.33                                 | 3.42                          |
| LD1-331-R   | 330                   | 330                        | 0.22                                 | 0.30                                 | 4.70                          |
| LD2-100-R   | 10                    | 10.0                       | 3.83                                 | 3.45                                 | 0.0700                        |
| LD2-120-R   | 12                    | 12.0                       | 3.57                                 | 3.20                                 | 0.0800                        |
| LD2-150-R   | 15                    | 15.0                       | 3.38                                 | 2.85                                 | 0.0900                        |
| LD2-180-R   | 18                    | 18.0                       | 3.19                                 | 2.60                                 | 0.1000                        |
| LD2-220-R   | 22                    | 22.0                       | 3.13                                 | 2.45                                 | 0.1100                        |
| LD2-270-R   | 27                    | 27.0                       | 2.81                                 | 2.10                                 | 0.1200                        |
| LD2-330-R   | 33                    | 33.0                       | 2.70                                 | 2.01                                 | 0.1300                        |
| LD2-390-R   | 39                    | 39.0                       | 2.42                                 | 1.85                                 | 0.1600                        |
| LD2-470-R   | 47                    | 47.0                       | 2.25                                 | 1.64                                 | 0.1800                        |
| LD2-560-R   | 56                    | 56.0                       | 1.96                                 | 1.50                                 | 0.2400                        |
| LD2-680-R   | 68                    | 68.0                       | 1.88                                 | 1.35                                 | 0.2800                        |
| LD2-820-R   | 82                    | 82                         | 1.63                                 | 1.28                                 | 0.3700                        |
| LD2-101-R   | 100                   | 100                        | 1.53                                 | 1.15                                 | 0.4300                        |
| LD2-121-R   | 120                   | 120                        | 1.43                                 | 1.09                                 | 0.4700                        |
| LD2-151-R   | 150                   | 150                        | 1.23                                 | 0.95                                 | 0.6400                        |
| LD2-181-R   | 180                   | 180                        | 1.15                                 | 0.87                                 | 0.7100                        |
| LD2-221-R   | 220                   | 220                        | 1.00                                 | 0.79                                 | 0.9600                        |
| LD2-271-R   | 270                   | 270                        | 0.94                                 | 0.73                                 | 1.11                          |
| LD2-331-R   | 330                   | 330                        | 0.83                                 | 0.64                                 | 1.26                          |
| LD2-391-R   | 390                   | 390                        | 0.78                                 | 0.58                                 | 1.77                          |
| LD2-471-R   | 470                   | 470                        | 0.74                                 | 0.55                                 | 1.96                          |



Notes:

- 1) Open Circuit Inductance Test Parameters: 100kHz, 0.25V<sub>rms</sub>, 0.0Adc  
+/-20% except for LD1-330-R to LD1-331-R and LD2-470-R to LD2-471-R which is +/-10%
- 2) RMS current for an approximate ΔT of 40°C. It is recommended that the temperature of the part not exceed 125°C
- 3) Peak current for an approximate 10% rolloff at 20°C



4) DCR limits @ 20°C

- 5) Part number definition: LDx-yyy-R  
LDx = product code and size, -yyy = inductance value in μH,  
R = decimal point. If no R is present, third character = # of zeros  
-R suffix = RoHS compliant

## Dimensions - mm



## Recommended Pad Layout



## Marking:


LD1: xxx=inductance value  
per family chart  
LD2: "C" logo  
xxx=inductance value

| Dimensions | A<br>+/-0.3 | B<br>+/-0.3 | C<br>+/-0.3 | G<br>ref | H<br>ref | I<br>ref |
|------------|-------------|-------------|-------------|----------|----------|----------|
| LD1        | 4.5         | 4.0         | 3.2         | 1.5      | 4.5      | 1.75     |
| LD2        | 7.8         | 7.0         | 5.0         | 2.0      | 7.5      | 3.0      |

## Packaging Information

### LD1 Series


Supplied in tape and reel packaging,  
2000 parts per reel, 13" diameter reel.



  
ACTUAL SIZE  
LD1



### LD2 Series

Supplied in tape and reel packaging,  
1000 parts per reel, 13" diameter reel.



  
ACTUAL SIZE  
LD2

## Inductance Characteristics



### North America

Cooper Bussmann  
1225 Broken Sound Parkway NW  
Suite F  
Boca Raton, FL 33487-3533  
Tel: 1-561-998-4100  
Fax: 1-561-241-6640  
Toll Free: 1-888-414-2645

Cooper Bussmann  
P.O. Box 14460  
St. Louis, MO 63178-4460  
Tel: 1-636-394-2877  
Fax: 1-636-527-1607

### Europe

Cooper Bussmann  
Cooper (UK) Limited  
Burton-on-the-Wolds  
Leicestershire • LE12 5TH UK  
Tel: +44 (0) 1509 882 737  
Fax: +44 (0) 1509 882 786

Cooper Bussmann  
Avda. Santa Eulalia, 290  
08223  
Terrassa, (Barcelona), Spain  
Tel: +34 937 362 812  
+34 937 362 813  
Fax: +34 937 362 719

### Asia Pacific

Cooper Bussmann  
1 Jalan Kilang Timor  
#06-01 Pacific Tech Centre  
Singapore 159303  
Tel: +65 278 6151  
Fax: +65 270 4160

This bulletin is intended to present product design solutions and technical information that will help the end user with design applications. Cooper Bussmann reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Cooper Bussmann also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

Life Support Policy: Cooper Bussmann does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

© 2007 Cooper Bussmann  
St. Louis, MO 63178  
www.cooperbussmann.com

