

## Printed-circuit board connector - FMC 0,5/ 2-ST-2,54 - 1821096

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Plug component, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 2, pitch: 2.54 mm, connection method: Push-in spring connection, color: black, contact surface: Gold



The figure shows a 10-position version of the product

### Why buy this product

- ✓ Gold-plated contacts ensure transfer quality remains stable over the long term
- ✓ Time saving push-in connection, tools not required
- ✓ Defined contact force ensures that contact remains stable over the long term
- ✓ Intuitive use through colour coded actuation lever
- ✓ Optimized for tight installation situations: operation and conductor connection from one direction



### Key Commercial Data

|              |                                                                                      |
|--------------|--------------------------------------------------------------------------------------|
| Packing unit | 200 STK                                                                              |
| GTIN         |  |
| GTIN         | 4046356789158                                                                        |

### Technical data

#### Dimensions

|              |         |
|--------------|---------|
| Length [ l ] | 14 mm   |
| Width [ w ]  | 5.58 mm |
| Height [ h ] | 5.35 mm |
| Pitch        | 2.54 mm |
| Dimension a  | 2.54 mm |

#### General

|                     |                           |
|---------------------|---------------------------|
| Range of articles   | FMC 0,5/...-ST            |
| Type of contact     | Female connector          |
| Number of positions | 2                         |
| Connection method   | Push-in spring connection |

# Printed-circuit board connector - FMC 0,5/ 2-ST-2,54 - 1821096

## Technical data

### General

|                                        |                     |
|----------------------------------------|---------------------|
| Insulating material group              | IIIa                |
| Rated surge voltage (III/3)            | 2.5 kV              |
| Rated surge voltage (III/2)            | 2.5 kV              |
| Rated surge voltage (II/2)             | 2.5 kV              |
| Rated voltage (III/3)                  | 32 V                |
| Rated voltage (III/2)                  | 160 V               |
| Rated voltage (II/2)                   | 160 V               |
| Connection in acc. with standard       | EN-VDE              |
| Nominal current $I_N$                  | 6 A                 |
| Nominal cross section                  | 0.5 mm <sup>2</sup> |
| Maximum load current                   | 6 A                 |
| Insulating material                    | LCP                 |
| Flammability rating according to UL 94 | V0                  |
| Stripping length                       | 7 mm                |

### Connection data

|                                                                            |                      |
|----------------------------------------------------------------------------|----------------------|
| Conductor cross section solid min.                                         | 0.14 mm <sup>2</sup> |
| Conductor cross section solid max.                                         | 0.5 mm <sup>2</sup>  |
| Conductor cross section flexible min.                                      | 0.14 mm <sup>2</sup> |
| Conductor cross section flexible max.                                      | 0.5 mm <sup>2</sup>  |
| Conductor cross section flexible, with ferrule without plastic sleeve min. | 0.25 mm <sup>2</sup> |
| Conductor cross section flexible, with ferrule without plastic sleeve max. | 0.34 mm <sup>2</sup> |
| Conductor cross section flexible, with ferrule with plastic sleeve min.    | 0.14 mm <sup>2</sup> |
| Conductor cross section flexible, with ferrule with plastic sleeve max.    | 0.25 mm <sup>2</sup> |
| Conductor cross section AWG min.                                           | 26                   |
| Conductor cross section AWG max.                                           | 20                   |

### Standards and Regulations

|                                        |        |
|----------------------------------------|--------|
| Connection in acc. with standard       | EN-VDE |
| Flammability rating according to UL 94 | V0     |


### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

## Drawings


## Printed-circuit board connector - FMC 0,5/ 2-ST-2,54 - 1821096

Diagram




Type: FMC 0,5/...-ST-2,54 with MC 0,5/...-G-2,54 P20 THR R..

Diagram




Type: FMC 0,5/...-ST-2,54 with MCV 0,5/...-G-2,54 P20 THR R..

Diagram



Type FMC 0,5/...-ST-2,54 with MCV 0,5/...-G-2,54 SMD R..

Diagram



Type: FMC 0,5/...-ST-2,54 with MC 0,5/...-G-2,54 SMD R..

## Approvals

### Approvals

#### Approvals

cULus Recognized / VDE Gutachten mit Fertigungsüberwachung / IECEx CB Scheme / EAC

#### Ex Approvals

### Approval details

|                                |                                                                                     |                                                                                                                                                       |                 |
|--------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|
| cULus Recognized               |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | E60425-19920306 |
|                                | B                                                                                   | C                                                                                                                                                     |                 |
| mm²/AWG/kcmil                  | 26-20                                                                               | 26-20                                                                                                                                                 |                 |
| Nominal current I <sub>N</sub> | 6 A                                                                                 | 6 A                                                                                                                                                   |                 |
| Nominal voltage U <sub>N</sub> | 150 V                                                                               | 50 V                                                                                                                                                  |                 |

## Printed-circuit board connector - FMC 0,5/ 2-ST-2,54 - 1821096

### Approvals

|                                            |                                                                                   |                                                                                                                                                                                                              |          |
|--------------------------------------------|-----------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| VDE Gutachten mit<br>Fertigungsüberwachung |  | <a href="http://www.vde.com/en/Institute/OnlineService/VDE-approved-products/Pages/Online-Search.aspx">http://www.vde.com/en/Institute/OnlineService/<br/>VDE-approved-products/Pages/Online-Search.aspx</a> | 40042258 |
|                                            |                                                                                   |                                                                                                                                                                                                              |          |
| mm²/AWG/kcmil                              | 0.14-0.5                                                                          |                                                                                                                                                                                                              |          |
| Nominal current I <sub>N</sub>             | 6 A                                                                               |                                                                                                                                                                                                              |          |
| Nominal voltage U <sub>N</sub>             | 160 V                                                                             |                                                                                                                                                                                                              |          |

|                                |  |                                                                                   |                                                           |              |
|--------------------------------|--|-----------------------------------------------------------------------------------|-----------------------------------------------------------|--------------|
| IECEE CB Scheme                |  |  | <a href="http://www.iecee.org/">http://www.iecee.org/</a> | DE1-55663-B1 |
|                                |  |                                                                                   |                                                           |              |
| mm²/AWG/kcmil                  |  | 0.14-0.5                                                                          |                                                           |              |
| Nominal current I <sub>N</sub> |  | 6 A                                                                               |                                                           |              |
| Nominal voltage U <sub>N</sub> |  | 160 V                                                                             |                                                           |              |

|     |                                                                                     |         |
|-----|-------------------------------------------------------------------------------------|---------|
| EAC |  | B.01742 |
|-----|-------------------------------------------------------------------------------------|---------|

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>